

EAO – Your Expert Partner for Human Machine Interfaces

82-4151.0144 - Indicator 16 mm stainless-steel

82-4151.0144 - Indicator 16 mm stainless-steel



Attention: The preview is based on a sample product. This can differ from your current configuration.

Mounting

Mounting cut-out	Ø 16 mm
Design	flush

Front

Front dimension	Ø 18 mm
Front shape	round
Front ring shape	flush
Front bezel material	Stainless steel

Other Attributes

Operating voltage	24 V AC/DC
Weight	0,018 kg
Operation current	7 mA

Operating-/Indication part

Lens optics	opaque
Lens material	Stainless steel
Lens profile	flat
Lens illumination	illuminative
Lens colour	Stainless steel

IP-Rating

Front protection	IP65, IP67
------------------	------------

Connection Method

Terminal	Solder 2.8 x 0.5 mm
----------	---------------------

Illumination

Illumination	Ring with yellow LED
--------------	----------------------


Function

Indicator


EAO – Your Expert Partner for Human Machine Interfaces

82-4151.0144 - Indicator 16 mm stainless-steel


Dimensions




Mounting cut-outs



Wiring diagram



Component layout



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

[82-4151.0144](#)