

DS Series Detect Switch




Features/Benefits

- Compact design
- Low actuation force
- Detect mechanical movement
- Left and right options
- Right angle options

Typical Applications

- Computer peripherals
- Office equipment
- Consumer electronics
- Appliances
- Audio and visual equipment







PART NUMBER	PACKAGING	SCHEMATIC
DS-02005	1,000 pieces	1P-1T

Specifications

CONTACT ARRANGEMENT: SPST, NO
 CONTACT RATING: 100mA @ 30 VDC
 OPERATING LIFE: 50,000 cycles
 OPERATING FORCE: 50 gf max.
 PRE-TRAVEL: 0.7 mm
 TOTAL TRAVEL: 2.6 mm
 INITIAL CONTACT RESISTANCE: 1 Ω max.
 INSULATION RESISTANCE: 100 M Ω min. @ 100 VDC 60 sec.
 DIELECTRIC STRENGTH: 100 V AC (50-60Hz) 60 sec.
 OPERATING TEMPERATURE: -40°C to +85°C.

Materials

KNOB: PA
 COVER: PA
 SPRING: Gold plated, copper alloy
 HOUSING: PA
 TERMINAL: Silver plated, copper alloy







PART NUMBER	PACKAGING	SCHEMATIC
DS-02005 (30)	1,000 pieces	1P-1T

Specifications

CONTACT ARRANGEMENT: SPST, NO
 CONTACT RATING: 100mA @ 30 VDC
 OPERATING LIFE: 50,000 cycles
 OPERATING FORCE: 30 gf max.
 PRE-TRAVEL: 0.7 mm
 TOTAL TRAVEL: 2.2 mm
 INITIAL CONTACT RESISTANCE: 1 Ω max.
 INSULATION RESISTANCE: 100 M Ω min. @ 100 VDC 60 sec.
 DIELECTRIC STRENGTH: 100 V AC (50-60Hz) 60 sec.
 OPERATING TEMPERATURE: -40°C to +85°C.

Materials


KNOB: PA
 COVER: PA
 SPRING: Gold plated, copper alloy
 HOUSING: PA
 TERMINAL: Silver plated, copper alloy



Detect



PART NUMBER	PACKAGING	SCHEMATIC
DS-040-02	1,000 pieces	1P-1T N.O.




Specifications

CONTACT ARRANGEMENT: SPST, NO
 CONTACT RATING: 0.1A @ 16 VDC
 OPERATING LIFE: 20,000 cycles
 OPERATING FORCE: 30 ± 15 gf
 TRAVEL: 0.90 ± 0.20 mm
 INITIAL CONTACT RESISTANCE: 40 m Ω max.
 INSULATION RESISTANCE: 100 M Ω min. @ 250 VDC 60 sec.
 DIELECTRIC STRENGTH: 250 V AC (50-60Hz) 60 sec.
 OPERATING TEMPERATURE: -20°C to +70°C.

Materials

LEVER: POM
 CASE: PBT
 COVER: PC

PART NUMBER	PACKAGING	SCHEMATIC
DS-180 RT	3000 pieces	1P - 1T N.O.



Specifications

CONTACT ARRANGEMENT: SPST NO
 CONTACT RATING: 1mA @ 5 VDC
 OPERATING LIFE: 50,000 cycles
 OPERATING FORCE: 60 gf max.
 TOTAL TRAVEL: 2.0±0.2 mm
 INITIAL CONTACT RESISTANCE: 5Ω max.
 INSULATION RESISTANCE: 100 M Ω min. @ 100 VDC 60 sec.
 DIELECTRIC STRENGTH: 100 V AC (50-60Hz) 60 sec.
 OPERATING TEMPERATURE: -40°C to +85°C.

Materials

KNOB: PA
 COVER: SPTE
 SPRING: SUS
 HOUSING: LCP
 TERMINAL: Silver plated





Detect

DS Series Detect Switch



PART NUMBER	PACKAGING	SCHEMATIC
DS-080	1,000 pieces	



PIERCING PLAN

Specifications

CONTACT ARRANGEMENT: SPDT

CONTACT RATING: 100mA @ 30 VDC

OPERATING LIFE: 20,000 cycles

OPERATING FORCE: 30 ± 20 gf

OVER TRAVEL: 2.0 ± 0.40 mm

INITIAL CONTACT RESISTANCE: 200 m Ω max.

INSULATION RESISTANCE: 10 M Ω min. @ 250 VDC 60 sec.

DIELECTRIC STRENGTH: 250 V AC (50-60Hz) 60 sec.

OPERATING TEMPERATURE: -20°C to +70°C.

Materials

KNOB: POM

COVER: PA46




SLIDER: PBT

HOUSING: PA46

TERMINAL: Silver plated



PART NUMBER	PACKAGING	SCHEMATIC
DS-080-C PA	1,000 pieces	



PIERCING PLAN

Specifications

CONTACT ARRANGEMENT: SPDT

CONTACT RATING: 100mA @ 30 VDC

OPERATING LIFE: 20,000 cycles

OPERATING FORCE: 30 ± 20 gf

OVER TRAVEL: 2.0 ± 0.40 mm

INITIAL CONTACT RESISTANCE: 200 m Ω max.

INSULATION RESISTANCE: 10 M Ω min. @ 250 VDC 60 sec.

DIELECTRIC STRENGTH: 250 V AC (50-60Hz) 60 sec.

OPERATING TEMPERATURE: -20°C to +70°C.

Materials

KNOB: POM

COVER: PA46

SLIDER: PBT

HOUSING: PA46

TERMINAL: Silver plated



E

Detect



PART NUMBER	PACKAGING	SCHEMATIC
DS-09005-02 RP	500 pieces	

Specifications

CONTACT ARRANGEMENT: SPST

CONTACT RATING: 1mA @ 5 VDC

OPERATING LIFE: 100,000 cycles

OPERATING FORCE: 50 gf max.

TOTAL TRAVEL: 4.5±0.2 mm

INITIAL CONTACT RESISTANCE: 500 m Ω max.

INSULATION RESISTANCE: 100 M Ω min. @ 500 VDC 60 sec.

DIELECTRIC STRENGTH: 500 V AC (50-60Hz) 60 sec.

OPERATING TEMPERATURE: -20°C to +70°C.


Materials

LEVER: POM

COVER: PA

HOUSING: PA

TERMINAL: Silver plated



Detect

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[DS-02005 \(30\)](#) [DS-080-C PA](#) [DS203A](#) [DS02005](#) [DS21805](#) [DS0900502RP](#) [DS080](#) [DS02005A](#) [DS202A](#)
[DS0900502BK](#) [DS0200530](#) [DS04002](#) [DS080CPA](#)