

Series 45

Innovative and comprehensive. Modular.

<https://eao.com/45>



45 Information about the Series

Key advantages

- Comprehensive and modular series
- Rugged in use (up to IP69K)
- Easy to assemble and use
- Modern design with many options

Typical application areas

Various operating and control functions in machinery and equipment, such as:

- Start and stop
- Reset
- On and off
- Function control

Functions

- Pushbutton
- Illuminated pushbutton
- Double pushbutton
- Mushroom-head pushbutton
- Palm Switch
- Selector switch
- Keylock switch
- ID keylock switch
- Toggle stick
- Toggle switch
- Indicator
- Buzzer
- Potentiometer
- Stop switch
- Emergency stop switch

Design

- Flush
- Raised

IP front protection

- IP40
- IP65
- IP66
- IP67
- IP69K

Ratings

- 500 VAC (10 A)

Mounting cut-outs

- Ø 22.3 mm
- Ø 30.5 mm

Terminal

- Screw terminal
- PCB
- Spring-loaded terminal

Lens Material

- Plastic

Markings

- Laser marking

Approvals

- CCC
- CSA
- UL

Conformities

- CE
- 2014/30/EU (EMC)
- 2014/35/EU (LVD)
- 2011/65/EU (RoHS)



Product overview	4
Flush design	
Pushbutton	5
Illuminated pushbutton	6
Selector switch 2 positions short lever	7
Selector switch 2 positions long lever	8
Selector switch 3 positions short lever	9
Selector switch 3 positions long lever	10
Keylock switch 2 and 3 positions	11
Indicator	12
Raised design	
Pushbutton	13
Illuminated pushbutton	17
Double pushbutton	20
Illuminated double pushbutton	22
Mushroom-head pushbutton Ø 30 mm	24
Mushroom-head pushbutton Ø 40 mm	26
Mushroom-head pushbutton Ø 60 mm	28
Mushroom-head pushbutton illuminated Ø 30 mm	30
Mushroom-head pushbutton illuminated Ø 40 mm	32
Mushroom-head pushbutton illuminated Ø 60 mm	34
Palm switch	36
Selector switch 2 positions short lever	37
Selector switch 2 positions long lever	39
Selector switch 2 positions round lever	41
Selector switch 3 positions short lever	42
Selector switch 3 positions long lever	44
Selector switch 4 positions round lever	46
Keylock switch 2 positions	47
Keylock switch 3 positions	48
ID keylock switch	50
Toggle stick	51
Toggle switch	53
Indicator full-face illumination	54
Indicator front illumination	55
Buzzer	56
Potentiometer	57
Stop switch	58
Emergency stop switch foolproof, EN IEC 60947-5-5	60
Illuminated emergency stop switch, foolproof, EN IEC 60947-5-5	61
Components	63
Accessories	65
Drawings	81
Technical data	95
Marking	103
Application guidelines	115
Index	122
	123

45 Product overview



Functions

Indicator
 Buzzer
 Pushbutton
 Double pushbutton
 Illuminated pushbutton
 Emergency stop switch
 Stop switch
 Palm switch
 Mushroom-head pushbutton
 Keylock switch
 ID keylock switch
 Selector switch
 Potentiometer
 Toggle stick
 Toggle switch



Holder



Switching elements


1 Switching element 1 NC/1 NO
 2 Switching elements 2 NC or 2 NO




Lamp element

Pushbutton, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 65

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information


- Front panel thickness 1 ... 6 mm



Actuator, Front dimension Ø 38 mm

Switching action	Lens colour	Lens shape	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Black	flush	Sand grey	Metal	Silver	Metal	45-2131.4F10.000	72
	Red	flush	Sand grey	Metal	Silver	Metal	45-2131.4F20.000	72
	Yellow	flush	Sand grey	Metal	Silver	Metal	45-2131.4F40.000	72
	Green	flush	Sand grey	Metal	Silver	Metal	45-2131.4F50.000	72
	Blue	flush	Sand grey	Metal	Silver	Metal	45-2131.4F60.000	72
	White	flush	Sand grey	Metal	Silver	Metal	45-2131.4F90.000	72
Maintained	Black	flush	Sand grey	Metal	Silver	Metal	45-2134.4F10.000	73
	Red	flush	Sand grey	Metal	Silver	Metal	45-2134.4F20.000	73
	Yellow	flush	Sand grey	Metal	Silver	Metal	45-2134.4F40.000	73
	Green	flush	Sand grey	Metal	Silver	Metal	45-2134.4F50.000	73
	Blue	flush	Sand grey	Metal	Silver	Metal	45-2134.4F60.000	73
	White	flush	Sand grey	Metal	Silver	Metal	45-2134.4F90.000	73

Wiring diagrams




Wiring diagram 72




Wiring diagram 73

45 Flush design

Illuminated pushbutton, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

General information

- Front panel thickness 1 ... 6 mm



Mounting cut-outs [mm]

Equipment consisting of (schematic overview)

	Actuator	
	Holder	Page 65
	Switching element	Page 67
	Illumination element	Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 38 mm


Switching action	Lens colour	Lens shape	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Red	flush	Sand grey	Metal	Silver	Metal	45-2231.4FE0.000	191
	Yellow	flush	Sand grey	Metal	Silver	Metal	45-2231.4FG0.000	191
	Green	flush	Sand grey	Metal	Silver	Metal	45-2231.4FH0.000	191
	Blue	flush	Sand grey	Metal	Silver	Metal	45-2231.4FJ0.000	191
	Colourless	flush	Sand grey	Metal	Silver	Metal	45-2231.4FK0.000	191
Maintained	Red	flush	Sand grey	Metal	Silver	Metal	45-2234.4FE0.000	192
	Yellow	flush	Sand grey	Metal	Silver	Metal	45-2234.4FG0.000	192
	Green	flush	Sand grey	Metal	Silver	Metal	45-2234.4FH0.000	192
	Blue	flush	Sand grey	Metal	Silver	Metal	45-2234.4FJ0.000	192
	Colourless	flush	Sand grey	Metal	Silver	Metal	45-2234.4FK0.000	192

Wiring diagrams




Selector switch 2 positions short lever, IP66, IP67, IP69K


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.




Dimensions [mm]



Product can differ from the current configuration.

- General information
- Front panel thickness 1 ... 6 mm
 - It is advisable to choose a white illumination



Mounting cut-outs [mm]



Actuator, Front dimension Ø 38 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest - Maintained	90° right	Red	Sand grey	Metal	Metal	45-2828.4C20.001	194
	90° right	Green	Sand grey	Metal	Metal	45-2828.4C50.001	194
	90° right	White	Sand grey	Metal	Metal	45-2828.4C90.001	194
Rest - Momentary	45° right	Red	Sand grey	Metal	Metal	45-2844.4C20.006	193
	45° right	Green	Sand grey	Metal	Metal	45-2844.4C50.006	193
	45° right	White	Sand grey	Metal	Metal	45-2844.4C90.006	193

Wiring diagrams

Wiring diagram 193


Wiring diagram 194

45 Flush design

Selector switch 2 positions long lever, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- Front panel thickness 1 ... 6 mm
- It is advisable to choose a white illumination



Mounting cut-outs [mm]


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 38 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest - Maintained	90° right	Red	Sand grey	Metal	Metal	45-2828.4D20.001	194
	90° right	Green	Sand grey	Metal	Metal	45-2828.4D50.001	194
	90° right	White	Sand grey	Metal	Metal	45-2828.4D90.001	194
Rest - Momentary	45° right	Green	Sand grey	Metal	Metal	45-2844.4D50.006	193
	45° right	White	Sand grey	Metal	Metal	45-2844.4D90.006	193

Wiring diagrams




Wiring diagram 193


Wiring diagram 194

Selector switch 3 positions short lever, IP66, IP67, IP69K


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.




Dimensions [mm]




Product can differ from the current configuration.

General information

- Front panel thickness 1 ... 6 mm
- It is advisable to choose a white illumination




Mounting cut-outs [mm]



Actuator, Front dimension Ø 38 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary - Rest - Momentary	45° left / 45° right	Red	Sand grey	Metal	Metal	45-280S.4C20.003	196
	45° left / 45° right	Green	Sand grey	Metal	Metal	45-280S.4C50.003	196
	45° left / 45° right	White	Sand grey	Metal	Metal	45-280S.4C90.003	196
Maintained - Rest - Maintained	45° left / 45° right	Red	Sand grey	Metal	Metal	45-2819.4C20.003	195
	45° left / 45° right	Green	Sand grey	Metal	Metal	45-2819.4C50.003	195
	45° left / 45° right	White	Sand grey	Metal	Metal	45-2819.4C90.003	195

Wiring diagrams




45 Flush design

Selector switch 3 positions long lever, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- Front panel thickness 1 ... 6 mm
- It is advisable to choose a white illumination



Mounting cut-outs [mm]


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 38 mm


Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary - Rest - Momentary	45° left / 45° right	Red	Sand grey	Metal	Metal	45-280S.4D20.003	196
	45° left / 45° right	Green	Sand grey	Metal	Metal	45-280S.4D50.003	196
	45° left / 45° right	White	Sand grey	Metal	Metal	45-280S.4D90.003	196
Maintained - Rest - Maintained	45° left / 45° right	Red	Sand grey	Metal	Metal	45-2819.4D20.003	195
	45° left / 45° right	Green	Sand grey	Metal	Metal	45-2819.4D50.003	195
	45° left / 45° right	White	Sand grey	Metal	Metal	45-2819.4D90.003	195

Wiring diagrams




Keylock switch 2 and 3 positions, IP66, IP67, IP69K

Equipment consisting of (schematic overview)




Actuator



Holder


Page 65



Switching element

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.
To obtain a complete unit, please select the red components from the pages shown.




Dimensions [mm]



Product can differ from the current configuration.

General information

- Front panel thickness 1 ... 6 mm
- The standard lock: RONIS, T254



Mounting cut-outs [mm]



Actuator, Front dimension Ø 38 mm

Switching action	Switching angle	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Maintained (a) - Rest (a) - Maintained (a)	45° left / 45° right	Sand grey	Metal	Metal	45-290F.4F00.113	83
Rest (a) - Maintained (a)	90° right	Sand grey	Metal	Metal	45-290H.4F00.111	79
Rest - Maintained (a)	90° right	Sand grey	Metal	Metal	45-290J.4F00.111	79
Rest (a) - Momentary	45° right	Sand grey	Metal	Metal	45-290J.4F00.116	78


a = Key remove

Wiring diagrams


Wiring diagram 78	Wiring diagram 79	Wiring diagram 83

45 Flush design

Indicator, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

General information

- Front panel thickness 1 ... 6 mm



Mounting cut-outs [mm]

Equipment consisting of (schematic overview)

	Actuator	
	Holder	Page 65
	Illumination element	Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 38 mm


Front bezel colour	Front bezel material	Lens cap colour	Housing material	Part No.	Wiring diagram
Sand grey	Metal	Red	Metal	45-2T07.4FE0.000	190
	Metal	Yellow	Metal	45-2T07.4FG0.000	190
	Metal	Green	Metal	45-2T07.4FH0.000	190
	Metal	Blue	Metal	45-2T07.4FJ0.000	190
	Metal	Colourless	Metal	45-2T07.4FK0.000	190

Wiring diagrams



Pushbutton, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 65


Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Mounting cut-outs [mm]



Product can differ from the current configuration.

General information

- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 29,5 mm

Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Black	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1110.000	72
	Red	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1120.000	72
	Yellow	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1140.000	72
	Green	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1150.000	72

45 Raised design

Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Blue	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1160.000	72
	Grey	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1180.000	72
	White	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.1190.000	72
	Colourless	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2131.11K0.000	72
	Black	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1210.000	72
	Red	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1220.000	72
	Yellow	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1240.000	72
	Green	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1250.000	72
	Blue	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1260.000	72
	White	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2131.1290.000	72
	Black	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2110.000	72
	Red	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2120.000	72
	Yellow	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2140.000	72
	Green	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2150.000	72
	Blue	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2160.000	72
	Grey	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2180.000	72
	White	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.2190.000	72
	Colourless	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2131.21K0.000	72
	Black	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2131.2210.000	72
	Red	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2131.2220.000	72
	Yellow	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2131.2240.000	72
	Green	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2131.2250.000	72
	Blue	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2131.2260.000	72

Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Black	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1110.000	73
	Red	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1120.000	73
	Yellow	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1140.000	73
	Green	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1150.000	73
	Blue	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1160.000	73
	White	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2134.1190.000	73
	Black	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2110.000	73
	Red	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2120.000	73
	Yellow	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2140.000	73
	Green	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2150.000	73
	Blue	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2160.000	73
	White	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2134.2190.000	73
Momentary	Red	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2131.1320.000	72
	Green	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2131.1350.000	72
	Blue	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2131.1360.000	72
	Yellow	flush	lower than front bezel	Silver	Metal	Silver	Metal	45-2131.2340.000	72
	Green	flush	lower than front bezel	Silver	Metal	Silver	Metal	45-2131.2350.000	72
	Blue	flush	lower than front bezel	Silver	Metal	Silver	Metal	45-2131.2360.000	72
	Yellow	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2131.1440.000	72
	Blue	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2131.1460.000	72

Wiring diagrams

Wiring diagram 72	Wiring diagram 73

45 Raised design

01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96



Robust. Ästhetisch und vielseitig. *EAO Baureihe 45 Leuchtdrucktasten.*

Prädestiniert für den rauen Einsatz – dank robuster Ausführung in Schutzart IP69K und dem flachen, ästhetischen Design.

- Robuste Metall- oder Kunststoff-Ausführung (IP69K)
- Einfache und schnelle Montage ohne Spezialwerkzeug
- Ästhetisches Design mit harmonischer LED Ausleuchtung
- Lange mechanische Lebensdauer
- Modulares System mit kundenspezifischen Optionen

eao ■

www.eao.com/45


Your Expert Partner for Human Machine Interfaces

Illuminated pushbutton, IP66, IP67, IP69K

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67




Illumination element

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 29,5 mm


Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Red	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11E0.000	191
	Amber	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11F0.000	191
	Yellow	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11G0.000	191
	Green	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11H0.000	191
	Blue	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11J0.000	191
	Colourless	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11K0.000	191
	White	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2231.11N0.000	191

45 Raised design

Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Momentary	Red	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2231.12E0.000	191
	Yellow	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2231.12G0.000	191
	Green	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2231.12H0.000	191
	Blue	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2231.12J0.000	191
	Colour-less	flush	raised above front bezel	Black	Plastic	Black	Plastic	45-2231.12K0.000	191
	Blue	flush	lower than front bezel	Black	Plastic	Black	Plastic	45-2231.14J0.000	191
	Red	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21E0.000	191
	Amber	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21F0.000	191
	Yellow	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21G0.000	191
	Green	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21H0.000	191
	Blue	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21J0.000	191
	Colour-less	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21K0.000	191
	White	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2231.21N0.000	191
	Red	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22E0.000	191
	Amber	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22F0.000	191
	Yellow	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22G0.000	191
	Green	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22H0.000	191
	Blue	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22J0.000	191
	Colour-less	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22K0.000	191
	White	flush	raised above front bezel	Silver	Metal	Silver	Metal	45-2231.22N0.000	191
Maintained	Red	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11E0.000	192
	Yellow	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11G0.000	192
	Green	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11H0.000	192
	Blue	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11J0.000	192
	Colour-less	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11K0.000	192
	White	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11N0.000	192
	Red	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21E0.000	192
	Yellow	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21G0.000	192
	Green	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21H0.000	192
	Blue	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21J0.000	192
	White	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21N0.000	192

Switching action	Lens colour	Lens shape	Lens type	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Blue	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11J0.000	192
	Colourless	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11K0.000	192
	White	flush	level with front bezel	Black	Plastic	Black	Plastic	45-2234.11N0.000	192
	Red	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21E0.000	192
	Yellow	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21G0.000	192
	Green	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21H0.000	192
	Blue	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21J0.000	192
	White	flush	level with front bezel	Silver	Metal	Silver	Metal	45-2234.21N0.000	192

Wiring diagrams




45 Raised design

Double pushbutton, IP66, IP67, IP69K



Product can differ from the current configuration.



Dimensions [mm]


Equipment consisting of (schematic overview)



Actuator



Holder



Switching element

Page 65


Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]




Actuator, Front dimension 58 mm x 30 mm

Switching action	Lens colour	Lens shape	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram	Component Layout
Momentary	Green/ Red	flush	Black	Plastic	Black	Plastic	45-2J31.15T0.000	200	25
	White / Black	flush	Black	Plastic	Black	Plastic	45-2J31.15V0.000	200	25
	Green/ Red	flush	Black	Plastic	Black	Plastic	45-2J31.16T0.000	200	25
	White / Black	flush	Black	Plastic	Black	Plastic	45-2J31.16V0.000	200	25
	Green/ Red	flush	Silver	Metal	Silver	Metal	45-2J31.25T0.000	200	25
	White / Black	flush	Silver	Metal	Silver	Metal	45-2J31.25V0.000	200	25
	Green/ Red	flush	Silver	Metal	Silver	Metal	45-2J31.26T0.000	200	25
	White / Black	flush	Silver	Metal	Silver	Metal	45-2J31.26V0.000	200	25

Wiring diagrams



Component layouts



- A = Switching action
- B = green (white) button pressed
- C = red (black) button pressed
- D = Arrangement switching element corresponds to designation of front adaptor
- E = Switching element actuated


01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

Illuminated double pushbutton, IP66, IP67, IP69K



Product can differ from the current configuration.



Dimensions [mm]


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element

Page 65

Page 67


Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- With illuminative centre window
- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]




Actuator, Front dimension 58 mm x 30 mm

Switching action	Lens colour	Lens shape	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram	Component Layout
Momentary	White / Black	flush	Black	Plastic	Black	Plastic	45-2K31.15V0.000	201	25
	Green/ Red	flush	Black	Plastic	Black	Plastic	45-2K31.16T0.000	201	25
	White / Black	flush	Black	Plastic	Black	Plastic	45-2K31.16V0.000	201	25

Wiring diagrams



Component layouts



- A = Switching action
- B = green (white) button pressed
- C = red (black) button pressed
- D = Arrangement switching element corresponds to designation of front adaptor
- E = Switching element actuated



Versatile. Aesthetic and robust.
EAO Series 45 double pushbuttons.

Double pushbuttons are cost effective, compact pushbuttons, ideal for start/stop, up/down or similar machine functions.


- Compact construction – two switches in one
- Range of colours and marking options
- IP69K sealed and optional silicon covers
- Plastic or metal versions
- Up to three contacts for each pushbutton
- Optional illumination

45 Raised design

Mushroom-head pushbutton Ø 30 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]

Equipment consisting of (schematic overview)




Actuator



Holder

Page 65



Switching element

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.
To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 30 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Black	Black	Plastic	Black	Plastic	45-2530.1810.000	73
	Red	Black	Plastic	Black	Plastic	45-2530.1820.000	73
	Red	Silver	Metal	Silver	Metal	45-2530.2820.000	73
Momentary	Black	Black	Plastic	Black	Plastic	45-2531.1810.000	72
	Red	Black	Plastic	Black	Plastic	45-2531.1820.000	72
	Yellow	Black	Plastic	Black	Plastic	45-2531.1840.000	72
	Black	Silver	Metal	Silver	Metal	45-2531.2810.000	72
	Red	Silver	Metal	Silver	Metal	45-2531.2820.000	72
	Yellow	Silver	Metal	Silver	Metal	45-2531.2840.000	72
	Green	Silver	Metal	Silver	Metal	45-2531.2850.000	72

Wiring diagrams

	
Wiring diagram 72	Wiring diagram 73

01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

Follow us.
We are on LinkedIn!
EAO creates possibilities. Since 1947.







[Come take a look at our LinkedIn profile today!](https://www.linkedin.com/company/eao/) Be sure to give us
a follow so that you can fully interact with us.

<https://www.linkedin.com/company/eao/>

www.eao.com


eao ■
Your Expert Partner for Human Machine Interfaces

45 Raised design

Mushroom-head pushbutton Ø 40 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


Equipment consisting of (schematic overview)



Actuator



Holder



Switching element

Page 65


Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings



Mounting cut-outs [mm]



Actuator, Front dimension Ø 40 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Black	Black	Plastic	Black	Plastic	45-2530.1910.000	73
	Red	Black	Plastic	Black	Plastic	45-2530.1920.000	73
	Yellow	Black	Plastic	Black	Plastic	45-2530.1940.000	73
	Green	Black	Plastic	Black	Plastic	45-2530.1950.000	73
	Black	Silver	Metal	Silver	Metal	45-2530.2910.000	73
	Red	Silver	Metal	Silver	Metal	45-2530.2920.000	73
	Yellow	Silver	Metal	Silver	Metal	45-2530.2940.000	73
Momentary	Black	Black	Plastic	Black	Plastic	45-2531.1910.000	72
	Red	Black	Plastic	Black	Plastic	45-2531.1920.000	72
	Yellow	Black	Plastic	Black	Plastic	45-2531.1940.000	72
	Green	Black	Plastic	Black	Plastic	45-2531.1950.000	72
	Black	Silver	Metal	Silver	Metal	45-2531.2910.000	72
	Red	Silver	Metal	Silver	Metal	45-2531.2920.000	72
	Yellow	Silver	Metal	Silver	Metal	45-2531.2940.000	72
Momentary / maintained	Red	Silver	Metal	Silver	Metal	45-2532.2920.000	208
	Black	Silver	Metal	Silver	Metal	45-2533.2910.000	209
	Red	Silver	Metal	Silver	Metal	45-2533.2920.000	209
	Black	Silver	Metal	Silver	Metal	45-2533.2920.000	209

Wiring diagrams

			
Wiring diagram 72	Wiring diagram 73	Wiring diagram 208	Wiring diagram 209


01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

Mushroom-head pushbutton Ø 60 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

Equipment consisting of (schematic overview)




Actuator



Holder

Page 65



Switching element


Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings



Mounting cut-outs [mm]



Actuator, Front dimension Ø 60 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Black	Silver	Metal	Silver	Metal	45-2530.2A10.000	73
	Red	Silver	Metal	Silver	Metal	45-2530.2A20.000	73
Momentary	Black	Black	Plastic	Black	Plastic	45-2531.1A10.000	72
	Red	Black	Plastic	Black	Plastic	45-2531.1A20.000	72
	Yellow	Black	Plastic	Black	Plastic	45-2531.1A40.000	72
	Green	Black	Plastic	Black	Plastic	45-2531.1A50.000	72
	Black	Silver	Metal	Silver	Metal	45-2531.2A10.000	72
	Red	Silver	Metal	Silver	Metal	45-2531.2A20.000	72

Wiring diagrams

	
Wiring diagram 72	Wiring diagram 73


01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

Mushroom-head pushbutton illuminated Ø 30 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element

Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 30 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Yellow	Black	Plastic	Black	Plastic	45-2630.18G0.000	192
	Red	Silver	Metal	Silver	Metal	45-2630.28E0.000	192
	Green	Silver	Metal	Silver	Metal	45-2630.28H0.000	192
	Blue	Silver	Metal	Silver	Metal	45-2630.28J0.000	192
	Colourless	Silver	Metal	Silver	Metal	45-2630.28K0.000	192
Momentary	Red	Black	Plastic	Black	Plastic	45-2631.18E0.000	191
	Yellow	Black	Plastic	Black	Plastic	45-2631.18G0.000	191
	Green	Black	Plastic	Black	Plastic	45-2631.18H0.000	191
	Blue	Black	Plastic	Black	Plastic	45-2631.18J0.000	191
	White	Black	Plastic	Black	Plastic	45-2631.18N0.000	191
	White	Silver	Metal	Silver	Metal	45-2631.28N0.000	191

Wiring diagrams




01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

Mushroom-head pushbutton illuminated Ø 40 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67



Illumination element


Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings





Mounting cut-outs [mm]



Actuator, Front dimension Ø 40 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Red	Black	Plastic	Black	Plastic	45-2630.19E0.000	192
	Green	Black	Plastic	Black	Plastic	45-2630.19H0.000	192
	Blue	Black	Plastic	Black	Plastic	45-2630.19J0.000	192
	Red	Silver	Metal	Silver	Metal	45-2630.29E0.000	192
	Yellow	Silver	Metal	Silver	Metal	45-2630.29G0.000	192
	Blue	Silver	Metal	Silver	Metal	45-2630.29J0.000	192
	Colourless	Silver	Metal	Silver	Metal	45-2630.29K0.000	192
Momentary	Yellow	Black	Plastic	Black	Plastic	45-2631.19G0.000	191
	Green	Black	Plastic	Black	Plastic	45-2631.19H0.000	191
	Colourless	Black	Plastic	Black	Plastic	45-2631.19K0.000	191
	White	Black	Plastic	Black	Plastic	45-2631.19N0.000	191
	Amber	Silver	Metal	Silver	Metal	45-2631.29F0.000	191
	Yellow	Silver	Metal	Silver	Metal	45-2631.29G0.000	191
	Green	Silver	Metal	Silver	Metal	45-2631.29H0.000	191
	White	Silver	Metal	Silver	Metal	45-2631.29N0.000	191
	Red	Silver	Metal	Silver	Metal	45-2632.29E0.000	191

Wiring diagrams



Innovative and comprehensive.
EAO's new Series 45.

Modular, aesthetic and robust for every conceivable HMI function of machine operating.


- Comprehensive and modular Series
- Rugged in use (up to IP69K)
- Easy to assemble and use
- Modern design with many options
- Value added services
- Long service life (up to 10 million switching cycles, depending on function)

45 Raised design

Mushroom-head pushbutton illuminated Ø 60 mm, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67



Illumination element


Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]



Actuator, Front dimension Ø 60 mm

Switching action	Lens colour	Front bezel colour	Front bezel material	Housing colour	Housing material	Part No.	Wiring diagram
Maintained	Red	Silver	Metal	Silver	Metal	45-2630.2AE0.000	192
	Blue	Silver	Metal	Silver	Metal	45-2630.2AJ0.000	192
	Colourless	Silver	Metal	Silver	Metal	45-2630.2AK0.000	192
Momentary	Amber	Silver	Metal	Silver	Metal	45-2631.2AF0.000	191
	Yellow	Silver	Metal	Silver	Metal	45-2631.2AG0.000	191
	Green	Silver	Metal	Silver	Metal	45-2631.2AH0.000	191
	White	Silver	Metal	Silver	Metal	45-2631.2AN0.000	191

Wiring diagrams



Wiring diagram 192


01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

Palm switch, IP66, IP67, IP69K




Product can differ from the current configuration.




Dimensions [mm]

Equipment consisting of (schematic overview)



Actuator



Switching element


Page 71

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- Mounting depth, incl. front plate, see chapter drawings




Actuator, Front dimension 85 mm x 85 mm


Switching action	Lens colour	Housing colour	Housing material	Part No.
Momentary	Black	Grey	Plastic	45-481.1810
	Black	Grey	Metal	45-481.2810
Maintained	Red	Yellow	Plastic	45-482.1810
	Red	Yellow	Metal	45-482.2810

Selector switch 2 positions short lever, IP66, IP67, IP69K


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- External diameter of the short lever 32.3 mm
- Mounting depth, incl. front plate, see chapter drawings




Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest - Maintained	90° right	Red	Black	Plastic	Plastic	45-2828.1C20.001	214
	90° right	Yellow	Black	Plastic	Plastic	45-2828.1C40.001	214
	90° right	Green	Black	Plastic	Plastic	45-2828.1C50.001	214
	90° right	Blue	Black	Plastic	Plastic	45-2828.1C60.001	214
	90° right	White	Black	Plastic	Plastic	45-2828.1C90.001	214
	90° right	Red	Silver	Metal	Metal	45-2828.2C20.001	214
	90° right	Amber	Silver	Metal	Metal	45-2828.2C30.001	214
	90° right	Green	Silver	Metal	Metal	45-2828.2C50.001	214
	90° right	White	Silver	Metal	Metal	45-2828.2C90.001	214
Rest - Momentary	45° right	Red	Black	Plastic	Plastic	45-2844.1C20.006	215
	45° right	White	Black	Plastic	Plastic	45-2844.1C90.006	215
	45° right	White	Silver	Metal	Metal	45-2844.2C90.006	215


45 Raised design

Wiring diagrams




Selector switch 2 positions long lever, IP66, IP67, IP69K


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- External diameter of the long lever 44.8 mm
- Mounting depth, incl. front plate, see chapter drawings




Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest - Maintained	90° right	Red	Black	Plastic	Plastic	45-2828.1D20.001	214
	90° right	White	Black	Plastic	Plastic	45-2828.1D90.001	214
	90° right	Red	Silver	Metal	Metal	45-2828.2D20.001	214
	90° right	Green	Silver	Metal	Metal	45-2828.2D50.001	214
	90° right	Blue	Silver	Metal	Metal	45-2828.2D60.001	214
	90° right	White	Silver	Metal	Metal	45-2828.2D90.001	214
Rest - Momentary	45° right	Green	Silver	Metal	Metal	45-2844.2D50.006	215
	45° right	White	Silver	Metal	Metal	45-2844.2D90.006	215

45 Raised design

Wiring diagrams



Follow us.
We are on YouTube!
EAO ermöglicht. Seit 1947.



[Come take a look at our YouTube profile today!](https://www.youtube.com/user/eaoswitches) Be sure to give us a follow so that you can fully interact with us.

<https://www.youtube.com/user/eaoswitches>


www.eao.com

eao ■


Your Expert Partner for Human Machine Interfaces

Selector switch 2 positions round lever, IP66, IP67, IP69K


Equipment consisting of (schematic overview)




Actuator



Holder



Switching element



Illumination element


Page 65

Page 67

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information


- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest - Maintained	90° right	Red	Black	Plastic	Plastic	45-2828.1E20.001	214
	90° right	White	Black	Plastic	Plastic	45-2828.1E90.001	214

Wiring diagrams




45 Raised design

Selector switch 3 positions short lever, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- External diameter of the short lever 32.3 mm
- Mounting depth, incl. front plate, see chapter drawings



Mounting cut-outs [mm]

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67




Illumination element

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.




Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary - Rest - Momentary	45° left / 45° right	Red	Black	Plastic	Plastic	45-280S.1C20.003	217
	45° left / 45° right	Yellow	Black	Plastic	Plastic	45-280S.1C40.003	217
	45° left / 45° right	Blue	Black	Plastic	Plastic	45-280S.1C60.003	217
	45° left / 45° right	White	Black	Plastic	Plastic	45-280S.1C90.003	217
	45° left / 45° right	Red	Silver	Metal	Metal	45-280S.2C20.003	217
	45° left / 45° right	Amber	Silver	Metal	Metal	45-280S.2C30.003	217
	45° left / 45° right	Yellow	Silver	Metal	Metal	45-280S.2C40.003	217
	45° left / 45° right	Green	Silver	Metal	Metal	45-280S.2C50.003	217
	45° left / 45° right	Blue	Silver	Metal	Metal	45-280S.2C60.003	217
	45° left / 45° right	White	Silver	Metal	Metal	45-280S.2C90.003	217
	45° left / 45° right	Red	Black	Plastic	Plastic	45-280X.1C20.003	219
Momentary - Rest - Maintained	45° left / 45° right	Yellow	Black	Plastic	Plastic	45-280X.1C40.003	219
	45° left / 45° right	Green	Black	Plastic	Plastic	45-280X.1C50.003	219
	45° left / 45° right	Blue	Black	Plastic	Plastic	45-280X.1C60.003	219
	45° left / 45° right	White	Black	Plastic	Plastic	45-280X.1C90.003	219
	45° left / 45° right	White	Silver	Metal	Metal	45-280X.2C90.003	219

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary - Rest - Maintained	45° left / 45° right	White	Sand grey	Metal	Plastic	45-280X.3C90.003	219
Maintained - Rest - Momentary	45° left / 45° right	Red	Black	Plastic	Plastic	45-2816.1C20.003	218
	45° left / 45° right	Yellow	Black	Plastic	Plastic	45-2816.1C40.003	218
	45° left / 45° right	Green	Black	Plastic	Plastic	45-2816.1C50.003	218
	45° left / 45° right	Blue	Black	Plastic	Plastic	45-2816.1C60.003	218
	45° left / 45° right	White	Black	Plastic	Plastic	45-2816.1C90.003	218
	45° left / 45° right	Red	Silver	Metal	Metal	45-2816.2C20.003	218
	45° left / 45° right	White	Silver	Metal	Metal	45-2816.2C90.003	218
Maintained - Rest - Maintained	45° left / 45° right	Red	Black	Plastic	Plastic	45-2819.1C20.003	216
	45° left / 45° right	Yellow	Black	Plastic	Plastic	45-2819.1C40.003	216
	45° left / 45° right	Green	Black	Plastic	Plastic	45-2819.1C50.003	216
	45° left / 45° right	Blue	Black	Plastic	Plastic	45-2819.1C60.003	216
	45° left / 45° right	White	Black	Plastic	Plastic	45-2819.1C90.003	216
	45° left / 45° right	Red	Silver	Metal	Metal	45-2819.2C20.003	216
	45° left / 45° right	Yellow	Silver	Metal	Metal	45-2819.2C40.003	216
	45° left / 45° right	Green	Silver	Metal	Metal	45-2819.2C50.003	216
	45° left / 45° right	White	Silver	Metal	Metal	45-2819.2C90.003	216

Wiring diagrams




45 Raised design

Selector switch 3 positions long lever, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- External diameter of the long lever 44.8 mm
- Mounting depth, incl. front plate, see chapter drawings



Mounting cut-outs [mm]

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67




Illumination element

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.




Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary - Rest - Momentary	45° left / 45° right	Red	Silver	Metal	Metal	45-280S.2D20.003	217
	45° left / 45° right	Green	Silver	Metal	Metal	45-280S.2D50.003	217
	45° left / 45° right	White	Silver	Metal	Metal	45-280S.2D90.003	217
Momentary - Rest - Maintained	45° left / 45° right	Red	Silver	Metal	Metal	45-280X.2D20.003	219
	45° left / 45° right	White	Silver	Metal	Metal	45-280X.2D90.003	219
Maintained - Rest - Momentary	45° left / 45° right	Red	Silver	Metal	Metal	45-2816.2D20.003	218
	45° left / 45° right	White	Silver	Metal	Metal	45-2816.2D90.003	218
Maintained - Rest - Maintained	45° left / 45° right	Red	Silver	Metal	Metal	45-2819.2D20.003	216
	45° left / 45° right	Green	Silver	Metal	Metal	45-2819.2D50.003	216
	45° left / 45° right	White	Silver	Metal	Metal	45-2819.2D90.003	216

Wiring diagrams



Wiring diagrams



Innovative and comprehensive.
EAO's new Series 45.

Modular, aesthetic and robust for every conceivable HMI function of machine operating.

- Comprehensive and modular Series
- Rugged in use (up to IP69K)
- Easy to assemble and use
- Modern design with many options
- Value added services
- Long service life (up to 10 million switching cycles, depending on function)

www.eao.com

eao ■


Your Expert Partner for Human Machine Interfaces

45 Raised design

Selector switch 4 positions round lever, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- Use only with holder for 4 elements
- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 67

Page 67


Each Part Number listed below includes all the black components shown in the 3D-drawing.
To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Maintained - Maintained - Maintained - Maintained	4 x 90°	White	Black	Plastic	Plastic	45-2845.1E90.002	220
	4 x 90°	White	Silver	Metal	Metal	45-2845.2E90.002	220


Wiring diagrams



Wiring diagram 220

Keylock switch 2 positions, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 65

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- The standard lock: RONIS, T254
- Mounting depth, incl. front plate, see chapter drawings




Actuator, Front dimension Ø 29,5 mm


Switching action	Switching angle	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Rest (a) - Maintained (a)	90° right	Black	Plastic	Plastic	45-290H.1000.111	79
	90° right	Silver	Metal	Metal	45-290H.2000.111	79
Rest (a) - Maintained	90° right	Black	Plastic	Plastic	45-290J.1000.111	79
	90° right	Silver	Metal	Metal	45-290J.2000.111	79
Rest (a) - Momentary	45° right	Black	Plastic	Plastic	45-290K.1000.116	78
	45° right	Silver	Metal	Metal	45-290K.2000.116	78
Rest - Maintained (a)	90° right	Black	Plastic	Plastic	45-2925.1000.111	79
	90° right	Silver	Metal	Metal	45-2925.2000.111	79

a = Key remove

Wiring diagrams



Wiring diagram 78




Wiring diagram 79

45 Raised design

Keylock switch 3 positions, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]


General information

- The standard lock: RONIS, T254
- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]


Equipment consisting of (schematic overview)



Actuator



Holder



Switching element

Page 65

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.






Actuator, Front dimension Ø 29,5 mm

Switching action	Switching angle	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Maintained (a) - Rest - Momentary	45° left / 45° right	Black	Plastic	Plastic	45-290A.1000.113	81
	45° left / 45° right	Silver	Metal	Metal	45-290A.2000.113	81
Maintained (a) - Rest - Maintained (a)	45° left / 45° right	Silver	Metal	Metal	45-290C.2000.113	83
Maintained (a) - Rest - Maintained	45° left / 45° right	Silver	Metal	Metal	45-290D.2000.113	83
Maintained (a) - Rest (a) - Maintained (a)	45° left / 45° right	Black	Plastic	Plastic	45-290F.1000.113	83
	45° left / 45° right	Silver	Metal	Metal	45-290F.2000.113	83
Maintained (a) - Rest (a) - Maintained	45° left / 45° right	Black	Plastic	Plastic	45-290G.1000.113	83
	45° left / 45° right	Silver	Metal	Metal	45-290G.2000.113	83
Momentary - Rest (a) - Momentary	45° left / 45° right	Black	Plastic	Plastic	45-290Z.1000.113	82
	45° left / 45° right	Silver	Metal	Metal	45-290Z.2000.113	82
Maintained - Rest - Maintained (a)	45° left / 45° right	Black	Plastic	Plastic	45-2917.1000.113	83
	45° left / 45° right	Silver	Metal	Metal	45-2917.2000.113	83
Maintained - Rest (a) - Momentary	45° left / 45° right	Black	Plastic	Plastic	45-2922.1000.113	81
	45° left / 45° right	Silver	Metal	Metal	45-2922.2000.113	81
Maintained - Rest (a) - Maintained	45° left / 45° right	Black	Plastic	Plastic	45-2924.1000.113	83
	45° left / 45° right	Silver	Metal	Metal	45-2924.2000.113	83

a = Key remove

Wiring diagrams

		
Wiring diagram 81	Wiring diagram 82	Wiring diagram 83


01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Raised design

ID keylock switch, IP65




Product can differ from the current configuration.



Dimensions [mm]


General information

- Mounting depth, incl. front plate, see chapter drawings



Mounting cut-outs [mm]

Equipment consisting of (schematic overview)

	ID key	Page 79
	Actuator	
	Holder	Page 65
	Electronic module	Page 78

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 29,5 mm

Switching action	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Maintained - Maintained - Maintained - Maintained	Black	Plastic	Plastic	45-2S00.1001.404	213


Wiring diagrams



Wiring diagram 213


Toggle stick, IP65, IP67

Equipment consisting of (schematic overview)




Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Mounting cut-outs [mm]



Product can differ from the current configuration.

General information

- Use only with holder for 4 elements
- Mounting depth, incl. front plate, see chapter drawings
- Lockable only in center position





Actuator, Front dimension Ø 29,5 mm

Switching action	Product attributes	Housing material	Front bezel colour	Front bezel material	Part No.	Wiring diagram
Momentary	2 positions (L-R)	Plastic	Black	Plastic	45-2F0T.1010.000	223
	2 positions (L-R)	Metal	Silver	Metal	45-2F0T.2010.000	223
	4 positions	Plastic	Black	Plastic	45-2F0V.1010.000	225
	4 positions	Metal	Silver	Metal	45-2F0V.2010.000	225
	2 positions (L-R), lockable	Plastic	Black	Plastic	45-2F13.1010.000	223
	2 positions (L-R), lockable	Metal	Silver	Metal	45-2F13.2010.000	223
	4 positions, lockable	Plastic	Black	Plastic	45-2F14.1010.000	225
	4 positions, lockable	Metal	Silver	Metal	45-2F14.2010.000	225
	2 positions (U-D)	Metal	Silver	Metal	45-2F38.2010.000	221
	2 positions (U-D), lockable	Plastic	Black	Plastic	45-2F40.1010.000	221
	2 positions (U-D), lockable	Metal	Silver	Metal	45-2F40.2010.000	221

45 Raised design

Wiring diagrams



Toggle switch, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 65

Page 67


Each Part Number listed below includes all the black components shown in the 3D-drawing.
To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 29,5 mm

Switching action	Lever colour	Front bezel colour	Front bezel material	Housing material	Part No.	Wiring diagram
Momentary	Black	Black	Plastic	Plastic	45-2N39.1010.000	72
	Black	Silver	Metal	Metal	45-2N39.2010.000	72
Maintained	Black	Black	Plastic	Plastic	45-2N42.1010.000	73
	Black	Silver	Metal	Metal	45-2N42.2010.000	73

Wiring diagrams



Wiring diagram 72




Wiring diagram 73

45 Raised design

Indicator full-face illumination, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]

Equipment consisting of (schematic overview)




Actuator



Holder

Page 65



Illumination element

Page 74


Each Part Number listed below includes all the black components shown in the 3D-drawing.
To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 30 mm

Lens cap colour	Housing material	Part No.	Wiring diagram
Red	Plastic	45-2T00.10E0.000	190
Amber	Plastic	45-2T00.10F0.000	190
Yellow	Plastic	45-2T00.10G0.000	190
Green	Plastic	45-2T00.10H0.000	190
Blue	Plastic	45-2T00.10J0.000	190
Colourless	Plastic	45-2T00.10K0.000	190
White	Plastic	45-2T00.10N0.000	190
Red	Metal	45-2T00.20E0.000	190
Amber	Metal	45-2T00.20F0.000	190
Yellow	Metal	45-2T00.20G0.000	190
Green	Metal	45-2T00.20H0.000	190
Blue	Metal	45-2T00.20J0.000	190
Colourless	Metal	45-2T00.20K0.000	190
White	Metal	45-2T00.20N0.000	190

Wiring diagrams




Indicator front illumination, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Illumination element

Page 65

Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information


- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 29,5 mm

Front bezel colour	Front bezel material	Lens cap colour	Housing material	Part No.	Wiring diagram
Black	Plastic	Red	Plastic	45-2T07.10E0.000	190
	Plastic	Yellow	Plastic	45-2T07.10G0.000	190
	Plastic	Green	Plastic	45-2T07.10H0.000	190
	Plastic	Blue	Plastic	45-2T07.10J0.000	190
	Plastic	White	Plastic	45-2T07.10K0.000	190

Wiring diagrams




45 Raised design

Buzzer, IP40




Product can differ from the current configuration.



Dimensions [mm]


General information

- Mounting depth, incl. front plate, see chapter drawings




Mounting cut-outs [mm]

Equipment consisting of (schematic overview)



Actuator



Holder

Page 65

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Actuator, Front dimension Ø 29,5 mm

Operating voltage	Housing material	Part No.	Wiring diagram
24 V AC/DC	Plastic	45-2H00.1016.000	199
110 V AC	Plastic	45-2H00.1017.000	199
230 V AC	Plastic	45-2H00.1018.000	199


Wiring diagrams



Wiring diagram 199

Potentiometer, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.


Page 65



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information


- Power 0.5 W
- Mounting depth, incl. front plate, see chapter drawings



Actuator, Front dimension Ø 30 mm



Front bezel colour	Front bezel material	Housing material	Resistance	Resistance kind of	Part No.	Wiring diagram	Component Layout
Black	Plastic	Plastic	100 kΩ	linear, row_E3	45-2P01.1E10.000	104	22
	Plastic	Plastic	10 kΩ	linear, row_E3	45-2P02.1E10.000	104	22
	Plastic	Plastic	1 kΩ	linear, row_E3	45-2P03.1E10.000	104	22
	Plastic	Plastic	4.7 kΩ	linear, row_E3	45-2P04.1E10.000	104	22

Wiring diagrams



45 Raised design

Component layouts



User-friendly and robust. *EAO Series 45 Potentiometers.*

Ideal for harsh industrial environments – thanks to IP69K protection and the long service life.

- IP69K protection
- Long service life
- Easy mounting
- Rotational range of 280°
- Resistance from 1 k to 470 kΩ


eao ■

www.eao.com/45


Your Expert Partner for Human Machine Interfaces

Stop switch, IP66, IP67, IP69K


Equipment consisting of (schematic overview)



Actuator



Holder




Switching element

Page 65

Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.


To obtain a complete unit, please select the red components from the pages shown.



Dimensions [mm]



Product can differ from the current configuration.



Mounting cut-outs [mm]

General information

- Mounting depth, incl. front plate, see chapter drawings



Actuator

Product attributes	Lens colour	Front bezel colour	Front bezel material	Dimensions	Housing material	Part No.	Wiring diagram
Twist to unlock clockwise	Black	Black	Plastic	Ø 40 mm	Plastic	45-2736.1910.000	76
	Blue	Black	Plastic	Ø 40 mm	Plastic	45-2736.1960.000	76
	Black	Silver	Metal	Ø 40 mm	Metal	45-2C36.2910.000	76
Twist to release, can be latched after pressing by rotating to the right	Black	Black	Plastic	Ø 29 mm	Plastic	45-2729.1010.000	76
	Red	Black	Plastic	Ø 29 mm	Plastic	45-2729.1020.000	76

Wiring diagrams




Wiring diagram 76

45 Raised design

Emergency stop switch foolproof, EN IEC 60947-5-5, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

Equipment consisting of (schematic overview)




Actuator



Holder

Page 65



Switching element


Page 67

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- The standard lock: RONIS, T254
- Mounting depth, incl. front plate, see chapter drawings
- Application as per DIN EN ISO 13850



Mounting cut-outs [mm]




Actuator

Product attributes	Lens colour	Front bezel colour	Front bezel material	Dimensions	Housing colour	Housing material	Part No.	Wiring diagram
Twist to unlock clockwise	Red	Black	Plastic	Ø 40 mm	Yellow	Plastic	45-2C35.1920.110	364
	Red	Silver	Metal	Ø 40 mm	Yellow	Metal	45-2C35.2920.110	364
Pull release	Red	Black	Plastic	Ø 40 mm	Yellow	Plastic	45-2C37.1920.000	76
	Red	Silver	Metal	Ø 40 mm	Yellow	Metal	45-2C37.2920.000	76
Twist to unlock clockwise	Red	Black	Plastic	Ø 34 mm	Yellow	Plastic	45-2C36.1820.000	76
	Red	Black	Plastic	Ø 40 mm	Yellow	Plastic	45-2C36.1920.000	76
	Red	Black	Plastic	Ø 60 mm	Yellow	Plastic	45-2C36.1A20.000	76

Product attributes	Lens colour	Front bezel colour	Front bezel material	Dimensions	Housing colour	Housing material	Part No.	Wiring diagram
Twist to unlock clockwise	Red	Silver	Metal	Ø 34 mm	Silver	Metal	45-2C36.2820.000	76
	Red	Silver	Metal	Ø 40 mm	Silver	Metal	45-2C36.2920.000	76

Wiring diagrams

	
Wiring diagram 76	Wiring diagram 364



Innovative, intuitive and aesthetic.
EAO Series 45 ID keylock switches.

Ideal for implementing electronic access control systems in industrial environments.

- Intuitive and ease of use
- Authentication of up to 4 users or groups
- Robust in use
- Modular construction and quick mounting
- Aesthetic design, matching Series 45
- Innovative RFID technology

www.eao.com/45

eao ■


Your Expert Partner for Human Machine Interfaces

45 Raised design

Illuminated emergency stop switch, foolproof, EN IEC 60947-5-5, IP66, IP67, IP69K




Product can differ from the current configuration.



Dimensions [mm]

Equipment consisting of (schematic overview)




Actuator




Holder

Page 65



Switching element

Page 67



Illumination element


Page 74

Each Part Number listed below includes all the black components shown in the 3D-drawing.

To obtain a complete unit, please select the red components from the pages shown.

General information

- The standard lock: RONIS, T254
- Mounting depth, incl. front plate, see chapter drawings
- Application as per DIN EN ISO 13850




Mounting cut-outs [mm]



Actuator

Product attributes	Lens colour	Front bezel colour	Front bezel material	Dimensions	Housing colour	Housing material	Part No.	Wiring diagram
Twist to unlock clockwise	Red	Black	Plastic	Ø 34 mm	Yellow	Plastic	45-2D36.1820.000	205
	Red	Black	Plastic	Ø 40 mm	Yellow	Plastic	45-2D36.1920.000	205
	Red	Black	Plastic	Ø 60 mm	Yellow	Plastic	45-2D36.1A20.000	205
	Red	Silver	Metal	Ø 34 mm	Silver	Metal	45-2D36.2820.000	205
	Red	Silver	Metal	Ø 40 mm	Silver	Metal	45-2D36.2920.000	205
	Red	Silver	Metal	Ø 60 mm	Silver	Metal	45-2D36.2A20.000	205

Wiring diagrams



Rugged and reliable. *EAO Series 45 mushroom-head pushbuttons.*

Reliable switching for harsh industrial environments – thanks to a large operating area and IP69K.

- Large, distinctive operating area
- Easy operation – even with gloves
- Many configuration options
- Optional illumination
- Long service life (up to 10 million switching cycles)
- Rugged in use (IP69K)

www.eao.com/45

eao ■


Your Expert Partner for Human Machine Interfaces

45 Raised design



Lens plastic round encreased

Lens material	Lens colour	Lens optics	Lens shape	Lens illumination	Dimensions	Part No.
Plastic	Colourless	transparent	flush	illuminative	Ø 23.7 mm	45-552.0K00




Dimensions [mm]



Lens plastic round flat

Lens material	Lens colour	Lens optics	Lens shape	Lens illumination	Dimensions	Part No.
Plastic	Red	opaque	flush	non illuminative	Ø 23.7 mm	45-553.0200
	Yellow	opaque	flush	non illuminative	Ø 23.7 mm	45-553.0400
	Green	opaque	flush	non illuminative	Ø 23.7 mm	45-553.0500
	Blue	opaque	flush	non illuminative	Ø 23.7 mm	45-553.0600
	White	opaque	flush	non illuminative	Ø 23.7 mm	45-553.0900
	Red	transparent	flush	illuminative	Ø 23.7 mm	45-553.0E00
	Amber	transparent	flush	illuminative	Ø 23.7 mm	45-553.0F00
	Yellow	transparent	flush	illuminative	Ø 23.7 mm	45-553.0G00
	Green	transparent	flush	illuminative	Ø 23.7 mm	45-553.0H00
	Blue	transparent	flush	illuminative	Ø 23.7 mm	45-553.0J00
	White	transparent	flush	illuminative	Ø 23.7 mm	45-553.0K00
	Colourless	transparent	flush	illuminative	Ø 23.7 mm	45-553.0N00




Dimensions [mm]



Single frame

Product attributes	Material	Colour	Dimensions	Part No.
For design square	Plastic	Black	29,8 mm x 29,8 mm	45-558.0000




Dimensions [mm]




Holder for 3 elements

Material	Part No.	Component Layout
Plastic	45-2300.1000.000	23
Metal	45-2300.2000.000	23
Metal/plastic	45-2300.3000.000	23



Dimensions [mm]

Component layouts




45 Components




Holder for 4 elements

Product attributes	Material	Part No.	Component Layout
for selector switch 4 positions and toggle stick	Plastic	45-2400.1000.000	24
	Metal	45-2400.2000.000	24



Dimensions [mm]

Component layouts




Component layout 24



Slow-make switching element front mounting with screw terminal

Switching current	Contacts	Contact material	Terminal	Part No.	Wiring diagram
10 A	1 NO	Silver	Screw terminal	45-311.1Z10	227
	1 NC	Silver	Screw terminal	45-312.1Z10	228
	2 NO	Silver	Screw terminal	45-313.1Z10	231
	2 NC	Silver	Screw terminal	45-314.1Z10	234
	1 NC / 1 NO	Silver	Screw terminal	45-315.1Z10	235
	1 NO	Gold	Screw terminal	45-311.1X10	227
	1 NC	Gold	Screw terminal	45-312.1X10	228
	1 NC / 1 FS	Gold	Screw terminal	45-316.1X10	233


Contacts: NC = Normally closed, NO = Normally open



Dimensions [mm]
A = Screw terminal
for Part No. 45-311.1Z10, 45-311.1X10


Dimensions [mm]
A = Screw terminal
for Part No. 45-312.1Z10, 45-312.1X10

Dimensions [mm]
A = Screw terminal
for Part No. 45-313.1Z10



Dimensions [mm]
A = Screw terminal
for Part No. 45-314.1Z10

Dimensions [mm]
A = Screw terminal
for Part No. 45-315.1Z10



Dimensions [mm]
A = Screw terminal
for Part No. 45-316.1X10

45 Components

Wiring diagrams

.3 NO .4 NO Wiring diagram 227	.1 NC .2 NC Wiring diagram 228	.3 NO .3 NO .4 NO .4 NO Wiring diagram 231	.7 NO .5 NC .8 NO .6 NC Wiring diagram 233	.1 NC .1 NC .2 NC .2 NC Wiring diagram 234	.3 NO .1 NC .4 NO .2 NC Wiring diagram 235
---	---	---	---	---	---



Innovative and comprehensive.
EAO's new Series 45.

Modular, aesthetic and robust for every conceivable HMI function of machine operating.

- Comprehensive and modular Series
- Rugged in use (up to IP69K)
- Easy to assemble and use
- Modern design with many options
- Value added services
- Long service life (up to 10 million switching cycles, depending on function)

eao ■

www.eao.com


Your Expert Partner for Human Machine Interfaces




Slow-make switching element front mounting with spring-type terminal

Switching current	Contacts	Contact material	Terminal	Part No.	Wiring diagram
10 A	1 NO	Silver	Spring-type terminal	45-311.1Z40	227
	1 NC	Silver	Spring-type terminal	45-312.1Z40	228
	2 NO	Silver	Spring-type terminal	45-313.1Z40	231
	2 NC	Silver	Spring-type terminal	45-314.1Z40	234
	1 NC / 1 NO	Silver	Spring-type terminal	45-315.1Z40	235
	1 NC / 1 FS	Silver	Spring-type terminal	45-316.1Z40	233
	1 NC	Silver	Spring-type terminal	45-317.1Z40	232
	1 NO	Gold	Spring-type terminal	45-311.1X40	227
	1 NC	Gold	Spring-type terminal	45-312.1X40	228
	2 NO	Gold	Spring-type terminal	45-313.1X40	231
	2 NC	Gold	Spring-type terminal	45-314.1X40	234
	1 NC / 1 NO	Gold	Spring-type terminal	45-315.1X40	235
	1 NC / 1 FS	Gold	Spring-type terminal	45-316.1X40	233


Contacts: NC = Normally closed, NO = Normally open




Dimensions [mm]
B = Spring-type terminal
for Part No. 45-311.1Z40, 45-311.1X40




Dimensions [mm]
B = Spring-type terminal
for Part No. 45-312.1Z40, 45-312.1X40




Dimensions [mm]
B = Spring-type terminal
for Part No. 45-313.1Z40, 45-313.1X40




Dimensions [mm]
B = Spring-type terminal
for Part No. 45-314.1Z40, 45-314.1X40



Dimensions [mm]
B = Spring-type terminal
for Part No. 45-315.1Z40, 45-315.1X40



Dimensions [mm]
B = Spring-type terminal
for Part No. 45-316.1Z40, 45-316.1X40



Dimensions [mm]
B = Spring-type terminal
for Part No. 45-317.1Z40

Wiring diagrams

Wiring diagram 227	Wiring diagram 228	Wiring diagram 231	Wiring diagram 232	Wiring diagram 233	Wiring diagram 234	Wiring diagram 235




Slow-make switching element base mounting with screw terminal

Switching current	Contacts	Contact material	Terminal	Part No.	Wiring diagram
10 A	1 NO	Silver	Screw terminal	45-311.2Z10	227
	1 NC	Silver	Screw terminal	45-312.2Z10	228

Contacts: NC = Normally closed, NO = Normally open

General information

- Switching element base mounting can used only with enclosure



Dimensions [mm]
A = Screw terminal
for Part No. 45-311.2Z10

Dimensions [mm]
A = Screw terminal
for Part No. 45-312.2Z10

Wiring diagrams

Wiring diagram 227	Wiring diagram 228




Slow-make switching element base mounting with spring-type terminal

Switching current	Contacts	Contact material	Terminal	Part No.	Wiring diagram
10 A	1 NO	Silver	Spring-type terminal	45-311.2Z40	227
	1 NC	Silver	Spring-type terminal	45-312.2Z40	228


Contacts: NC = Normally closed, NO = Normally open

General information

- Switching element base mounting can used only with enclosure



Wiring diagrams




45 Components




Illumination element front mounting with screw terminal

Operating voltage	Lumi. Intensity	Illuminative colour	Part No.	Wiring diagram
6 - 24 V AC/DC	450 - 1120 mcd	Red	45-320.1E11	229
	450 - 1120 mcd	Amber	45-320.1F11	229
	900 - 1400 mcd	Yellow	45-320.1G11	229
	900 - 1400 mcd	Green	45-320.1H11	229
	280 - 710 mcd	Blue	45-320.1J11	229
	900 - 1400 mcd	White	45-320.1N11	229
24 - 240 V AC/DC	450 - 1120 mcd	Red	45-320.1E12	229
	450 - 1120 mcd	Amber	45-320.1F12	229
	900 - 1400 mcd	Yellow	45-320.1G12	229
	900 - 1400 mcd	Green	45-320.1H12	229
	280 - 710 mcd	Blue	45-320.1J12	229
	900 - 1400 mcd	White	45-320.1N12	229
24 V AC/DC	450 - 1120 mcd	Red	45-320.1E16	229
	450 - 1120 mcd	Amber	45-320.1F16	229
	900 - 1400 mcd	Yellow	45-320.1G16	229
	900 - 1400 mcd	Green	45-320.1H16	229
	280 - 710 mcd	Blue	45-320.1J16	229
	900 - 1400 mcd	White	45-320.1N16	229
110 V AC	450 - 1120 mcd	Red	45-320.1E17	229
	900 - 1400 mcd	Green	45-320.1H17	229
	900 - 1400 mcd	White	45-320.1N17	229
230 V AC	450 - 1120 mcd	Red	45-320.1E18	229
	450 - 1120 mcd	Amber	45-320.1F18	229
	900 - 1400 mcd	Yellow	45-320.1G18	229
	900 - 1400 mcd	Green	45-320.1H18	229
	280 - 710 mcd	Blue	45-320.1J18	229
	900 - 1400 mcd	White	45-320.1N18	229



Dimensions [mm]

Wiring diagrams




01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96

45 Components




Illumination element front mounting with spring-type terminal

Operating voltage	Lumi. Intensity	Illuminative colour	Part No.	Wiring diagram
6 - 24 V AC/DC	450 - 1120 mcd	Red	45-320.1E41	229
	450 - 1120 mcd	Amber	45-320.1F41	229
	900 - 1400 mcd	Yellow	45-320.1G41	229
	900 - 1400 mcd	Green	45-320.1H41	229
	280 - 710 mcd	Blue	45-320.1J41	229
	900 - 1400 mcd	White	45-320.1N41	229
24 - 240 V AC/DC	450 - 1120 mcd	Red	45-320.1E42	229
	450 - 1120 mcd	Amber	45-320.1F42	229
	900 - 1400 mcd	Yellow	45-320.1G42	229
	900 - 1400 mcd	Green	45-320.1H42	229
	280 - 710 mcd	Blue	45-320.1J42	229
	900 - 1400 mcd	White	45-320.1N42	229
24 V AC/DC	450 - 1120 mcd	Red	45-320.1E46	229
	450 - 1120 mcd	Amber	45-320.1F46	229
	900 - 1400 mcd	Yellow	45-320.1G46	229
	900 - 1400 mcd	Green	45-320.1H46	229
	280 - 710 mcd	Blue	45-320.1J46	229
	900 - 1400 mcd	White	45-320.1N46	229
110 V AC	450 - 1120 mcd	Red	45-320.1E47	229
230 V AC	450 - 1120 mcd	Red	45-320.1E48	229
	900 - 1400 mcd	Yellow	45-320.1G48	229
	900 - 1400 mcd	Green	45-320.1H48	229
	280 - 710 mcd	Blue	45-320.1J48	229
	900 - 1400 mcd	White	45-320.1N48	229



Dimensions [mm]

Wiring diagrams






Illumination element base mounting with screw terminal

Operating voltage	Illuminative colour	Part No.	Wiring diagram
6 - 24 V AC/DC	Red	45-320.2E11	229
	Amber	45-320.2F11	229
	Yellow	45-320.2G11	229
	Blue	45-320.2J11	229
	White	45-320.2N11	229
24 - 240 V AC/DC	Red	45-320.2E12	229
	Yellow	45-320.2G12	229
	Green	45-320.2H12	229
	Blue	45-320.2J12	229
	White	45-320.2N12	229
24 V AC/DC	Red	45-320.2E16	229
	Amber	45-320.2F16	229
	Yellow	45-320.2G16	229
	Green	45-320.2H16	229
	Blue	45-320.2J16	229
230 V AC	White	45-320.2N16	229
	Yellow	45-320.2G18	229
	Green	45-320.2H18	229
	Blue	45-320.2J18	229
	White	45-320.2N18	229


Additional information

- Illumination element base mounting can used only with enclosure



Dimensions [mm]

Wiring diagrams






Illumination element base mounting with spring-type terminal

Operating voltage	Lumi. Intensity	Illuminative colour	Part No.	Wiring diagram
6 - 24 V AC/DC	900 - 1400 mcd	Green	45-320.2H41	229
	280 - 710 mcd	Blue	45-320.2J41	229
	900 - 1400 mcd	White	45-320.2N41	229
24 - 240 V AC/DC	450 - 1120 mcd	Red	45-320.2E42	229
	900 - 1400 mcd	Green	45-320.2H42	229
	900 - 1400 mcd	White	45-320.2N42	229
24 V AC/DC	900 - 1400 mcd	Yellow	45-320.2G46	229
	900 - 1400 mcd	White	45-320.2N46	229
230 V AC	900 - 1400 mcd	White	45-320.2N48	229


Additional information

- Illumination element base mounting can used only with enclosure



Dimensions [mm]

Wiring diagrams




Dimensions [mm]




Illumination element PCB mounting

Operating voltage	Illuminative colour	Part No.	Wiring diagram
5 V AC/DC	Green	45-320.3H60	229
	White	45-320.3N60	229



Dimensions [mm]

Wiring diagrams




45 Components




Electronic module

Product attributes	Operating voltage	Terminal	Part No.	Wiring diagram	Component Layout
Front mounting	24 V DC	Screw terminal	45-36F.1114	213	26




Dimensions [mm]

Wiring diagrams



Wiring diagram 213

Component layouts



A = Device



ID-Key


Product attributes	Colour	Part No.
Design of the RFID coding: Step 1	Green	45-50T.0500
Design of the RFID coding: Step 1+2	Yellow	45-50V.0400
Design of the RFID coding: Step 1+2+3	Red	45-50W.0200
Design of the RFID coding: Step 1+2+3+4	Blue	45-574.0600

Front side



Cover for locking device

Product attributes	Material	Colour	Optics	IP Protection	Part No.
For pushbuttons, selector switches with round or short lever	Metal / plastic	Colourless	transparent	IP66, IP67, IP69K	45-529.2100



Dimensions [mm]

Follow us.

We are on LinkedIn!

EAO creates possibilities. Since 1947.



[Come take a look at our LinkedIn profile today!](#) Be sure to give us a follow so that you can fully interact with us.

<https://www.linkedin.com/company/eao/>


www.eao.com



Your Expert Partner for Human Machine Interfaces

**Locking device**


Product attributes	Dimension	Material	Colour	Part No.
For mushroom-head pushbutton Ø 30 mm or Ø 40 mm	47 mm x 25.1 mm x 43.1 mm	Metal	Silver	45-530.2100
For selector switch in position left	47 mm x 21.1 mm x 47.1 mm	Metal	Silver	45-534.2100
For selector switch in position center	47 mm x 21.1 mm x 47.1 mm	Metal	Silver	45-533.2100
For selector switch in position right	47 mm x 21.1 mm x 47.1 mm	Metal	Silver	45-536.2100



Dimensions [mm]
for Part No. 45-532.2100, 45-530.2100

Dimensions [mm]
for Part No. 45-534.2100

Dimensions [mm]
for Part No. 45-533.2100




Dimensions [mm]
for Part No. 45-536.2100

45 Accessories




Legend plate

Product attributes	Dimensions	Material	Colour	Mounting type	Part No.
Not to use with emergency stop switch	27 mm x 12.5 mm	Plastic	Black	adhesive	45-573.1102
	27 mm x 12.5 mm	Plastic	Red	adhesive	45-573.1202
	27 mm x 12.5 mm	Plastic	Silver	adhesive	45-573.1A02
	27 mm x 17.5 mm	Plastic	Black	adhesive	45-573.1103
	27 mm x 17.5 mm	Plastic	Silver	adhesive	45-573.1A03
	27 mm x 27 mm	Plastic	Black	adhesive	45-573.1105
	27 mm x 27 mm	Plastic	Silver	adhesive	45-573.1A05
	22 mm x 22 mm	Plastic	Silver	adhesive	45-573.1A04
	22 mm x 22 mm	Plastic	Black	adhesive	45-573.1104



Dimensions [mm]
for Part No. 45-573.1102, 45-573.1202, 45-573.1A02 for Part No. 45-573.1103, 45-573.1A03

Dimensions [mm]
for Part No. 45-573.1105, 45-573.1A05



Dimensions [mm]
for Part No. 45-573.1A04, 45-573.1104



Emergency stop legend

Dimensions	Material	Colour	Mounting type	Marking	Part No.
Ø 45 mm	Plastic	Yellow		without marking	45-50K.1407
Ø 75 mm	Plastic	Yellow		without marking	45-50K.1408
	Plastic	Yellow	adhesive	without marking	45-50J.1400
	Plastic	Yellow	adhesive	NOT - HALT	45-50J.140Q
	Plastic	Yellow	adhesive	EMERGENCY STOP	45-50J.140S
	Plastic	Yellow	adhesive	NOT - AUS	45-50J.140P
	Plastic	Yellow	adhesive	ARRET D'URGENCE	45-50J.140T
	Plastic	Yellow	adhesive	EMERGENZA	45-50J.140V
	Plastic	Yellow	adhesive	NODSTOP	45-50J.140W
	Plastic	Yellow	adhesive	紧急停止	45-50J.140X
	Plastic	Yellow	adhesive	NOT-HALT EMERGENCY STOP EMERGENZA EMERGENCIA	45-50J.140Z
112 mm x 38 mm	Plastic	Yellow	adhesive	without marking	45-561.1400
	Plastic	Yellow	adhesive	NOT - AUS	45-561.140P
	Plastic	Yellow	adhesive	without marking, with recess	45-562.1400


Additional information

- Front panel thickness 3 mm max.



Blind plug

Material	Colour	Part No.
Plastic	Black	45-506.1100
Metal	Silver	45-506.2A00



Dimensions [mm]



Spare key

Product attributes	Part No.
2 spare keys	45-522.0900

Additional information


- For standard lock RONIS T254

45 Accessories



Protective cap


Product attributes	Material	Colour	Optics	Part No.
For lens raised above bezel	Silicone	Colourless	transparent	45-544.1K00
For lens flush	Silicone	Colourless	transparent	45-545.1K00
For lens flush	Silicone	Colourless	transparent	45-547.1K00
For lens raised above bezel	Silicone	Colourless	transparent	45-548.1K00
For lens raised above bezel	Silicone	Colourless	transparent	45-542.1K00
For Mushroom-head pushbutton Ø 40 mm	Silicone	Colourless	transparent	45-543.1K00
For lever switch, short lever	Silicone	Colourless	transparent	45-546.1K00
For keylock switch	Silicone	Colourless	transparent	45-50F.1100



Dimensions [mm]
for Part No. 45-544.1K00

Dimensions [mm]
for Part No. 45-545.1K00


Dimensions [mm]
for Part No. 45-547.1K00, 45-548.1K00



Dimensions [mm]
for Part No. 45-547.1K00, 45-548.1K00

Dimensions [mm]
for Part No. 45-542.1K00

Dimensions [mm]
for Part No. 45-543.1K00




Dimensions [mm]
for Part No. 45-546.1K00

Dimensions [mm]
for Part No. 45-50F.1100



Legend support without legend


Product attributes	Material	Colour	Mounting type	Part No.
For legend 27 mm x 12.5 mm	Plastic	Black	For sticking or snapping in place	45-564.1102
	Plastic	Black	For sticking or snapping in place	45-567.1103
For legend 27 mm x 27 mm	Plastic	Black	For sticking or snapping in place	45-569.1105
	Plastic	Black	For sticking or snapping in place	45-570.1105
For legend 27 mm x 12.5 mm	Plastic	Black	For sticking or snapping in place	45-564.1110
For legend 27 mm x 17.5 mm	Plastic	Black	For sticking or snapping in place	45-567.1111
For legend 27 mm x 27 mm	Plastic	Black	For sticking or snapping in place	45-569.1112



Dimensions [mm]
for Part No. 45-564.1102

Dimensions [mm]
for Part No. 45-567.1103


Dimensions [mm]
for Part No. 45-569.1105



Dimensions [mm]
for Part No. 45-570.1105

Dimensions [mm]
for Part No. 45-564.1110

Dimensions [mm]
for Part No. 45-567.1111




Dimensions [mm]
for Part No. 45-569.1112

45 Accessories



Protective cover

Product attributes	Material	Colour	Optics	Part No.
Hinged, with means for sealing	Plastic	Black	opaque	45-555.1100
	Plastic	Colourless	transparent	45-555.1K00




Dimensions [mm]



Protective shroud

Dimensions	Material	Colour	Part No.
Ø 34.8 mm	Plastic	Black	45-50N.1100
Ø 46.4 mm	Metal	Silver	45-50Q.2100
Ø 39.6 mm	Metal	Silver	45-50P.0100



Dimensions [mm]
for Part No. 45-50N.1100

Dimensions [mm]
for Part No. 45-50Q.2100


Dimensions [mm]
for Part No. 45-50P.0100

**E stop protective shroud**

Product attributes	Material	Colour	Part No.
	Plastic	Yellow	45-549.1400
	Plastic	Grey	45-549.1800
	Plastic	Yellow	45-550.1400
For Emergency stop switch Ø 40 mm, for 5 padlocks	Metal	Yellow	45-539.2400
	Metal	Grey	45-539.2800

Additional information

- The protection shroud is not suitable for a proper use of emergency stop. It can obstruct a spontaneous operation of the emergency stop




Dimensions [mm]
for Part No. 45-549.1400, 45-549.1800

Dimensions [mm]
for Part No. 45-550.1400

Dimensions [mm]
for Part No. 45-539.2400, 45-539.2800

**Sun collar**

Product attributes	Material	Colour	Part No.
For pushbutton illuminated	Plastic	Black	45-560.1100



Dimensions [mm]


45 Accessories

Rear side



Legend plate for switching elements

Dimensions	Material	Colour	Mounting type	Part No.
10.5 mm x 9.5 mm	Plastic	White	for snapping in place	45-523.1900




Dimensions [mm]




Test module

Product attributes	Operating voltage	Terminal	Part No.	Wiring diagram
Front mounting	12 - 240 V AC/DC	Screw terminal	45-330.1115	236
Base mounting	12 - 240 V AC/DC	Screw terminal	45-330.2115	236



Dimensions [mm]

Wiring diagrams



01
02
03
04
09
14
17
18
19
22
31
41
45
51
56
57
61
70
71
82
84
92
96



[Come take a look at our YouTube profile today!](https://www.youtube.com/user/eaoswitches) Be sure to give us a follow so that you can fully interact with us.

<https://www.youtube.com/user/eaoswitches>

www.eao.com

eao ■

Your Expert Partner for Human Machine Interfaces

45 Accessories

Mounting




Adapter for reduction of 30.5 mm to 22.3 mm

Product attributes	Material	IP front protection	Part No.
With seal	Metal	IP66, IP67, IP69K	45-501.2000




Enclosure


Product attributes	Dimensions	Material	Colour	IP Protection	Part No.
1 mounting hole Ø 22.3 mm 1 x M20	85 mm x 64 mm x 85 mm	Plastic	Grey	IP66, IP67, IP69K	45-430.1801
	85 mm x 64 mm x 85 mm	Plastic	Yellow	IP66, IP67, IP69K	45-410.1401
1 mounting hole Ø 22.3 mm, top and bottom each 1 x M20	89.4 mm x 64 mm x 85 mm	Metal	Yellow	IP66, IP67, IP69K	45-410.2403
	89.4 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-430.2803
1 mounting hole Ø 22.3 mm 1 x M20, with protective shroud	85 mm x 64 mm x 85 mm	Plastic	Yellow	IP66, IP67, IP69K	45-420.1401
	85 mm x 64 mm x 85 mm	Metal	Yellow	IP66, IP67, IP69K	45-420.2403
1 mounting hole Ø 22.3 mm, with protective shroud, top and bottom 1 x M20	89.4 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-420.2803
2 mounting holes Ø 22.3 mm, top and bottom 1 x M20	114 mm x 64 mm x 85 mm	Plastic	Grey	IP66, IP67, IP69K	45-440.1801
	118 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-440.2803
3 mounting holes Ø 22.3 mm, top and bottom 1 x M20	154 mm x 64 mm x 85 mm	Plastic	Grey	IP66, IP67, IP69K	45-450.1801
	158 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-450.2803
4 mounting holes Ø 22.3 mm, top and bottom 1 x M25	194 mm x 64 mm x 85 mm	Plastic	Grey	IP66, IP67, IP69K	45-460.1802
	199 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-460.2804
6 mounting holes Ø 22.3 mm, top and bottom 1 x M25	280 mm x 64 mm x 85 mm	Plastic	Grey	IP66, IP67, IP69K	45-470.1802
	285 mm x 64 mm x 85 mm	Metal	Grey	IP66, IP67, IP69K	45-470.2804




Dimensions [mm]
for Part No. 45-430.1801, 45-410.1401




Dimensions [mm]
for Part No. 45-410.2403, 45-430.2803, 45-420.2803 for Part No. 45-420.1401, 45-420.2403




Dimensions [mm]
for Part No. 45-420.1401, 45-420.2403




Dimensions [mm]
for Part No. 45-440.1801, 45-440.2803




Dimensions [mm]
for Part No. 45-450.1801




Dimensions [mm]
for Part No. 45-450.2803




Dimensions [mm]
for Part No. 45-460.1802



Dimensions [mm]
for Part No. 45-460.2804



Dimensions [mm]
for Part No. 45-470.1802




Dimensions [mm]
for Part No. 45-470.2804

45 Accessories



Enclosure cover monitoring

Product attributes	Material	Colour	Part No.
With extension plungers	Plastic	Black	45-50G.0900




Dimensions [mm]



Cable gland

Material	Colour	IP Protection	Thread	Part No.
Plastic	Black	IP66, IP67, IP69K	M20	45-507.1100
	Black	IP66, IP67, IP69K	M25	45-509.1100




Dimensions [mm]




Connection piece


Product attributes	Material	Colour	IP Protection	Thread	Part No.
For connecting 2 enclosures, with hexagonal nut	Plastic	Black	IP66, IP67, IP69K	M20 / M20	45-50C.1900
	Plastic	Black	IP66, IP67, IP69K	M20 / M25	45-50D.1900
	Plastic	Black	IP66, IP67, IP69K	M25 / M26	45-50E.1900
	Metal	Silver	IP66, IP67, IP69K	M20 / M20	45-50C.2900
	Metal	Silver	IP66, IP67, IP69K	M20 / M25	45-50D.2900
	Metal	Silver	IP66, IP67, IP69K	M25 / M26	45-50E.2900
	Plastic	Black	IP66, IP67, IP69K	M20 / M25	45-50F.2900




Dimensions [mm]
for Part No. 45-50C.1900




Dimensions [mm]
for Part No. 45-50D.1900




Dimensions [mm]
for Part No. 45-50E.1900




Dimensions [mm]
for Part No. 45-50C.2900



Dimensions [mm]
for Part No. 45-50D.2900



Dimensions [mm]
for Part No. 45-50E.2900




Dimensions [mm]
for Part No. 45-50F.2900


45 Accessories

Dimensions incl. mounting depth of 3 or 4 elements


Indicator, Pushbutton, Illuminated pushbutton (flush design)




Keylock switch (flush design)




Selector switch short lever (flush design)




Selector switch long lever (flush design)




Indicator full face illumination (raised design)



Indicator front illumination, Pushbutton, Illuminated pushbutton, Lens level with front ring (raised design)




Buzzer




45 Drawings


Pushbutton, Illuminated pushbutton, lens raised above front ring (raised design)




Pushbutton, lens lower than front ring (raised design)




Pushbutton, Illuminated pushbutton, lens lower than front ring, with castellation (raised design)




Double pushbutton, Lens level with front ring (raised design)




Double pushbutton, level with/raised above front ring (raised design)




Emergency stop switch Ø 33.8 mm (raised design)



Emergency stop switch, Stop switch Ø 40 mm (raised design)




Emergency stop switch, Stop switch Ø 40 mm (raised design)




45 Drawings


Emergency stop switch Ø 60 mm (raised design)




Emergency stop switch with key Ø 40 mm (raised design)




Stop switch Ø 29.5 mm (raised design)




Palm switch




Mushroom-head pushbutton Ø 30 mm (raised design)




Mushroom-head pushbutton Momentary, Maintain, Ø 40 mm (raised design)



Mushroom-head pushbutton Momentary/Maintain, Momentary/Momentary, Ø 40 mm (raised design)




Mushroom-head pushbutton Ø 60 mm (raised design)




45 Drawings


Keylock switch (raised design)




ID keylock switch (raised design)




Selector switch, round lever (raised design)




Selector switch, short lever (raised design)




Selector switch, long lever (raised design)




Potentiometer (raised design)



Toggle stick (raised design)



Toggle switch (raised design)



45 Technical data

01	Indicator actuator	
02	Material	Protection degree IP66, IP67, IP69K
03	Actuator element Plastic	Vibration resistance According to IEC 60068-2-6 2 ... 500 Hz: 5g
04	Front ring Plastic or metal	Shock resistance According to IEC 60068-2-27 Sinusoidal half-wave 50g/11ms
09	Actuator housing Plastic or metal	Climatic ambient conditions During operation according to IEC 60721: 3K6, 3C3, 3S2, 3M6
14	Ambient conditions	
17	Operating temperature −25 °C ... +70 °C	
18	Storage temperature −40 °C ... +80 °C	
19		
22	Buzzer	
31	Material	Electrical characteristics
41	Actuator element Plastic	Frequency (tone) Approx. 2.4 kHz continuous tone only
45	Front bezel Plastic or metal	Sound pressure 95 db (A) ±8 dB at a distance of 0.1 m
51	Actuator housing Plastic or metal	Insulation voltage Rated value 320 V
56	Mechanical characteristics	Pollution degree 3
57	Terminal Screw terminal	Surge voltage resistance Rated value 4 kV
61	- Solid without end sleeves 2 x (1.0 ... 1.5 mm ²) - Solid with end sleeves 2 x (0.5 ... 0.75 mm ²) - Finely stranded without end sleeves 2 x (0.5 ... 0.75 mm ²) - Finely stranded with end sleeves 2 x (0.5 ... 1.5 mm ²) - For AWG cables for auxiliary contacts 2 x (18 ... 14)	Operating voltage at AC - Rated value 24 ... 24 V at DC - Rated value 24 ... 24 V
70		
71	Tightening torque Screw terminal 0.8 ... 1 Nm	
82		
84		
92		
96		

Ambient conditions

Operating temperature
-25 °C ... +70 °C

Storage temperature
-40 °C ... +80 °C

Protection degree
IP40

Vibration resistance

According to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance

According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions

During operation according to IEC 60721:
3B2, 3K6, 3S2, 3M6

Pushbutton actuator

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
- Momentary max. 3 600/h
- Maintain max. 1 800/h

Mechanical lifetime
- Momentary 500 000 cycles of operation
- Maintain 10 000 000 cycles of operation

Ambient conditions

Operating temperature
-25 °C ... +70 °C

Storage temperature
-40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
20 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g / 11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

45 Technical data

Double pushbutton actuator, Double pushbutton actuator illuminated

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
max. 3 600/h

Mechanical lifetime
2 000 000 cycles of operation

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g / 11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6, 3B2

Illuminated pushbutton actuator

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
- Momentary max. 3 600/h
- Maintain max. 1 800/h

Mechanical lifetime
- Momentary 3 000 000 cycles of operation
- Maintain 500 000 cycles of operation

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
20 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g / 11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Emergency stop switch actuator

Material

Actuator element
Plastic red

Actuator housing
Plastic or metal

Mechanical characteristics

Type of unlocking device
Twist to release, pull release or
key to release

Operating frequency
Max. 600/h

Mechanical lifetime
300 000 cycles of operation

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
2 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Stop switch actuator

Material

Actuator element
Plastic red

Actuator housing
Plastic or metal

Mechanical characteristics

Type of unlocking device
Twist to release

Operating frequency
Max. 600/h

Mechanical lifetime
300 000 cycles of operation

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
2 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

45 Technical data

Palm switch

Material

Actuator element
Plastic or metal, red or black

Actuator housing
Plastic or metal

Mechanical characteristics

Type of unlocking device
Pull to release

Electrical characteristics

Operating voltage
at AC
- Rated value 5 ... 500 V

at DC
- Rated value 5 ... 500 V

Ambient conditions

Operating temperature
-25 °C ... +70 °C

Storage temperature
-40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6, 3B2

Mushroom-head pushbutton actuator

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Type of unlocking device
Pull release

Operating frequency
- Momentary max. 3600/h
- Maintain max. 1800/h

Mechanical lifetime
- Momentary 10 000 000 cycles of operation
- Maintain 500 000 cycles of operation

Ambient conditions

Operating temperature
-25 °C ... +70 °C

Storage temperature
-40 °C ... +80 °C

Vibration resistance
According to IEC 60068-2-6
20 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Protection degree
IP66, IP67, IP69K

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Keylock switch actuator

Material

Actuator element
Metal

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
Max. 1800/h

Mechanical lifetime
1 000 000 cycles of operation

Ambient conditions

Operating temperature
-25 °C ... +70 °C

Storage temperature
-40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
10 ... 500 Hz: 5g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

ID keylock switch

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic

Mechanical characteristics

Terminals
Screw terminal front mounting

- Solid with end sleeves
1 x (0.2 ... 2.5 mm²), 2 x (0.2 ... 0.75 mm²)
- Solid without end sleeves
1 x (0.2 ... 2.5 mm²), 2 x (0.2 ... 0.75 mm²)
- Finely stranded with end sleeves
1 x (0.2 ... 2.5 mm²), 2 x (0.25 ... 0.75 mm²)
- Finely stranded with end sleeves
1 x (0.2 ... 2.5 mm²), 2 x (0.2 ... 0.75 mm²)
- For AWG cables
1 x (24 ... 14), (24 ... 19)

Tightening torque
Screw terminal
0.35 ... 0.4 Nm

Mechanical lifetime
100 000 cycles of operation

Number of NO contacts
5

ID-Key

Authorization level	Key colour
1	green
1+2	yellow
1+2+3	red
1+2+3+4	blue

Electrical characteristics

Operating voltage
24 VDC

45 Technical data

Ambient conditions

Operating temperature

–25 °C ... +70 °C

Storage temperature

–40 °C ... +80 °C

Protection degree

IP65

Climatic ambient conditions

During operation according to IEC 60721:

3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95 %)

Selector switch actuator

Material

Actuator element

Round lever, plastic, illuminable

Short lever, plastic, illuminable

Long lever, plastic, illuminable

Front ring

Plastic or metal

Actuator housing

Plastic or metal

Ambient conditions

Operating temperature

–25 °C ... +70 °C

Storage temperature

–40 °C ... +80 °C

Protection degree

IP66, IP67, IP69K

Vibration resistance

According to IEC 60068-2-6

10 ... 500 Hz: 5g

Shock resistance

According to IEC 60068-2-27

Sinusoidal half-wave 50g/11ms

Climatic ambient conditions

During operation according to IEC 60721:

3K6, 3C3, 3S2, 3M6

Mechanical characteristics

Operating frequency

Max. 1 800/h

Mechanical lifetime

1 000 000 cycles of operation

Potentiometer

Material

Actuator element

Round lever, plastic

Front ring

Plastic or metal

Actuator housing

Plastic or metal

Mechanical characteristics

Terminals

Screw terminal

- Solid 2 x (1.0 ... 1.5 mm²)

- With end sleeves 2 x (0.5 ... 0.75 mm²)

- Finely stranded

- Without end sleeves 2 x (0.5 ... 0.75 mm²)

- With end sleeves 2 x (0.5 ... 1.5 mm²)

- For AWG cables for auxiliary contacts 2 x (18 ... 14)

Tightening torque

0.8 ... 1 Nm

Turning frequency

Max. 1 800/h

Mechanical lifetime
25000 turning cycles

Slewing range
300°

Electrical characteristics

Active power consumption
0.5 W

Insulation voltage
Rated value 500 V

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
according to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance
according to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Toggle stick actuator

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
3600/h

Mechanical lifetime
Momentary: 250 000 cycles of operation per direction of actuation
Maintain: 100 000 cycles of operation per direction of actuation

Deflection angle
Max. 30°

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP65, IP67

Vibration resistance
According to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

45 Technical data

Toggle switch actuator

Material

Actuator element
Plastic

Front ring
Plastic or metal

Actuator housing
Plastic or metal

Mechanical characteristics

Operating frequency
Max. 1 800/h

Mechanical lifetime
1 000 000 cycles of operation

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Protection degree
IP66, IP67, IP69K

Vibration resistance
According to IEC 60068-2-6
10 ... 500 Hz: 5 g

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Slow-make switching element

Switching system

The double-break, slow-make switching element is equipped with normally open or normally closed contact. The normally closed contact has forced opening. Slow-make contacts with forced action are ideal for high switch ratings. Up to six switching elements can be snapped to each holder.

The NC contact opens automatically upon disconnection of the actuator. On delivery, the contact is open (= safe state). Activation (= NC contacts on the non-actuated commanding device are closed) takes place upon first-time actuation after the contact block is snapped onto the actuator.

Material

Material of contact
Silver alloy

Housing
Plastic

Mechanical characteristics

Terminals
Screw terminal
- Solid 2 x (1.0 ... 1.5 mm²)
- With end sleeves 2 x (0.5 ... 0.75 mm²)
- Finely stranded
- Without end sleeves 2 x (0.5 ... 0.75 mm²)
- With end sleeves 2 x (0.5 ... 1.5 mm²)
- For AWG cables for auxiliary contacts 2 x (18 ... 14)

Spring-type terminal (SP)
- Solid 2 x (0.25 ... 1.5 mm²)
- Finely stranded
- Without end sleeves 2 x (0.5 ... 1.5 mm²)
- With end sleeves 2 x (0.5 ... 0.75 mm²)
- For AWG cables for auxiliary contacts 2 x (24 ... 16)

Tightening torque
Screw terminal, spring-type terminal 0.8 ... 0.9 Nm

Operating frequency
Max. 3 600/h

Mechanical lifetime
10 000 000 cycles of operation

Electrical characteristics

Standards

The switches comply with the "Standards for low-voltage switching devices" EN IEC 60947-5-1

Thermal current I_{th}

10 A

Insulation voltage

Rated value 500 V

Pollution degree

3

Surge voltage resistance

Rated value 6 kV

Contact reliability

One contact failure per 100 million switching operations
(17 V, 5 mA)

One contact failure per 10 million switching operations (5 V, 1 mA)

Operating voltage

at AC

- Rated value 5 ... 500 V

at DC

- Rated value 5 ... 500 V

Switching voltage and switching current

at AC-12

Voltage	24 V	230 V	500 V
Current	10 A	10 A	10 A

at AC-15

Voltage	24 V	230 V	400 V	500 V
Current	6 A	6 A	3 A	1.4 A

at DC-12

Voltage	24 V	48 V	110 V	230 V	400 V	500 V
Current	10 A	5 A	2.5 A	1 A	0.3 A	0.2 A

at DC-13

Voltage	24 V	48 V	110 V	230 V	400 V	500 V
Current	3 A	1.5 A	0.7 A	0.3 A	0.1 A	0.07 A

Ambient conditions

Operating temperature

-25 °C ... +70 °C

Storage temperature

-40 °C ... +80 °C

Protection degree

IP40 housing

IP20 terminal

Vibration resistance

According to IEC 60068-2-6

2 ... 500 Hz: 5 g

Shock resistance

According to IEC 60068-2-27

Sinusoidal half-wave 50 g/11 ms

Climatic ambient conditions

During operation according to IEC 60721:

3K6, 3C3, 3S2, 3M6

Approvals

Approbations

CCC

CSA

UL

Declaration of conformity

CE

45 Technical data

Illumination element

Material

Housing
Plastic

Ambient conditions

Operating temperature
−25 °C ... +70 °C

Storage temperature
−40 °C ... +80 °C

Mechanical characteristics

Terminals

- Screw terminal
- Solid 2 x (1.0 ... 1.5 mm²)
 - With end sleeves 2 x (0.5 ... 0.75 mm²)
 - Finely stranded
 - Without end sleeves 2 x (0.5 ... 0.75 mm²)
 - With end sleeves 2 x (0.5 ... 1.5 mm²)
 - For AWG cables for auxiliary contacts 2 x (18 ... 14)

Protection degree
IP20 terminal

Shock resistance
According to IEC 60068-2-27
Sinusoidal half-wave 50 g/11 ms

Vibration resistance
According to IEC 60068-2-6
2 ... 500 Hz: 5 g

- Spring-type terminal (SP)
- Solid 2 x (0.25 ... 1.5 mm²)
 - Finely stranded
 - Without end sleeves 2 x (0.5 ... 1.5 mm²)
 - With end sleeves 2 x (0.5 ... 0.75 mm²)
 - For AWG cables for auxiliary contacts 2 x (24 ... 16)

Climatic ambient conditions
During operation according to IEC 60721:
3K6, 3C3, 3S2, 3M6

Tightening torque

Screw terminal, spring-type terminal 0.8 ... 0.9 Nm

Optical characteristics

Luminous intensity	
Red	450 ... 1120 mcd
Amber	450 ... 1120 mcd
Yellow	900 ... 1400 mcd
Green	900 ... 1400 mcd
Blue	280 ... 710 mcd
White	900 ... 1400 mcd

Electrical characteristics

Standards

The switches comply with the "Standards for low-voltage switching devices" EN IEC 60947-5-1

Approvals

Approbations

CCC
CSA
UL

Declaration of conformity

CE

EAO reserves the right to alter specifications without further notice.

Inscription marking plates and legend plates

Labels can be inserted for identification purposes in illuminated pushbuttons and pushbuttons with a flat lens. This marking plates are made of translucent plastic with a black inscription, which can be fitted in any 90° angle.

Standard texts for marking plates

Example		Part No. 45-563.0K00.T00029
----------------	---	-----------------------------

Standard texts German		Standard texts English	
Ein	Part No. 45-563.0K00.T00001	On	Part No. 45-563.0K00.T00020
Aus	Part No. 45-563.0K00.T00002	Off	Part No. 45-563.0K00.T00021
Auf	Part No. 45-563.0K00.T00003	Up	Part No. 45-563.0K00.T00022
Ab	Part No. 45-563.0K00.T00004	Down	Part No. 45-563.0K00.T00023
Vor	Part No. 45-563.0K00.T00005	Forward	Part No. 45-563.0K00.T00024
Zurück	Part No. 45-563.0K00.T00006	Right	Part No. 45-563.0K00.T00026
Rechts	Part No. 45-563.0K00.T00007	Left	Part No. 45-563.0K00.T00027
Links	Part No. 45-563.0K00.T00008	Stop	Part No. 45-563.0K00.T00028
Halt	Part No. 45-563.0K00.T00009	Start	Part No. 45-563.0K00.T00029
Zu	Part No. 45-563.0K00.T00010	Reset	Part No. 45-563.0K00.T00030
Schnell	Part No. 45-563.0K00.T00011	Test	Part No. 45-563.0K00.T00031
Langsam	Part No. 45-563.0K00.T00012	Open	Part No. 45-563.0K00.T00032
Betrieb	Part No. 45-563.0K00.T00013	Close	Part No. 45-563.0K00.T00033
Störung	Part No. 45-563.0K00.T00014	Running	Part No. 45-563.0K00.T00035
Einrichten	Part No. 45-563.0K00.T00018	Fast	Part No. 45-563.0K00.T00044
		Slow	Part No. 45-563.0K00.T00045

45 Marking

Symbols for marking plates


Graphic symbols are according to ISO 7000 or IEC 60417.

 Part No. 45-563.0K00.S00001	 Part No. 45-563.0K00.S00012 Decrease, Minus	 Part No. 45-563.0K00.S00023 Unlock
 Part No. 45-563.0K00.S00002	 Part No. 45-563.0K00.S00013 Electric motor	 Part No. 45-563.0K00.S00024 Setting
 Part No. 45-563.0K00.S00003	 Part No. 45-563.0K00.S00014 Horn	 Part No. 45-563.0K00.S00025 On-Off momentary contact type
 Part No. 45-563.0K00.S00004	 Part No. 45-563.0K00.S00015 Water tap	 Part No. 45-563.0K00.S00026 Manual operating
 Part No. 45-563.0K00.S00005 Arrow direction to right	 Part No. 45-563.0K00.S00016 Pump	 Part No. 45-563.0K00.S00027 Automatic cycle
 Part No. 45-563.0K00.S00006 Arrow direction up	 Part No. 45-563.0K00.S00017 Coolant pump	 Part No. 45-563.0K00.S00028 Suction
 Part No. 45-563.0K00.S00007 Clockwise rotation	 Part No. 45-563.0K00.S00018 Lock, tighten	 Part No. 45-563.0K00.S00029 Blowing
 Part No. 45-563.0K00.S00008 Counterclockwise rotation	 Part No. 45-563.0K00.S00019 Unlock, unclamp	
 Part No. 45-563.0K00.S00009 Rapid traverse	 Part No. 45-563.0K00.S00020 Brake	
 Part No. 45-563.0K00.S00010 Feed	 Part No. 45-563.0K00.S00021 Release brake	
 Part No. 45-563.0K00.S00011 Increase, Plus	 Part No. 45-563.0K00.S00022 Interlock	

Customised inscription for marking plates


All dimensions in mm

Height of letters	Number of lines	Number of letters per line (target value)		
h		b1	b2	b3
4	1	10	—	—
3	2	—	8	—
	3	10	—	6



The gap between two words results in each case a letter less.

Standard texts for legend plates black, 27 x 27 mm

Example		Part No. 45-573.1103.T00028
---------	---	-----------------------------

Standard texts German		Standard texts English		Standard texts French	
Ein	Part No. 45-573.1105.T00001	On	Part No. 45-573.1105.T00020	Marche	Part No. 45-573.1105.T00048
Aus	Part No. 45-573.1105.T00002	Off	Part No. 45-573.1105.T00021	Arrêt	Part No. 45-573.1105.T00049
Auf	Part No. 45-573.1105.T00003	Up	Part No. 45-573.1105.T00022	Montée	Part No. 45-573.1105.T00050
Ab	Part No. 45-573.1105.T00004	Down	Part No. 45-573.1105.T00023	Descente	Part No. 45-573.1105.T00051
Vor	Part No. 45-573.1105.T00005	Forward	Part No. 45-573.1105.T00024	En Service	Part No. 45-573.1105.T00059
Zurück	Part No. 45-573.1105.T00006	Reverse	Part No. 45-573.1105.T00025	Default	Part No. 45-573.1105.T00060
Rechts	Part No. 45-573.1105.T00007	Stop	Part No. 45-573.1105.T00028	Sous tension	Part No. 45-573.1105.T00064
Links	Part No. 45-573.1105.T00008	Start	Part No. 45-573.1105.T00029	Manu Auto	Part No. 45-573.1105.T00065
Halt	Part No. 45-573.1105.T00009	Stop Start	Part No. 45-573.1105.T00038	Marche Arrêt	Part No. 45-573.1105.T00066
Zu	Part No. 45-573.1105.T00010	EMERGENCY STOP	Part No. 45-573.1105.T00046		
Betrieb	Part No. 45-573.1105.T00013				
Störung	Part No. 45-573.1105.T00014				
Hand Auto	Part No. 45-573.1105.T00015				

Symbols for legend plates black, 27 x 27 mm

Graphic symbols are according to ISO 7000 or IEC 60417.

	Part No. 45-573.1105.S00003		Part No. 45-573.1105.S00008 Arrow/Direction right
---	-----------------------------	---	--

Customized inscription for legend plates

All dimensionen in mm

Size of legend plates	Height of letters	Number of lines
27 x 12.5	4	1
	3.5	2
	2.5	3
27 x 17.5	4	1 – 2
	3	3
27 x 27	4	1 – 5

Up to 11 characters per line are possible.

45 Application guidelines

Suppressor circuits

When switching inductive loads such as relays, DC motors, and DC solenoids, it is always important to absorb surges (e.g. with a diode) to protect the contacts. When these inductive loads are switched off, a counter emf can severely damage switch contacts and greatly shorten lifetime.


Fig. 1 shows an inductive load with a free-wheeling diode connected in parallel. This free-wheeling diode provides a path for the inductor current to flow when the current is interrupted by the switch. Without this free-wheeling diode, the voltage across the coil will be limited only by dielectric breakdown voltages of the circuit or parasitic elements of the coil. This voltage can be kilo-

volts in amplitude even when nominal circuit voltages are low (e.g. 12VDC) see Fig. 2.


The free-wheeling diode should be chosen so that the reverse breakdown voltage is greater than the voltage driving the inductive load. The DC blocking voltage (VR) of the free-wheeling diode can be found in the datasheet of a diode. The forward current should be equal or greater than the maximum current flowing through the load.

To get an efficient protection, the free-wheeling diode must be connected as close as possible to the inductive load!

Switching with inductive load
Fig. 1



Counter EMF
over load without free-wheeling diode
Fig. 2



Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page	Part No.	Page
45-2131.1110.000	13	45-2231.21K0.000	18	45-2630.18G0.000	30	45-2819.1C60.003	43	45-2925.2000.111	47	45-311.1Z10	67
45-2131.1120.000	13	45-2231.21N0.000	18	45-2630.19E0.000	32	45-2819.1C90.003	43	45-2C35.1920.110	60	45-311.1Z40	69
45-2131.1140.000	13	45-2231.22E0.000	18	45-2630.19H0.000	32	45-2819.2C20.003	43	45-2C35.2920.110	60	45-311.2Z10	70
45-2131.1150.000	13	45-2231.22F0.000	18	45-2630.19J0.000	32	45-2819.2C40.003	43	45-2C36.1820.000	60	45-311.2Z40	71
45-2131.1160.000	14	45-2231.22G0.000	18	45-2630.28E0.000	30	45-2819.2C50.003	43	45-2C36.1920.000	60	45-312.1X10	67
45-2131.1180.000	14	45-2231.22H0.000	18	45-2630.28H0.000	30	45-2819.2C90.003	43	45-2C36.1A20.000	60	45-312.1X40	69
45-2131.1190.000	14	45-2231.22J0.000	18	45-2630.28J0.000	30	45-2819.2D20.003	44	45-2C36.2820.000	61	45-312.1Z10	67
45-2131.11K0.000	14	45-2231.22K0.000	18	45-2630.28K0.000	30	45-2819.2D50.003	44	45-2C36.2910.000	59	45-312.1Z40	69
45-2131.1210.000	14	45-2231.22N0.000	18	45-2630.29E0.000	32	45-2819.2D90.003	44	45-2C36.2920.000	61	45-312.2Z10	70
45-2131.1220.000	14	45-2231.4FE0.000	6	45-2630.29G0.000	32	45-2819.4C20.003	9	45-2C37.1920.000	60	45-312.2Z40	71
45-2131.1240.000	14	45-2231.4FG0.000	6	45-2630.29J0.000	32	45-2819.4C50.003	9	45-2C37.2920.000	60	45-313.1X40	69
45-2131.1250.000	14	45-2231.4FH0.000	6	45-2630.29K0.000	32	45-2819.4C90.003	9	45-2D36.1820.000	62	45-313.1Z10	67
45-2131.1260.000	14	45-2231.4FJ0.000	6	45-2630.2AE0.000	34	45-2819.4D20.003	10	45-2D36.1920.000	62	45-313.1Z40	69
45-2131.1290.000	14	45-2231.4FK0.000	6	45-2630.2AJ0.000	34	45-2819.4D50.003	10	45-2D36.1A20.000	62	45-314.1X40	69
45-2131.1320.000	15	45-2234.11E0.000	18	45-2630.2AK0.000	34	45-2819.4D90.003	10	45-2D36.2820.000	62	45-314.1Z10	67
45-2131.1350.000	15	45-2234.11G0.000	18	45-2631.18E0.000	30	45-2828.1C20.001	37	45-2D36.2920.000	62	45-314.1Z40	69
45-2131.1360.000	15	45-2234.11H0.000	18	45-2631.18G0.000	30	45-2828.1C40.001	37	45-2D36.2A20.000	62	45-315.1X40	69
45-2131.1460.000	15	45-2234.11J0.000	18	45-2631.18H0.000	30	45-2828.1C50.001	37	45-2F0T.1010.000	51	45-315.1Z10	67
45-2131.1460.000	15	45-2234.11K0.000	18	45-2631.18J0.000	30	45-2828.1C60.001	37	45-2F0T.2010.000	51	45-315.1Z40	69
45-2131.2110.000	14	45-2234.11N0.000	18	45-2631.18N0.000	30	45-2828.1C90.001	37	45-2F0V.1010.000	51	45-316.1X10	67
45-2131.2120.000	14	45-2234.21E0.000	18	45-2631.19G0.000	32	45-2828.1D20.001	39	45-2F0V.2010.000	51	45-316.1X40	69
45-2131.2140.000	14	45-2234.21G0.000	19	45-2631.19H0.000	32	45-2828.1D90.001	39	45-2F13.1010.000	51	45-316.1Z40	69
45-2131.2150.000	14	45-2234.21H0.000	19	45-2631.19K0.000	32	45-2828.1E20.001	41	45-2F13.2010.000	51	45-317.1Z40	69
45-2131.2160.000	14	45-2234.21J0.000	19	45-2631.19N0.000	32	45-2828.1E90.001	41	45-2F14.1010.000	51	45-320.1E11	72
45-2131.2180.000	14	45-2234.21N0.000	19	45-2631.28N0.000	30	45-2828.2C20.001	37	45-2F14.2010.000	51	45-320.1E12	72
45-2131.2190.000	14	45-2234.31E0.000	19	45-2631.29F0.000	32	45-2828.2C30.001	37	45-2F38.2010.000	51	45-320.1E16	72
45-2131.21K0.000	14	45-2234.31G0.000	19	45-2631.29G0.000	32	45-2828.2C50.001	37	45-2F40.1010.000	51	45-320.1E17	72
45-2131.2210.000	14	45-2234.31H0.000	19	45-2631.29H0.000	32	45-2828.2C90.001	37	45-2F40.2010.000	51	45-320.1E18	72
45-2131.2220.000	14	45-2234.31J0.000	19	45-2631.29N0.000	32	45-2828.2D20.001	39	45-2H00.1016.000	56	45-320.1E41	74
45-2131.2240.000	14	45-2234.31K0.000	19	45-2631.2AF0.000	34	45-2828.2D50.001	39	45-2H00.1017.000	56	45-320.1E42	74
45-2131.2250.000	14	45-2234.31N0.000	19	45-2631.2AG0.000	34	45-2828.2D60.001	39	45-2H00.1018.000	56	45-320.1E46	74
45-2131.2260.000	14	45-2234.4FE0.000	6	45-2631.2AH0.000	34	45-2828.2D90.001	39	45-2J31.15T0.000	20	45-320.1E47	74
45-2131.2340.000	15	45-2234.4FG0.000	6	45-2631.2AN0.000	34	45-2828.4C20.001	7	45-2J31.15V0.000	20	45-320.1E48	74
45-2131.2350.000	15	45-2234.4FH0.000	6	45-2632.29E0.000	32	45-2828.4C50.001	7	45-2J31.16T0.000	20	45-320.1F11	72
45-2131.2360.000	15	45-2234.4FJ0.000	6	45-2729.1010.000	59	45-2828.4C90.001	7	45-2J31.16V0.000	20	45-320.1F12	72
45-2131.4F10.000	5	45-2234.4FK0.000	6	45-2729.1020.000	59	45-2828.4D20.001	8	45-2J31.25T0.000	20	45-320.1F16	72
45-2131.4F20.000	5	45-2300.1000.000	65	45-2736.1910.000	59	45-2828.4D50.001	8	45-2J31.25V0.000	20	45-320.1F18	72
45-2131.4F40.000	5	45-2300.2000.000	65	45-2736.1960.000	59	45-2828.4D90.001	8	45-2J31.26T0.000	20	45-320.1F41	74
45-2131.4F50.000	5	45-2300.3000.000	65	45-280S.1C20.003	42	45-2844.1C20.006	37	45-2J31.26V0.000	20	45-320.1F42	74
45-2131.4F60.000	5	45-2400.1000.000	66	45-280S.1C40.003	42	45-2844.1C90.006	37	45-2K31.15V0.000	22	45-320.1F46	74
45-2131.4F90.000	5	45-2400.2000.000	66	45-280S.1C60.003	42	45-2844.2C90.006	37	45-2K31.16T0.000	22	45-320.1G11	72
45-2134.1110.000	15	45-2530.1810.000	24	45-280S.1C90.003	42	45-2844.2D50.006	39	45-2K31.16V0.000	22	45-320.1G12	72
45-2134.1120.000	15	45-2530.1820.000	24	45-280S.2C20.003	42	45-2844.2D90.006	39	45-2N39.1010.000	53	45-320.1G16	72
45-2134.1140.000	15	45-2530.1910.000	26	45-280S.2C30.003	42	45-2844.4C20.006	7	45-2N39.2010.000	53	45-320.1G18	72
45-2134.1150.000	15	45-2530.1920.000	26	45-280S.2C40.003	42	45-2844.4C50.006	7	45-2N42.1010.000	53	45-320.1G41	74
45-2134.1160.000	15	45-2530.1940.000	26	45-280S.2C50.003	42	45-2844.4C90.006	7	45-2N42.2010.000	53	45-320.1G42	74
45-2134.1190.000	15	45-2530.1950.000	26	45-280S.2C60.003	42	45-2844.4D50.006	8	45-2P01.1E10.000	57	45-320.1G46	74
45-2134.2110.000	15	45-2530.2820.000	24	45-280S.2C90.003	42	45-2844.4D90.006	8	45-2P02.1E10.000	57	45-320.1G48	74
45-2134.2120.000	15	45-2530.2910.000	26	45-280S.2D20.003	44	45-2845.1E90.002	46	45-2P03.1E10.000	57	45-320.1H11	72
45-2134.2140.000	15	45-2530.2920.000	26	45-280S.2D50.003	44	45-2845.2E90.002	46	45-2P04.1E10.000	57	45-320.1H12	72
45-2134.2150.000	15	45-2530.2940.000	26	45-280S.2D90.003	44	45-290A.1000.113	48	45-2S00.1001.404	50	45-320.1H16	72
45-2134.2160.000	15	45-2530.2A10.000	28	45-280S.4C20.003	9	45-290A.2000.113	48	45-2T00.10E0.000	54	45-320.1H17	72
45-2134.2190.000	15	45-2530.2A20.000	28	45-280S.4C50.003	9	45-290C.2000.113	48	45-2T00.10F0.000	54	45-320.1H18	72
45-2134.4F10.000	5	45-2531.1810.000	24	45-280S.4C90.003	9	45-290D.2000.113	48	45-2T00.10G0.000	54	45-320.1H41	74
45-2134.4F20.000	5	45-2531.1820.000	24	45-280S.4D20.003	10	45-290F.1000.113	48	45-2T00.10H0.000	54	45-320.1H42	74
45-2134.4F40.000	5	45-2531.1840.000	24	45-280S.4D50.003	10	45-290F.2000.113	48	45-2T00.10J0.000	54	45-320.1H46	74
45-2134.4F50.000	5	45-2531.1910.000	26	45-280S.4D90.003	10	45-290F.4F00.113	11	45-2T00.10K0.000	54	45-320.1H48	74
45-2134.4F60.000	5	45-2531.1920.000	26	45-280X.1C20.003	42	45-290G.1000.113	48	45-2T00.10N0.000	54	45-320.1J11	72
45-2134.4F90.000	5	45-2531.1940.000	26	45-280X.1C40.003	42	45-290G.2000.113	48	45-2T00.20E0.000	54	45-320.1J12	72
45-2231.11E0.000	17	45-2531.1950.000	26	45-280X.1C50.003	42	45-290H.1000.111	47	45-2T00.20F0.000	54	45-320.1J16	72
45-2231.11F0.000	17	45-2531.1A10.000	28	45-280X.1C60.003	42	45-290H.2000.111	47	45-2T00.20G0.000	54	45-320.1J18	72
45-2231.11G0.000	17	45-2531.1A20.000	28	45-280X.1C90.003	42	45-290H.4F00.111	11	45-2T00.20H0.000	54	45-320.1J41	74
45-2231.11H0.000	17	45-2531.1A40.000	28	45-280X.2C90.003	42	45-290J.1000.111	47	45-2T00.20J0.000	54	45-320.1J42	74
45-2231.11J0.000	17	45-2531.1A50.000	28	45-280X.2D20.003	44	45-290J.2000.111	47	45-2T00.20K0.000	54	45-320.1J46	74
45-2231.11K0.000	17	45-2531.2810.000	24	45-280X.2D90.003	44	45-290J.4F00.111	11	45-2T00.20N0.000	54	45-320.1J48	74
45-2231.11N0.000	17	45-2531.2820.000	24	45-2816.1C20.003	43	45-290J.4F00.116	11	45-2T00.20O0.000	55	45-320.1N11	72
45-2231.12E0.000	18	45-2531.2840.000	24	45-2816.1C40.003	43	45-290K.1000.116	47	45-2T07.10G0.000	55	45-320.1N12	72
45-2231.12G0.000	18	45-2531.2850.000	24	45-2816.1C50.003	43	45-290K.2000.116	47	45-2T07.10H0.000	55	45-320.1N16	72
45-2231.12H0.000	18	45-2531.2910.000	26	45-2816.1C60.003	43	45-290Z.1000.113	48	45-2T07.10J0.000	55	45-320.1N17	72
45-2231.12J0.000	18	45-2531.2920.000	26	45-2816.1C90.003	43	45-290Z.2000.113	48	45-2T07.10K0.000	55	45-320.1N18	72
45-2231.12K0.000	18	45-2531.2940.000	26	45-2816.2C20.003	43	45-2917.1000					

45 Index

	Part No.	Page	Part No.	Page
01	45-320.2E42	76	45-50Q.2100	86
02	45-320.2F11	75	45-50T.0500	79
03	45-320.2F16	75	45-50V.0400	79
04	45-320.2G11	75	45-50W.0200	79
09	45-320.2G12	75	45-522.0900	83
14	45-320.2G16	75	45-523.1900	88
17	45-320.2G18	75	45-529.2100	80
18	45-320.2G46	76	45-530.2100	81
19	45-320.2H12	75	45-533.2100	81
22	45-320.2H16	75	45-534.2100	81
31	45-320.2H18	75	45-536.2100	81
41	45-320.2H41	76	45-539.2400	87
45	45-320.2H42	76	45-539.2800	87
51	45-320.2J11	75	45-542.1K00	84
56	45-320.2J12	75	45-543.1K00	84
57	45-320.2J16	75	45-544.1K00	84
61	45-320.2J18	75	45-545.1K00	84
70	45-320.2J41	76	45-546.1K00	84
71	45-320.2N11	75	45-547.1K00	84
82	45-320.2N12	75	45-548.1K00	84
84	45-320.2N16	75	45-549.1400	87
92	45-320.2N18	75	45-549.1800	87
96	45-320.2N41	76	45-550.1400	87
	45-320.2N42	76	45-552.0K00	64
	45-320.2N46	76	45-553.0200	64
	45-320.2N48	76	45-553.0400	64
	45-320.3H60	77	45-553.0500	64
	45-320.3N60	77	45-553.0600	64
	45-330.1115	88	45-553.0900	64
	45-330.2115	88	45-553.0E00	64
	45-36F.1114	78	45-553.0F00	64
	45-410.1401	90	45-553.0G00	64
	45-410.2403	90	45-553.0H00	64
	45-420.1401	90	45-553.0J00	64
	45-420.2403	90	45-553.0K00	64
	45-420.2803	90	45-553.0N00	64
	45-430.1801	90	45-555.1100	86
	45-430.2803	90	45-555.1K00	86
	45-440.1801	90	45-558.0000	65
	45-440.2803	90	45-560.1100	87
	45-450.1801	90	45-561.1400	82
	45-450.2803	90	45-561.140P	82
	45-460.1802	90	45-562.1400	82
	45-460.2804	90	45-564.1102	85
	45-470.1802	90	45-564.1110	85
	45-470.2804	90	45-567.1103	85
	45-481.1810	36	45-567.1111	85
	45-481.2810	36	45-569.1105	85
	45-482.1810	36	45-569.1112	85
	45-482.2810	36	45-570.1105	85
	45-501.2000	90	45-573.1102	82
	45-506.1100	83	45-573.1103	82
	45-506.2A00	83	45-573.1104	82
	45-507.1100	92	45-573.1105	82
	45-509.1100	92	45-573.1202	82
	45-50C.1900	93	45-573.1A02	82
	45-50C.2900	93	45-573.1A03	82
	45-50D.1900	93	45-573.1A04	82
	45-50D.2900	93	45-573.1A05	82
	45-50E.1900	93	45-574.0600	79
	45-50E.2900	93		
	45-50F.1100	84		
	45-50F.2900	93		
	45-50G.0900	92		
	45-50J.1400	82		
	45-50J.140P	82		
	45-50J.140Q	82		
	45-50J.140S	82		
	45-50J.140T	82		
	45-50J.140V	82		
	45-50J.140W	82		
	45-50J.140X	82		
	45-50J.140Z	82		
	45-50K.1407	82		
	45-50K.1408	82		
	45-50N.1100	86		
	45-50P.0100	86		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

EAO:

[45-2J31.16V0.000](#) [45-2N39.1010.000](#) [45-2D36.2820.000](#) [45-2N42.1010.000](#) [45-2J31.26T0.000](#) [45-2N42.3010.000](#)
[45-2J31.26V0.000](#) [45-2D36.1820.000](#) [45-2N42.2010.000](#) [45-2N39.3010.000](#) [45-312.1X10](#) [45-315.1Z40](#) [45-](#)
[314.1Z10](#) [45-313.1Z10](#) [45-2K31.36V0.000](#) [45-2K31.15V0.000](#) [45-2J31.15V0.000](#) [45-2J31.25T0.000](#) [45-530.2100](#)
[45-2K31.16T0.000](#) [45-2J31.15T0.000](#) [45-2K31.15T0.000](#) [45-2K31.16V0.000](#) [45-2K31.36T0.000](#) [45-2K31.35T0.000](#)
[45-2H00.1016.000](#) [45-50P.0100](#) [45-2K31.35V0.000](#) [45-2J31.25V0.000](#) [45-2H00.1017.000](#) [45-2J31.35T0.000](#) [45-](#)
[2H00.2018.000](#) [45-2J31.36T0.000](#) [45-2J31.36V0.000](#)