


DS Series Interlock Snap Switches

Features/Benefits

- Snap-in mounting
- Reliable snap action mechanism
- Latch or momentary
- RoHS compliant
- Halogen free material

Typical Applications

- Interlock switch
- Detection switch
- Circuit interrupt



UL61058-1

Specifications

FUNCTION: Single pole double throw / Double pole double throw
MOUNTING TYPE: Snap in style

Electrical

ELECTRICAL LIFE: see ratings chart below
DIELECTRIC STRENGTH: 1500 V (50-60 Hz @ sea level)
INSULATION RESISTANCE: 100 M Ω min.
INITIAL CONTACT RESISTANCE: 30 milli-ohms

Materials

HOUSING, COVER, ACTUATOR, KNOB: PA 66/6 halogen free, UL94V-0
NO & NC FIXED TERMINALS: Copper alloy
COMMON TERMINALS: Copper alloy, silver plate
CONTACTS: Silver alloy / F5 rating gold plated over silver alloy
RETURN SPRINGS: Stainless steel

Operating Environment

OPERATING TEMPERATURE: -40°C to +85°C

NOTE: Specifications and materials listed above are for switches with standard options.
For information on specific and custom switches, please contact Customer Service.

Build-A-Switch

To order, simply select desired option from each category and place in the appropriate box.

D S													
Designation												Housing Color	
DS DS Series												NONE White	
Number of Poles												B Black	
1 SPDT												Terminals	
2 DPDT												Q1 4.8 x 0.5	
Rating												Q2 4.8 x 0.8	
F5 0.1 (0.5)A @ 125/250 V AC 50/60 Hz 50E3												Q3 6.3 x 0.8	
F7 0.1 (0.5)A @ 125/250 V AC 50/60 Hz 10E4												Actuator Style	
D6 10 (4)A @125/250 V AC 50/60 Hz 50E3												A Momentary, Short button	
10A G.P. @ 125 / 250 V AC 1/3HP @ 125/250 V AC												B Momentary, Long button	
50/60 Hz 10E3												C Momentary/Pulled out button (not available on D7 rating)	
D7* 16A G.P. @125/250 V AC 3/4HP 125/250 V AC													
50/60 Hz 10E3													
16 (6) A @125/250 V AC 50/60 Hz 10E3													
* Note - 16A version has Q3 terminals only													

International Rating Symbols





10E3	Cycles 10,000
10E4	Cycles 100,000
50E3	Cycles 50,000
10(4)	Current rating: First number represents resistive rating. Second number represents inductive (motor) rating
GP	General purpose rating UL1054



DS Series Interlock Snap Switches





NUMBER OF POLES

1 SPDT




PANEL MOUNTING		
PANEL THICKNESS	DIM "A" mm	DIM "B" mm
1.14	28.32	13.97
2.54	28.58	13.97

2 DPDT




PANEL MOUNTING		
PANEL THICKNESS	DIM "A" mm	DIM "B" mm
1.14	36.70	13.97
2.54	36.96	13.97




ACTUATOR STYLE / SPECIFICATIONS

A SHORT BUTTON




SHORT BUTTON

B LONG BUTTON




LONG BUTTON

C MOMENTARY/PULLED OUT



FREE POSITION



PULLED OUT POSITION

SPDT Specification


BUTTON STYLE	OVER TRAVEL POSITION PUSH MAX	OVER TRAVEL POSITION PULL MAX	OPERATING POSITION PUSH	OPERATING POSITION PULL	FREE POSITION AT REST	OPERATING FORCE	
A	3.20	NA	8.90 ± 1.25	NA	11.45 ± 0.75	425 gf	
B	10.15	NA	19.55 ± 1.25	NA	22.25 ± 0.75	425 gf	
C	13.20	24.90	16.75 ± 1.25	21.60 ± 1.25	19.30 ± 0.75	PUSH 385gf	PULL 475gf

DPDT Specification


BUTTON STYLE	OVER TRAVEL POSITION PUSH MAX	OVER TRAVEL POSITION PULL MAX	OPERATING POSITION PUSH	OPERATING POSITION PULL	FREE POSITION AT REST	OPERATING FORCE	
A	3.20	NA	8.90 ± 1.25	NA	11.45 ± 0.75	680 gf	
B	10.15	NA	19.55 ± 1.25	NA	22.25 ± 0.75	680gf	
C	13.20	24.90	16.75 ± 1.25	21.60 ± 1.25	19.30 ± 0.75	PUSH 560gf	PULL 750gf

TERMINALS

Q1 4.8 x 0.5
Q2 4.8 x 0.8



Q3 6.3 x 0.8



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

C&K Switches:

[DS1F5AQ1](#) [DS2F5AQ3](#) [DS1F5BQ1](#) [DS2D6BQ2](#) [DS2F5CQ1](#) [DS1D6AQ1](#) [DS2D6AQ2](#) [DS2F5BQ1](#) [DS1F5CQ2](#)
[DS1D6AQ3](#) [DS2F5BQ3](#) [DS2D6CQ3](#) [DS1F5BQ2](#) [DS1D6AQ2](#) [DS2F5CQ2](#) [DS1F5AQ2](#) [DS1D6BQ2](#) [DS2D6AQ3](#)
[DS1F5CQ3](#) [DS2D6BQ3](#) [DS1D6BQ1](#) [DS2D6CQ2](#) [DS1D6CQ1](#) [DS1D6BQ3](#) [DS2D6CQ1](#) [DS1D6CQ3](#) [DS1F5BQ3](#)
[DS2D6AQ1](#) [DS2D6BQ1](#) [DS2F5AQ1](#) [DS1D6CQ2](#) [DS2F5CQ3](#) [DS2F5AQ2](#) [DS1F5CQ1](#) [DS1F5AQ3](#) [DS2F5BQ2](#)
[DS1D7BQ3](#) [DS2D7BQ3](#) [DS2D7AQ3](#) [DS1D7AQ3](#)