



# Raspberry Pi 4 Computer Model B




Published in June 2019  
by Raspberry Pi Trading Ltd.

[www.raspberrypi.org](http://www.raspberrypi.org)



Raspberry Pi

# Overview



Raspberry Pi 4 Model B is the latest product in the popular Raspberry Pi range of computers. It offers ground-breaking increases in processor speed, multimedia performance, memory, and connectivity compared to the prior-generation Raspberry Pi 3 Model B+, while retaining backwards compatibility and similar power consumption. For the end user, Raspberry Pi 4 Model B provides desktop performance comparable to entry-level x86 PC systems.


This product's key features include a high-performance 64-bit quad-core processor, dual-display support at resolutions up to 4K via a pair of micro-HDMI ports, hardware video decode at up to 4Kp60, up to 4GB of RAM, dual-band 2.4/5.0 GHz wireless LAN, Bluetooth 5.0, Gigabit Ethernet, USB 3.0, and PoE capability (via a separate PoE HAT add-on).

The dual-band wireless LAN and Bluetooth have modular compliance certification, allowing the board to be designed into end products with significantly reduced compliance testing, improving both cost and time to market.

# Specification


<b>Processor:</b>	Broadcom BCM2711, quad-core Cortex-A72 (ARM v8) 64-bit SoC @ 1.5GHz
<b>Memory:</b>	1GB, 2GB or 4GB LPDDR4-2400 SDRAM (depending on model)
<b>Connectivity:</b>	2.4 GHz and 5.0 GHz IEEE 802.11b/g/n/ac wireless LAN, Bluetooth 5.0, BLE Gigabit Ethernet 2 × USB 3.0 ports 2 × USB 2.0 ports.
<b>GPIO:</b>	Standard 40-pin GPIO header (fully backwards-compatible with previous boards)
<b>Video &amp; sound:</b>	2 × micro HDMI ports (up to 4Kp60 supported) 2-lane MIPI DSI display port 2-lane MIPI CSI camera port 4-pole stereo audio and composite video port
<b>Multimedia:</b>	H.265 (4Kp60 decode); H.264 (1080p60 decode, 1080p30 encode); OpenGL ES, 3.0 graphics
<b>SD card support:</b>	Micro SD card slot for loading operating system and data storage
<b>Input power:</b>	5V DC via USB-C connector (minimum 3A <sup>1</sup> ) 5V DC via GPIO header (minimum 3A <sup>1</sup> ) Power over Ethernet (PoE)–enabled (requires separate PoE HAT)
<b>Environment:</b>	Operating temperature 0–50°C
<b>Compliance:</b>	For a full list of local and regional product approvals, please visit <a href="https://www.raspberrypi.org/documentation/hardware/raspberrypi/conformity.md">https://www.raspberrypi.org/documentation/hardware/raspberrypi/conformity.md</a>
<b>Production lifetime:</b>	The Raspberry Pi 4 Model B will remain in production until at least January 2026.





HDMI is a trademark of HDMI Licensing, LLC  
MIPI DSI and MIPI CSI are service marks of MIPI Alliance, Inc  
Raspberry Pi and the Raspberry Pi logo are trademarks of the Raspberry Pi Foundation

[www.raspberrypi.org](http://www.raspberrypi.org)



**Raspberry Pi**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Raspberry Pi:](#)

[RPI4-MODBP-4GB-BULK](#) [RPI4-MODBP-1GB](#) [RPI4-MODBP-2GB-BULK](#) [RPI4-MODBP-8GB-BULK](#)