

Standard Sample Kit

<u>SL03 10001</u> Max Dia = 3.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 1.00 A Energy = 2.0 J	<u>SL05 10001</u> Max Dia = 5.0mm $\pm$ 10 % R@25°C = 10Ω $\pm$ 15% SSI = 1.00 A Energy = 6.0 J	<u>SL08 10002</u> Max Dia = 8.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 2.00 A Energy = 10 J	<u>SL10 10003</u> Max Dia = 10mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 3.00 A Energy = 17 J
<u>SL12 10005</u> Max Dia = 12.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 5.00 A Energy = 60 J <u>SL15 10006</u> Max Dia = 15.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 6.00 A Energy = 55 J	<u>SL18 10005</u> Max Dia = 19.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 5.00 A Energy = 75 J	<u>SL22 10008</u> Max Dia = 21.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 8.00 A Energy = 90 J	<u>SL32 10015</u> Max Dia = 31.0mm $\pm$ 10% R@25°C = 10Ω $\pm$ 20% SSI = 15.0 A Energy = 150 J

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[STD sample kit](#)