


REV	DATE	ECO#
A	09/06/90	1140
B	05/26/94	1314

DRAWING NOT TO SCALE  
ALL DIMENSIONS IN INCHES



#### SPECIFICATIONS:

RESISTANCE AT 25 DEG C = 10 OHMS +/- 15%  
 MAXIMUM CONTINUOUS CURRENT ( $I_{max}$ ) = 6 AMPS  
 RESISTANCE AT  $I_{max}$  = 0.15 OHMS NOMINAL  
 MAXIMUM VOLTAGE RATING = 265 VAC RMS  
 MAXIMUM SURGE RATING = 40 JOULES  
 MARKING = OPTIONAL  
 ENCAPSULATION = SILICONE RESIN  
 LEADS = RODAN P/N STL-209-37

DRAWN BY D. NGUYEN		<b>AMETHERM</b> <i>Circuit Protection Thermistors</i>
DATE 08/21/80	ORIG. F. TISED	
REV B	APP	SURGE-GARD INRUSH CURRENT LIMITER
SHEET 1 OF 1		SG27

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SG27](#)