



REV	DATE	ECO#
A	01/27/92	1194

DRAWING NOT TO SCALE
ALL DIMENSION IN INCHES



SPECIFICATIONS:

RESISTANCE AT 25 DEG C = 1 OHM +/- 15%
 MAX CONTINUOUS CURRENT (I_{max}) = 20 AMPS
 RESISTANCE AT I_{max} = 0.015 OHMS NOMINAL
 MAX VOLTAGE RATING = 120 VAC (RMS)
 MAX SURGE RATING = 48 JOULES
 ENCAPSULATION = SILICONE RESIN
 MARKING = OPTIONAL
 LEADS = RODAN P/N STL 209-45

DRAWN BY D. NGUYEN		<div>AMETHERM</div> <div><i>Circuit Protection Thermistors</i></div>
DATE 09/25/90		
REV A	APP.	SURGE-GARD INRUSH CURRENT LIMITER
SHEET 1 OF 1		SG301

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SG301](#)