



REV	DATE	ECD#
A	03/31/95	1342

DRAWING NOT TO SCALE
ALL DIMENSIONS IN INCHES



SPECIFICATIONS:

RESISTANCE AT 25 DEG C = 2 OHMS +/- 15%

MAX CONTINUOUS CURRENT (I_{max}) = 18 AMPS

RESISTANCE AT I_{max} = 0.03 OHMS NOMINAL

MAX VOLTAGE RATING = 265 VAC (RMS)

MAX SURGE RATING = 80 JOULES

ENCAPSULATION = SILICONE RESIN

MARKING = OPTIONAL

LEADS = RODAN P/N STL-209-45

DRAWN BY D. NGUYEN		AMETHERM <i>Circuit Protection Thermistors</i>
DATE 09/25/90	ORIG. F. TISED	
REV A	APP	SURGE-GARD INRUSH CURRENT LIMITER
SHEET 1 OF 1		SG302

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SG302](#)