


REV	DATE	ECO#
C	12/14/92	1232
D	02/28/05	27656

DRAWING NOT TO SCALE
ALL DIMENSIONS IN INCHES



SPECIFICATIONS:

RESISTANCE AT 25 DEG C = 12 OHMS +/- 10%
 MAXIMUM CONTINUOUS CURRENT (I_{max}) = 4.0 AMPS
 RESISTANCE AT I_{max} = 0.22 OHMS NOMINAL
 MAXIMUM VOLTAGE RATING = 265 VAC (RMS)
 MAXIMUM SURGE RATING = 40 JOULES
 ENCAPSULATION = SILICONE RESIN
 LEADS = RTI P/N STL-209-37
 MARKING = OPTIONAL

DRAWN BY D. NGUYEN		AMETHERM <i>Circuit Protection Thermistors</i>
DATE 06/15/88	ORIG. F. TISED	
REV D	APP	SURGE-GARD INRUSH CURRENT LIMITER
SHEET 1 OF 1		SG39

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SG39](#)