


Mechanical Specifications

D	20.0mm $\pm$ 1.0mm
T	6.0mm Max
Lead Diameter	1.0mm $\pm$ 0.1mm
S	9.5mm $\pm$ 0.5mm
L	42.0mm Nom
B	9.2mm $\pm$ 0.5mm
C	3.9mm $\pm$ 1.0mm



Electrical Specifications

Resistance @ 25°C	5.0 Ω $\pm$ 20%
Max Steady State Current Up to 65°C	12.0 A
Max recommended energy rating (Joules)	100.0 J
Max Capacitance @ 120 VAC	6400 μ F
Max Capacitance @ 240 VAC	1500 μ F
Resistance @ 100% of Max Current	0.054 Ω
Resistance @ 50% of Max Current	0.120 Ω
Body Temperature @ 100% Current rating	214°C
Dissipation Constant	32.4mW/°C
Thermal Time Constant	94 seconds
Material Type (for Beta and Curve)	G

Revision	Date	Change
0	10/31/08	Issue
1	4/4/23	Revised mechanical dimensions

Ametherm, Inc
961 Fairview Drive
Carson City, NV 89701
Telephone: **800-808-2434**
Fax: 775 884-0670
www.Ametherm.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL22 5R012-B](#) [SL225R012B](#)