




File: E209153



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	31.0	± max
T:	9.3	± max
Lead Diameter	1.0	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	6.0	± max
B:	7.80	± nom
C:	6.75	± nom



Electrical Specifications

Resistance:	10.0 Ω	± 25 %
Max Steady State Current upto 65°C:	15.00	A
Max Rec. Energy Rating:	250	J
Actual Failure Instantaneous Energy:	500	J
Maximum Capacitance @ 120 VAC:	19,250	μ f
Maximum Capacitance @ 240 VAC:	4,341	μ f
Maximum Capacitance @ 440 VAC:	1,003	μ f
Maximum Capacitance @ 680 VAC:	500	μ f
Resistance @ 100% Max Current:	0.00	Ω
Resistance @ 50% Max Current:	0.22	Ω
Body Temperature at 100% Max Current:	224.00	°C
Dissipation Constant:	63.7	mw/°C
Thermal Time Constant:	194	Sec.
Material Type (for Beta and Curve):	H	

MS32 10015

Date: 11/11/2008	Drawn by: Erin Landis
Ametherm, Inc. 961 Fairview Drive Carson City, Nevada USA 89701 www.ametherm.com	Approved By: Mehdi Samii
	Revision: A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[MS32 10015](#)