




File: E209153



ISO9001:2008 Certified

Mechanical Specifications (mm)

D:	13.0	± max
T:	4.5	± max
Lead Diameter	0.8	± nom
S:	7.8	± nom
L:	38.0	± nom
Coating Lead Run Down (straight Leads)	3.0	± max
B:	5.65	± nom
C:	2.15	± nom



Electrical Specifications

Resistance:	1.3	Ω	± 20 %
Max Steady State Current upto 65°C:	8.00	A	
Max Rec. Energy Rating:	40	J	
Actual Failure Instantaneous Energy:	80	J	
Maximum Capacitance @ 120 VAC:	2,778	µf	
Maximum Capacitance @ 240 VAC:	694	µf	
Resistance @ 100% Max Current:	0.04	Ω	
Resistance @ 50% Max Current:	0.09	Ω	
Body Temperature at 100% Max Current:	150.00	°C	
Dissipation Constant:	13.2	mw/°C	
Thermal Time Constant:	40	Sec.	
Material Type (for Beta and Curve):	A		

SL12 1R308

Date: 11/11/2008

Drawn by: Erin Landis

Ametherm, Inc.
3111 N. Deer Run Road
Carson City, Nevada USA 89701
www.ametherm.com

Approved By: Mehdi Samii

Revision: a

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL12 1R308](#)