


Part Number: SL32 0R540

Ordering Different Lead Types:

Inside Kinked Leads	Not Available
Outside Kinked Leads	Use -B after Ametherm's part #

For example: to order an inside kinked lead use part number SL32 0R540-B



Electrical Specifications:

Resistance @ 25°C	0.5 $\Omega \pm 20\%$
Max Steady State Current Up to 65°C	40.0 A
Max Recommended Energy Rating (Joules)	250.0 J
Actual Failure Point of Instantaneous Energy (Joules)	495.0 J
Resistance @ 100% of Max Current	0.008 Ω
Resistance @ 50% of Max Current	0.038 Ω
Body Temperature @ 100% Current Rating	234 °C
Dissipation Constant	45.4Mw/°C
Thermal Time Constant	194 seconds
Material Type	"B"
Max Recommended Capacitance @ 240/440 VAC	4000 μ F/1250 μ F

Mechanical Specifications:

D	30.0 \pm 2.5 mm
T	5.0 \pm 1.0 mm
Lead Diameter	1.0 \pm 0.1 mm
S	7.8 \pm 2.0 mm
L	38.0 \pm 9.0 mm
Straight Leads Coating Run Down	5.0 \pm 1.0 mm
B	11.5 \pm 3.50 mm
C	3.82 \pm 1.0 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Ametherm:](#)

[SL32 0R540](#)