

PJT

Highlights & Features

- Universal AC input voltage
- Standard industrial foot print of 2" x 3"
- Low leakage current < 0.1 mA
- Convection cooled operating temperature range from -10°C to +70°C
- High MTBF > 700,000 hrs as per Telcordia SR-332
- Multiple connector source options

Safety Standards



CB Certified for worldwide use

Model Number: Unit Weight:

PJT-DDV40WBAD 0.08 kg (0.18 lb) Dimensions (L x W x H): 76.2 x 50.8 x 22.9 mm [2" x 3"]

General Description

The PJT open frame power supply series offers choices of 12 V, 15 V, 18 V and 24 V nominal output voltages. The single output products are designed with small standard industrial foot prints at 2" x 3". The highly efficient convection cooling designs enable optimum thermal management for high power efficiency. The PJT series of products can operate from -10°C to +70°C across the entire input voltage range of 90 to 264 Vac and are certified for safety standard according to IEC/EN/UL 62368-1 and for EMI standard according to EN/BS EN 55032, Class B.

Model Information

PJT Open Frame Power Supply

Model Number	Input Voltage Range	Rated Output Voltage	Rated Output Current
PJT-12V40WBA	90-264 Vac	12 Vdc	3.33 A
PJT-15V40WBA□		15 Vdc	2.67 A
PJT-18V40WBA		18 Vdc	2.22 A
PJT-24V40WBA□	24 Vdc	1.66 A	

Model Numbering

PJ	Т —	<u>XX </u> V	40 W	В	Α	
Open Frame	Product Type T – ITE Application Series	Output Voltage 12 V 15 V 18 V 24 V	Output Power	Package Type B – Open Frame	Family Code A	Harness Connector A – JST connector B – Molex connector* C – JWT connector*

*Options



1

Specifications

	Model Number	PJT-12V40WBA	PJT-15V40WBA	PJT-18V40WBA	PJT-24V40WBA	
Input Ratings / Characteristics						
Nominal Input Voltage	100-240 Vac					
Input Voltage Range		90-264 Vac				
Nominal Input Frequency		50-6 0Hz				
Input Frequency Range		47-63 Hz				
Input Current		< 0.85 A typ. @ 1	115 Vac			
Efficiency at 100% Load	115 Vac	85.0% typ.	86.0% typ.	86.0% typ.	86.0% typ.	
	230 Vac	86.0% typ.	87.0% typ.		87.0% typ.	
Max Inrush Current (Cold Start)		30 A typ. @ 115 \	/ac, 60 A typ. @ 2	30 Vac		
Leakage Current		0.1 mA @ 240 Va	C			
Output Ratings / Characteristics						
Nominal Output Voltage	Iominal Output Voltage 12 Vdc 15 Vdc 18 Vdc 24 Vdc					
Factory Set Point Tolerance		No potentiometer (± 5%)				
Output Current		3.33 A	2.67 A	2.22 A	1.66 A	
Output Power		40 W				
Line Regulation		± 0.5% @ 115 Vac & 230 Vac				
Load Regulation		± 1.0% @ 115 Vac & 230 Vac				
PARD* (20 MHz)		< 120 mVpp	< 150 mVpp	< 180 mVpp	< 240 mVpp	
Start-up Time	115 Vac	2800 ms typ. (100% load)				
	230 Vac	1100 ms typ. (100% load)				
Hold-up Time	115 Vac	18 ms typ. (100% load)				
230 Vac		90 ms typ. (100% load)				
Dynamic Response (Overshoot & Undershoot O/P Voltage)		± 5% @ 50-100% load (Slew Rate: 0.1A/µS)				
Start-up with Capacitive Loads	4,000uF Max	3,500uF Max	3,000uF Max	2,000uF Max		

*PARD is measured with an AC coupling mode, 5 cm wires, and in parallel with 0.1 µF ceramic capacitor & 47 µF electrolytic capacitor.

Mechanical

Dimensions		76.2 x 50.8 x 22.9 mm [2" x 3"]		
Unit Weight		0.08 kg (0.18 lb)		
Cooling System		Convection		
Power Supply Header	PJT-□□V40WBA <u>A</u>	Input: JST B2P3-VH (LF)(SN) Output: JST B4P-VH (LF)(SN)		
	PJT-□□V40WBA <u>B</u>	Input: Molex 26-62-4030 Output: Molex 26-60-4040		
	PJT-□□V40WBA <u>C</u>	Input: JWT A3963WV2-3P-D Output: JWT A3963WV2-4P		
Wire		AWG 22-18		



Environment

Surrounding Air Temperature Op		-10°C to +70°C		
	Storage	-40°C to +85°C		
Power De-rating		> 50°C de-rate power by 2.5% / °C		
Operating Humidity		10 to 95% RH (Non-Condensing)		
Operating Altitude		0 to 5,000 Meters (16,400 ft.)		
Shock Test (Non-Operating)		IEC 60068-2-27, Half Sine Wave: 50 G for a duration of 11 ms, 3 shocks for each 3 directions		
Vibration (Operating)		IEC 60068-2-6, Sine Wave: 10 Hz to 150 Hz @ 25 m/S ² (2.5 G); 10 min per cycle, 90 min per axis for all X, Y, Z direction		

Protections

13.2-18.0 V,	16.5-22.5 V,	19.8-27.0 V,	26.4-36.0 V,	
Latch Mode	Latch Mode	Latch Mode	Latch Mode	
> 140% of rated load current, Hiccup Mode,				
Non-Latching (Auto-Recovery)				
Non-Latching (Auto-Recovery)				
Hiccup Mode, Non-Latching (Auto-Recovery when the fault is removed)				
Class I with PE* connection				
	13.2-18.0 V, Latch Mode > 140% of rated I Non-Latching (Au Non-Latching (Au Hiccup Mode, No Class I with PE*	13.2-18.0 V,16.5-22.5 V,Latch ModeLatch Mode> 140% of rated load current, HiccuNon-Latching (Auto-Recovery)Non-Latching (Auto-Recovery)Hiccup Mode, Non-Latching (Auto-FeedbackClass I with PE* connection	13.2-18.0 V, Latch Mode16.5-22.5 V, Latch Mode19.8-27.0 V, Latch Mode> 140% of rated load current, Hiccup Mode, Non-Latching (Auto-Recovery)Mode, Non-Latching (Auto-Recovery)Non-Latching (Auto-Recovery)Hiccup Mode, Non-Latching (Auto-Recovery)Hiccup Mode, Non-Latching (Auto-Recovery)Class I with PE* connection	

*PE: Primary Earth

Reliability Data

MTBF	> 700,000 hrs. as per Telcordia SR-332
Expected Cap Life Time	10 years (115 Vac & 230 Vac, 50% load @ 40°C)

Safety Standards / Directives

Electrical Safety	TUV Bauart	EN 60950-1/ EN 62368-1		
	UL/cUL recognized	UL 60950-1 and CSA C22.2 No. 60950-1 (File No. E131881)		
		UL 62368-1 and CSA C22.2 No. 62368-1 (File No. E131881)		
	CB scheme	IEC 60950-1/ IEC 62368-1		
CE		In conformance with EMC Directive 2014/30/EU and		
		Low Voltage Directive 2014/35/EU		
UKCA		In conformance with Electromagnetic Compatibility Regulations 2016 and Electrical Equipment (Safety) Regulations 2016		
Galvanic Isolation	Input to Output	3.0 KVac		
	Input to Ground	2.0 KVac		
	Output to Ground	0.5 KVac		



EMC

Emissions (CE&RE)		CISPR 32, EN/BS EN 55032, FCC Title 47: Class B
Immunity to		EN/BS EN 55024
Electrostatic Discharge	IEC 61000-4-2	Criteria A ¹⁾ Level 3 Air Discharge: 8 kV Level 3 Contact Discharge: 6 kV
Radiated Field	IEC 61000-4-3	Level 2 Criteria A ¹⁾ 80 MHz-1 GHz, 3 V/M with 1 kHz tone / 80% modulation
Electrical Fast Transient / Burst	IEC 61000-4-4	Level 3 Criteria A ¹⁾ 2 kV
Surge	IEC 61000-4-5	Level 3 Criteria A ¹⁾ Common Mode ²⁾ : 2 kV Differential Mode ³⁾ : 1 kV
Conducted	IEC 61000-4-6	Level 2 Criteria A ¹⁾ 3 V with 80% AM
Power Frequency Magnetic Fields	IEC 61000-4-8	Criteria A ¹⁾ Magnetic field strength 3 A/Meter
Voltage Dips	IEC 61000-4-11	30% dip; 10 ms Criterion A 60% dip; 100 ms Criterion B 95% dip; 5000 ms Criterion B
Voltage Fluctuation and Flicker		IEC/EN/BS EN 61000-3-3

1) Criteria A: Normal performance within the specification limits

2) Asymmetrical: Common mode (Line to earth)

3) Symmetrical: Differential mode (Line to line)

Block Diagram





Dimensions

L x W x H: 76.2 x 50.8 x 22.9 mm [2" x 3"]



ltem	Device Description
1	Input Connector (CN1) Pin 1: Line Pin 2: NC Pin 3: Neutral
0	0 1 1 0 1 (0)(0)

2 Output Connector (CN2) Pin 1 to 2 : V(+) Pin 3 to 4 : V(-)



Engineering Data

Output Load De-rating VS Surrounding Air Temperature



> 50°C de-rate power by 2.5% / °C

Output Load De-rating VS Input Voltage



Note

- 1. Power supply components may degrade, or be damaged, when the power supply is continuously used outside the shaded region, refer to the graph shown in Fig. 1.
- 2. If the output capacity is not reduced when the surrounding air temperature >50°C, the device will run into Over Temperature Protection. When activated, the output voltage will go into bouncing mode and will recover when the surrounding air temperature is lowered or the load is reduced as far as necessary to keep the device in working condition.
- 3. Depending on the surrounding air temperature and output load delivered by the power supply, the device can be very hot!
- 4. If the device has to be mounted in any other orientation, please contact **info@deltapsu.com** for more details.
 - No output power de-rating for the input voltage from 90 Vac to 264 Vac
 - L Frame / Enclosed



Assembly & Installation

Any excessive twisting or bending may damage the device's PCB. Please handle the device with care.





Use cable of AWG No. 22-18. Please refer to Table 1 for the recommended Mating Connector and Terminal.

Table 1	Input / Output	Power Supply Header	Mating Connector	Terminal
A – JST connector	Input	B2P3-VH (LF)(SN)	VHR-3N	SVH-21T-P1.1
	Output	B4P-VH (LF)(SN)	VHR-4N	SVH-21T-P1.1
B – Molex connector	Input	26-62-4030	09-50-3031	08-52-0071
	Output	26-60-4040	09-50-3041	08-52-0071
C – JWT connector	Input	A3963WV2-3P-D	A3963H02-3P	A3963TOP-2
	Output	A3963WV2-4P	A3963H02-4P	A3963TOP-2

Safety Instructions

- If the device has to be mounted in any other orientation, please contact info@deltapsu.com for more details.
- The device is not recommended to be placed on surface with low thermal conductivity, such as plastics, for example.
- For safety reasons, please ensure the mounted device is kept at ≥ 4 mm (0.16 inch) safety distance at all sides from other components and equipments. Please insert an insulation sheet between the system and product, if the safety distance is less than 4mm. In addition, to ensure sufficient convection cooling, always maintain a distance of ≥ 20 mm (0.79 inch) from ventilated surfaces while the device is in operation.
- Note that the device can become very hot depending on the ambient temperature and load of the power supply. Do not touch the device while it is in operation or immediately after power is turned OFF. Risk of burning!
- Do not touch the terminals while power is being supplied. Risk of electric shock.
- Prevent any foreign metal, particles or conductors from entering the device through the openings during installation. It may cause: Electric shock; Safety Hazard; Fire; Product failure
- The power supply must be mounted by metal screws onto a grounded metal surface. It is highly recommended that the Earth terminal on the connector be connected to the grounded metal surface.



7

Functions

Start-up Time

The time required for the output voltage to reach 90% of its final steady state set value, after the input voltage is applied.

Rise Time

The time required for the output voltage to change from 10% to 90% of its final steady state set value.

Hold-up Time

Time between the collapse of the AC input voltage, and the output falling to 95% of its steady state set value.

Graph illustrating the Start-up Time, Rise Time, and Hold-up Time



Inrush Current

Inrush current is the peak, instantaneous, input current measured and, occurs when the input voltage is first applied. For AC input voltages, the maximum peak value of inrush current will occur during the first half cycle of the applied AC voltage. This peak value decreases exponentially during subsequent cycles of AC voltage.



Dynamic Response

The power supply output voltage will remain within $\pm 5\%$ of its steady state value, when subjected to a dynamic load from 0 to 100% of its rated current.





Overload & Overcurrent Protections (Auto-Recovery)

The power supply's Overload (OLP) and Overcurrent (OCP) Protections will be activated when output current exceeds 140% of I_0 (Max load). In such occurrence, the V_0 will start to droop and once the power supply has reached its maximum power limit, the protection is activated and the power supply will go into "Hiccup mode" (Auto-Recovery). The power supply will recover once the fault condition of the OLP and OCP is removed and I_0 is back within the specifications.



It is not recommended to prolong the duration of I_0 when it is <140% but >100%, since it may cause damage to the PSU.

Short Circuit Protection (Auto-Recovery)

The power supply's output OLP/OCP function also provides protection against short circuits. When a short circuit is applied, the output current will operate in "Hiccup mode", as shown in the illustration in the OLP/OCP section on this page. The power supply will return to normal operation after the short circuit is removed.

Others

Attention

Delta provides all information in the datasheets on an "AS IS" basis and does not offer any kind of warranty through the information for using the product. In the event of any discrepancy between the information in the catalog and datasheets, the datasheets shall prevail (please refer to www.DeltaPSU.com for the latest datasheets information). Delta shall have no liability of indemnification for any claim or action arising from any error for the provided information in the datasheets. Customer shall take its responsibility for evaluation of using the product before placing an order with Delta.

Delta reserves the right to make changes to the information described in the datasheets without notice.

Manufacturer and Authorized Representatives Information

Manufacturer

<u>Thailand</u> Delta Electronics (Thailand) PCL. 909 Pattana 1 Rd., Muang, Samutprakarn, 10280 Thailand

Authorized Representatives

<u>The Netherlands</u> Delta Greentech (Netherlands) B.V. Zandsteen 15, 2132 MZ Hoofddorp, The Netherlands

Overvoltage Protection (Latch Mode)

The power supply's overvoltage circuit will be activated when its internal feedback circuit fails. The output voltage shall not exceed its specifications defined on Page 3 under "Protections". Power supply will latch off, and require removal/re-application of input AC voltage in order to restart.

The power supply should be latch.



Over Temperature Protection (Auto-Recovery)

As described in load de-rating section, the power supply also has Over Temperature Protection (OTP). In the event of a higher operating temperature at 100% load, the power supply will run into OTP when the operating temperature is beyond what is recommended in the de-rating graph. When activated, the output voltage will go into bouncing mode until the temperature drops to its normal operating temperature as recommended in the de-rating graph.

Taiwan Delta Electronics, Inc. 3 Tungyuan Road, Chungli Industrial Zone, Taoyuan County 32063, Taiwan

<u>United Kingdom</u> Delta Electronics Europe Limited 1 Redwood Court, Peel Park Campus, East Kilbride, Glasgow, G74 5PF, United Kingdom



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delta Electronics: PJT-18V40WBAA