



### FEATURES

- 1.8 V analog and digital core supply voltage
- Serial data link with reduced range LVDS outputs
- Correlated double sampler (CDS) with  $-3$  dB,  $0$  dB,  $+3$  dB, and  $+6$  dB gain
- $6$  dB to  $42$  dB,  $10$ -bit variable gain amplifier (VGA)
- $14$ -bit,  $65$  MHz ADC
- Black level clamp with variable level control
- Complete on-chip timing generator
- Precision Timing* core with  $240$  ps resolution at  $65$  MHz
- On-chip,  $3$  V horizontal and RG drivers
- $5$  mm  $\times$   $5$  mm,  $32$ -lead LFCSP\_VQ

### APPLICATIONS

- Professional HDTV camcorders
- Professional/high end digital cameras
- Broadcast cameras
- Industrial high speed cameras
- High speed data acquisition systems

### GENERAL DESCRIPTION

The **AD9970** is a highly integrated CCD signal processor for high speed digital video camera applications. Specified at pixel rates of up to  $65$  MHz, the **AD9970** consists of a complete analog front end with analog-to-digital conversion combined with a programmable timing driver. The *Precision Timing* core allows adjustment of high speed clocks with  $240$  ps resolution at  $65$  MHz operation. The **AD9970** also contains a reduced range LVDS interface for data outputs.

The analog front end includes black level clamping, CDS, VGA, and a  $65$  MSPS,  $14$ -bit ADC. The timing driver provides the high speed CCD clock drivers for RG, HL, and H1 to H4. Operation is programmed using a  $3$ -wire serial interface.

Packaged in a space-saving  $5$  mm  $\times$   $5$  mm,  $32$ -lead LFCSP\_VQ, the **AD9970** is specified over an operating temperature range of  $-25^{\circ}\text{C}$  to  $+85^{\circ}\text{C}$ .

For more information about the **AD9970**, contact Analog Devices via email at [afe.ccd@analog.com](mailto:afe.ccd@analog.com).

### FUNCTIONAL BLOCK DIAGRAM




Figure 1.

**NOTES**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[AD9970BCPZ](#) [AD9970BCPZRL](#) [AD9970BCPZRL7](#)