

SOLENOID PRODUCT SPECIFICATION


PART No.	VOLTAGE	DUTY CYCLE	POWER (W)	CURRENT (A)	DCR (Ω) *
DSOL-0630-05C	5 VDC	100%	4	0.8	6
DSOL-0630-05E	5 VDC	25%, 60sec On	8.2	1.6	3.2
DSOL-0630-12C	12 VDC	100%	4	0.4	36
DSOL-0630-12E	12 VDC	25%, 60sec On	8.5	0.7	17
DSOL-0630-18C	18 VDC	100%	4.8	0.27	66
DSOL-0630-18E	18 VDC	25%, 60sec On	8.5	0.48	38
DSOL-0630-24C	24 VDC	100%	4	0.2	144
DSOL-0630-24E	24 VDC	25%, 60sec On	8.5	0.4	68

* OPERATION: POWER TO PULL , NO RETURN SPRING.


* DCR VALUES ARE $\pm 10\%$ AT 25°C

* WEIGHT ARE 80 GRAMS $\pm 10\%$

1. MECHANICAL DIMENSIONS :



2. SCHEMATIC AND CONSTRUCTION :



INSULATION MATERIALS: UL CONSTRUCTION, CLASS B 130°C
LIFE EXPECTANCY: 100K CYCLES OPERATIONS

LAYER TEST	IR. @500 Vdc.	HI-POT
(S-F) 500Vp. MIN.	COIL TO FRAME	@50/60Hz.,2mA
TEST ONLY COIL	50 MOHM MIN.	COIL TO FRAME
		1200Vac.,1s

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delta Electronics:

[DSOL-0630-05C](#) [DSOL-0630-05E](#) [DSOL-0630-12C](#) [DSOL-0630-12E](#) [DSOL-0630-18C](#) [DSOL-0630-18E](#) [DSOL-0630-24C](#) [DSOL-0630-24E](#)