

DEMO MANUAL DC1513B

LTM9004 14-Bit Direct Conversion Receiver Subsystem

DESCRIPTION

Demonstration circuit 1513 is an evaluation board featuring Linear Technology Corporation's LTM®9004 14-bit direct conversion receiver subsystem. DC1513 demonstrates good circuit layout techniques and recommended external circuitry for optimal system performance.

DC1513 comes with Linear Technology's 14-bit LTM9004 receiver subsystem installed. The board includes output CMOS buffers. DC1513 plugs into the DC890 data

acquisition demo board and the output can be easily analyzed with Linear Technology's PScope[™] data processing software, which is available for no charge on our website at http://www.linear.com/software.

Design files for this circuit board are available at http://www.linear.com/demo

∠ , LT, LTC, LTM, Linear Technology and the Linear logo are registered trademarks and PScope is a trademark of Linear Technology Corporation. All other trademarks are the property of their respective owners.

Table 1. DC1513B Variants

DC1513B VARIANTS	RESOLUTION	MAXIMUM SAMPLE RATE	BASEBAND BANDWIDTH	
1513B-AA	14-Bit	125Msps	DC - 1.92MHz	
1513B-AB	14-Bit	125Msps	DC - 4.42MHz	
1513B-AC	14-Bit	125Msps	DC - 9.42MHz	
1513B-AD	14-Bit	125Msps	DC - 20MHz	

QUICK START PROCEDURE

Validating the performance of the LTM9004 is simple with DC1513, and requires only two input sources, a clock source, a computer, and a lab power supply. Refer to Figure 1 for proper board evaluation equipment setup and follow the procedure below:

- Connect the power supply as shown in Figure 1. There are onboard low noise voltage regulators that provide the two supply voltages for the DC1513. The entire board and all components share a common ground. The power supply should still be a low noise lab power supply capable of supplying at least 0.5A at 5VDC, and 1A at 3VDC.
- Provide an encode clock to the ADC via SMA connector J7. Use a low-phase-noise clock source such as a filtered RF signal generator or a high quality clock oscillator.

NOTE: Similar to having a noisy input, a high jitter (phase noise) encode clock will degrade the signal-to-noise ratio (SNR) of the system.

Table 2. DC1513 Connectors and Jumpers

REFERENCE	FUNCTION
J3 (SHDN)	Enables/Disables the ADC. Default Is ON.
J4 (MODE)	Output Format and Clock Duty Stabilizer Pin. Default Is VDD.
J5 (SHDN_AMP)	Enables/Disables the Amplifiers. Default Is ON.
J6 (LO)	Board LO Signal Input. Impedance Matched to 50Ω for Use with Lab Signal Generators.
J7 (CLK)	Board Clock Input. Impedance Matched to 50Ω . Drive with a Low-Phase-Noise Clock Oscillator or Filtered Sine Wave Signal Source.
J8 (MIXER ENABLE)	Enables/Disables the RF Mixer. Default Is ON.
J11 (RF)	Board RF Signal Input. Impedance Matched to 50Ω for Use with Lab Signal Generators.
TP1 (SENSE_I)	Reference Input to Adjust the Full-Scale Range of the DC1513, I-Channel. Default Is VDD.
TP2 (GND)	DC Ground.
TP4 (GND)	DC Ground.
TP5 (3V)	DC Supply Input (3VDC).
TP7 (5V)	DC Supply Input (5VDC).
TP8 (GND)	DC Ground.
TP12 (SENSE_Q)	Reference Input to Adjust the Full-Scale Range of the DC1513, Q-Channel. Default Is VDD.



QUICK START PROCEDURE

- 3. Apply an RF input signal to the board. For best results, use a low distortion, low noise signal generator with sufficient filtering to avoid degrading the performance of the receiver.
- Apply an LO input signal to the board. Note that the difference in frequency between this signal and the RF signal will be the IF frequency resulting at the IF filter and ADC input.
- 5. Observe the ADC output with demo circuit DC890B, a USB cable, a Windows computer, and Linear Technology's PScope data processing software.



Figure 1. Proper Measurement Equipment Setup



QUICK START PROCEDURE

OTHER BOARD CIRCUITRY

Device U1 is an EEPROM device that is used by the PScope software to identify the board and apply the correct settings for the data collection.

USING PSCOPE SOFTWARE

T LINUTR

PScope, downloadable from Linear Technology's website http://www.linear.com/, processes data from the DC890 data acquisition board and displays FFT and signal analysis information on the computer screen.

The onboard EEPROM U1 should enable automatic board detection and auto configuration of the software, but if the user wishes to change the settings, they can easily do so.

From the configure menu in the toolbar, uncheck autodetect device. The default settings for DC1513 are shown in Figure 2.

ADC Configuration			
Read Demo Board		🗹 Config Manually	
DemoBd	DC1513A	LTC9004	
Bits	14	2 Channs	
Alignment	14	🔽 Bipolar	
FPGA Ld	CMOS 💌	Positive-Edge Clk	
	Cancel	Apply	

Figure 2. Entering the Correct Device Information for Your ADC. Select the Correct Parameters for the DC1513. Under Normal Conditions, PScope Should Automatically Recognize the Board and Adjust the Software Settings Accordingly.



DEMO MANUAL DC1513B

PARTS LIST

ITEM	QTY	REFERENCE	PART DESCRIPTION	MANUFACTURER/PART NUMBER
DC1513E	3			
1	2	C11, C13	CAP, X7R, 1000pF, 16V, 10%, 0402	AVX 0402YC102KAT
2	13	C2, C6, C24, C25, C27 TO C32, C34, C35, C36	CAP, 0402 0.1µF 10% 10V X5R	AVX 0402ZD104KAT2A
3	2	C20, C23	CAP, X7R, 0.1µF, 16V, 10%, 0603	AVX 0603YC104KAT
4	2	C21, C22	CAP, NPO, 100pF, 50V, 5%, 0402	AVX 04025A101JAT2A
5	7	C3, C8 TO C10, C14, C15, C19	CAP, 0805 4.7µF 20% 25V X7R	TAIYO YUDEN TMK212BJ475MG-T
6	0	C1, C4, C5, C12, C16, C18	CAP, 0402, DNI	
7	2	C7, C17	CAP, NPO, 10pF, 50V, 5%, 0402	AVX 04025A100JAT2A
8	3	J3, J4, J5	HEADER, 3 × 2 PIN, 2mm	SAMTEC TMM-103-02-L-D
9	3	J6, J7, J11	CONN, SMA 50Ω EDGE-LANCH	E.F. JOHNSON, 142-0701-851
10	1	J8	HEADER, 3 × 1 PIN, 2mm	SAMTEC TMM-103-02-L-S
11	1	J9	HEADER, 2 × 1 PIN, 2mm	SAMTEC TMM-102-02-L-S
12	7	JP1 TO JP7	SHUNT	SAMTEC, 2SN-BK-G
13	1	L1	FERRITE BEAD, 60Ω, 0603	MURATA BLM18PG600SN1D
14	1	Q1	XSTR, MOSFET, SOT23	DIODES/ZETEX 2N7002-7-F
15	9	R1, R2, R12, R14, R33, R34	RES, 0402 1k 1% 1/16W	NIC NRC04F1001TRF
16	2	R36, R37, R42, R10, R15	RES, 0402 33.2Ω 1% 1/16W	NIC NRC04F33R2TRF
17	1	R13	RES, 0402 49.9Ω 1% 1/16W	NIC NRC04F49R9TRF
18	1	R16	RES, 0805 0Ω JUMPER	VISHAY CRCW08050000Z0EA
19	5	R19, R21, R22, R24, R30	RES, 0402 100k 1% 1/16W	VISHAY CRCW0402100KFKED
20	1	R20	RES, 0402 75k 1% 1/16W	VISHAY CRCW040275K0FKED
21	0	R23, R27, R28	RES, 0402, DNI	
22	2	R3, R4	POT, 10k, TOP ADJUSTMENT, THROUGH HOLE	BOURNS 3262W-1-103LF
23	1	R39	RES, 0402 10k 1% 1/16W	VISHAY CRCW040210K0FKED
24	2	R6, R7	RES, 0402 4.75k 1% 1/16W	VISHAY CRCW04024K75FKED
25	8	R8, R11, R17, R18, R25, R26, R29, R43	RES, 0402 4.99k 1% 1/16W	VISHAY CRCW04024K99FKED
26	7	TP1, TP2, TP4, TP5, TP7, TP8, TP12	TURRET	MILL-MAX, 2308-2-00-80-00-00-07-0
27	1	U1	IC, SERIAL EEPROM, TSSOP	MICROCHIP 24LC025-I/ST
28	2	U2, U8	IC, LOGIC, INV, UNBUFFERED SC70	FAIRCHILD NC7SVU04P5X
29	4	U3, U4, U5, U7	IC, BUS BUF LVL XLATE CMOS, OCTAL, DFN 8mm × 4mm	FAIRCHILD FXLH42245MPX
30	1	U6	IC, DFN12, VREG, DUAL, 500MA, 100MA	LINEAR TECHNOLOGY LT3024IDE#PBF
31	4		HW, SPACER, NYLON, 0.25"	KEYSTONE 8831
DC1513E	B-AA			
1	1	DC1513B	GENERAL BOM	
2	1	R31	RES, 0603 0Ω JUMPER	VISHAY CRCW06030000Z0EA
3	0	R32	RES, 0603 DNI	
4	0	R5, R9	RES, 0402 DNI	
5	1	U9	LTM9004CV-AA	LINEAR TECHNOLOGY LTM9004CV-AA#PBF
6	1		FAB, PRINTED CIRCUIT BOARD	DEMO CIRCUIT 1513B

PARTS LIST

ITEM	QTY	REFERENCE	PART DESCRIPTION	MANUFACTURER/PART NUMBER
DC1513	B-AB			
1	1	DC1513B	GENERAL BOM	
2	1	R31	RES, 0603 0Ω JUMPER	VISHAY CRCW06030000Z0EA
3	0	R32	RES, 0603 DNI	
4	0	R5, R9	RES, 0402 DNI	
5	1	U9	LTM9004CV-AB	LINEAR TECHNOLOGY LTM9004CV-AB#PBF
6	1		FAB, PRINTED CIRCUIT BOARD	DEMO CIRCUIT 1513B
DC1513	B-AC			·
1	1	DC1513B	GENERAL BOM	
2	0	R31	RES, 0603 DNI	
3	1	R32	RES, 0603 0Ω JUMPER	VISHAY CRCW06030000Z0EA
4	2	R5, R9	RES, 0402 7.5k 1% 1/16W	VISHAY CRCW04027K50FKED
5	1	U9	LTM9004CV-AC	LINEAR TECHNOLOGY LTM9004CV-AC#PBF
6	1		FAB, PRINTED CIRCUIT BOARD	DEMO CIRCUIT 1513B
DC1513	B-AD			·
1	1	DC1513B	GENERAL BOM	
2	0	R31	RES, 0603 DNI	
3	1	R32	RES, 0603 0Ω JUMPER	VISHAY CRCW06030000Z0EA
4	2	R5, R9	RES, 0402 7.5k 1% 1/16W	VISHAY CRCW04027K50FKED
5	1	U9	LTM9004CV-AD	LINEAR TECHNOLOGY LTM9004CV-AD#PBF
6	1		FAB, PRINTED CIRCUIT BOARD	DEMO CIRCUIT 1513B



SCHEMATIC DIAGRAM





dc1513bf

6

SCHEMATIC DIAGRAM





Information furnished by Linear Technology Corporation is believed to be accurate and reliable. However, no responsibility is assumed for its use. Linear Technology Corporation makes no representation that the interconnection of its circuits as described herein will not infringe on existing patent rights.

DEMO MANUAL DC1513B

DEMONSTRATION BOARD IMPORTANT NOTICE

Linear Technology Corporation (LTC) provides the enclosed product(s) under the following AS IS conditions:

This demonstration board (DEMO BOARD) kit being sold or provided by Linear Technology is intended for use for **ENGINEERING DEVELOPMENT OR EVALUATION PURPOSES ONLY** and is not provided by LTC for commercial use. As such, the DEMO BOARD herein may not be complete in terms of required design-, marketing-, and/or manufacturing-related protective considerations, including but not limited to product safety measures typically found in finished commercial goods. As a prototype, this product does not fall within the scope of the European Union directive on electromagnetic compatibility and therefore may or may not meet the technical requirements of the directive, or other regulations.

If this evaluation kit does not meet the specifications recited in the DEMO BOARD manual the kit may be returned within 30 days from the date of delivery for a full refund. THE FOREGOING WARRANTY IS THE EXCLUSIVE WARRANTY MADE BY THE SELLER TO BUYER AND IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESSED, IMPLIED, OR STATUTORY, INCLUDING ANY WARRANTY OF MERCHANTABILITY OR FITNESS FOR ANY PARTICULAR PURPOSE. EXCEPT TO THE EXTENT OF THIS INDEMNITY, NEITHER PARTY SHALL BE LIABLE TO THE OTHER FOR ANY INDIRECT, SPECIAL, INCIDENTAL, OR CONSEQUENTIAL DAMAGES.

The user assumes all responsibility and liability for proper and safe handling of the goods. Further, the user releases LTC from all claims arising from the handling or use of the goods. Due to the open construction of the product, it is the user's responsibility to take any and all appropriate precautions with regard to electrostatic discharge. Also be aware that the products herein may not be regulatory compliant or agency certified (FCC, UL, CE, etc.).

No License is granted under any patent right or other intellectual property whatsoever. LTC assumes no liability for applications assistance, customer product design, software performance, or infringement of patents or any other intellectual property rights of any kind.

LTC currently services a variety of customers for products around the world, and therefore this transaction is not exclusive.

Please read the DEMO BOARD manual prior to handling the product. Persons handling this product must have electronics training and observe good laboratory practice standards. **Common sense is encouraged**.

This notice contains important safety information about temperatures and voltages. For further safety concerns, please contact a LTC application engineer.

Mailing Address:

Linear Technology 1630 McCarthy Blvd. Milpitas, CA 95035

Copyright © 2004, Linear Technology Corporation

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Analog Devices Inc.: DC1513B-AD DC1513B-AA DC1513B-AC DC1513B-AB