

# HMC1019ALP4E

## 0.5 dB LSB GaAs MMIC 5-BIT DIGITAL ATTENUATOR, 0.1 - 30 GHz

### Typical Applications


The HMC1019ALP4E is ideal for:

- Fiber Optics & Broadband Telecom
- Microwave Radio & VSAT
- Military Radios, Radar & ECM
- Space Applications
- Sensors
- Test & Measurement Equipment

### Features

- 0.5 dB LSB Steps to 15.5 dB
- TTL/CMOS Compatible, Serial Control
- Unique Asynchronous Mode Control Allows Immediate Attenuation Level Setting
- ±0.5 dB Typical Bit Error
- High Input IP3: +45 dBm
- 24 Lead 4x4mm SMT Package: 16mm<sup>2</sup>

### Functional Diagram



### General Description


The HMC1019ALP4E is a broadband 5-bit GaAs IC digital attenuator in a low cost leadless surface mount package. Covering 0.1 to 30.0 GHz, the insertion loss is less than 4.0 dB typical. The attenuator bit values are 0.5 (LSB), 1, 2, 4, 8 for a total attenuation of 15.5 dB. Attenuation accuracy is excellent at ±0.3 dB typical step error with an IIP3 of +45 dBm. The control interface is CMOS/TTL compatible and accepts a three wire serial input. The HMC1019ALP4E features a user selectable power up state and a serial output port for cascading other Analog Devices serial controlled components.

### Electrical Specifications, $T_A = +25^\circ\text{C}$ , With $V_{dd} = V_{dd1} = +5\text{V}$ , $V_{ss} = -5\text{V}$

| Parameter  | Frequency (GHz)     | Min.                               | Typ. | Max. | Units |
|--|---------------------|------------------------------------|------|------|-------|
| Insertion Loss   | 0.1 - 18.0 GHz      |                                    | 3.5  | 4.5  | dB    |
|  | 18.0 - 26.5 GHz     |                                    | 4.5  | 6.0  | dB    |
|  | 26.5 - 30.0 GHz     |                                    | 5.0  | 6.5  | dB    |
| Attenuation Range  | 0.1 - 30.0 GHz      |                                    | 15.5 |      | dB    |
| Return Loss (RF1 & RF2, All Atten. States)                                   | 0.1 - 30.0 GHz      |                                    | 12   |      | dB    |
| Attenuation Accuracy: (Referenced to Insertion Loss)                         | 0.5 - 7.5 dB States | ± (0.3 + 6%) of Atten. Setting Max |      |      | dB    |
|  | 8 - 15.5 dB States  | ± (0.3 + 8%) of Atten. Setting Max |      |      | dB    |
| Input Power for 0.1 dB Compression   | 0.1 - 0.5 GHz       |                                    | 22   |      | dBm   |
|  | 0.5 - 30.0 GHz      |                                    | 25   |      | dBm   |
| Input Third Order Intercept Point<br>(Two-Tone Input Power= 0 dBm Each Tone) | 0.1 - 0.5 GHz       |                                    | 42   |      | dBm   |
|  | 0.5 - 30.0 GHz      |                                    | 45   |      | dBm   |
| Switching Characteristics  | 0.1 - 30.0 GHz      | tRISE, tFALL (10/90% RF)           | 60   |      | ns    |
|  |                     | tON/tOFF (50% CTL to 10/90% RF)    | 90   |      | ns    |
| I <sub>dd1</sub>   | 0.1 - 30.0 GHz      | 2.5                                | 4.5  | 6.5  | mA    |
| I <sub>ss</sub>  | 0.1 - 30.0 GHz      | -7.0                               | -5.5 | -3.0 | mA    |


**0.5 dB LSB GaAs MMIC 5-BIT DIGITAL  
ATTENUATOR, 0.1 - 30 GHz**

**Insertion Loss vs. Temperature**




**Normalized Attenuation**

(Only Major States are Shown)




**Input Return Loss**

(Only Major States are Shown)




**Output Return Loss**

(Only Major States are Shown)




**Bit Error vs. Attenuation State**




**Bit Error vs. Frequency**

(Only Major States are Shown)




**0.5 dB LSB GaAs MMIC 5-BIT DIGITAL  
ATTENUATOR, 0.1 - 30 GHz**


**Relative Phase vs. Frequency**  
(Only Major States are Shown)




**Step Attenuation vs. Attenuation State**  
**0.1 - 18 GHz**




**Step Attenuation vs. Attenuation State**  
**18 - 30 GHz**




**Input Power for 0.1 dB Compression**



**Input IP3 Over Major Attenuation States**



**Input IP3 vs. Temperature**  
(Minimum Attenuation State)




## 0.5 dB LSB GaAs MMIC 5-BIT DIGITAL ATTENUATOR, 0.1 - 30 GHz

### Serial Control Interface

The HMC1019ALP4E contains a 3-wire SPI compatible digital interface (SERIN, CLK, LE). The serial control interface is activated when S/A is kept high. The 5-bit serial word must be loaded MSB first as a 6-bit word with the first bit ignored. The positive-edge sensitive CLK and LE requires clean transitions. If mechanical switches are used, sufficient debouncing should be provided. When LE is high, 5-bit data in the serial input register is transferred to the attenuator. When LE is high CLK is masked to prevent data transition during output loading.

For all modes of operations, the state will stay constant while LE is kept low.



### Serial Mode Truth Table

| Control Voltage Input |            |            |            |              | Attenuation<br>State<br>RF1 - RF2 |
|-----------------------|------------|------------|------------|--------------|-----------------------------------|
| P4<br>8 dB            | P3<br>4 dB | P2<br>2 dB | P1<br>1 dB | P0<br>0.5 dB |                                   |
| High                  | High       | High       | High       | High         | Reference I.L.                    |
| High                  | High       | High       | High       | Low          | 0.5 dB                            |
| High                  | High       | High       | Low        | High         | 1 dB                              |
| High                  | High       | Low        | High       | High         | 2 dB                              |
| High                  | Low        | High       | High       | High         | 4 dB                              |
| Low                   | High       | High       | High       | High         | 8 dB                              |
| Low                   | Low        | Low        | Low        | Low          | 15.5 dB                           |

Any combination of the above states will provide an attenuation approximately equal to the sum of the bits selected.


| Parameter                                 | Typ.   |
|---|--------|
| Min. serial period, $t_{SCK}$             | 100 ns |
| Control set-up time, $t_{CS}$             | 20 ns  |
| Control hold-time, $t_{CH}$               | 20 ns  |
| LE setup-time, $t_{LN}$                   | 10 ns  |
| Min. LE pulse width, $t_{LEW}$            | 10 ns  |
| Min LE pulse spacing, $t_{LES}$           | 630 ns |
| Serial clock hold-time from LE, $t_{CKN}$ | 10 ns  |
| Hold Time, $t_{PH}$                       | 0 ns   |
| Latch Enable Minimum Width, $t_{LEN}$     | 10 ns  |
| Setup Time, $t_{PS}$                      | 2 ns   |

### Asynchronous Mode

The HMC1019ALP4E can be switched to an asynchronous mode to change the attenuation state rapidly to one of four predefined states. The logic state of ASM1-ASM2 determines one of the four attenuation states in the asynchronous mode per truth table. The asynchronous mode works either directly or latched. To activate the direct-asynchronous-mode, S/A needs to be at logic low and LE needs to be at logic high. In the direct-asynchronous-mode, any change in the logic state of ASM1-ASM2 directly affects the attenuation state. In the latched-asynchronous-mode, the attenuation state changes per the asynchronous mode truth table when S/A is at logic low and LE is pulsed per the timing diagram. The attenuation stays constant (latched) as long as LE stays low. In the asynchronous mode, the inputs SERIN and CLK do not affect the attenuation state.

## 0.5 dB LSB GaAs MMIC 5-BIT DIGITAL ATTENUATOR, 0.1 - 30 GHz

### Timing Diagram (Latched Asynchronous Mode)



### Asynchronous Mode Truth Table

| ASM1 | ASM2 | Attenuation State RF1-RF2 |
|------|------|---------------------------|
| High | High | Reference I.L.            |
| High | Low  | 1.5 dB                    |
| Low  | High | 14 dB                     |
| Low  | Low  | 15.5 dB                   |

### Power-Up States

If LE is set to logic LOW at power-up, the logic state of PUP determines the power-up state of the part per PUP truth table. If the LE is set to logic HIGH at power-up, the logic state of ASM1-ASM2 determines the power-up state of the part per truth table for the asynchronous mode. The attenuator latches in the desired power-up state approximately 200 ms after power-up.

### PUP Truth Table

| PUP  | Attenuation State |
|------|-------------------|
| High | Reference I.L.    |
| Low  | 15.5 dB           |

Note: The logic state of ASM1-ASM2 determines the power-up state of the part per truth table for the asynchronous mode when LE is high at power-up.

### Bias Voltages & Currents

|      |               |
|------|---------------|
| Vdd  | +5V @ 0.06 mA |
| Vdd1 | +5V @ 4.5 mA  |
| Vss  | -5V @ 5.5 mA  |

### Control Voltage

| State | Bias Condition        |
|-------|-----------------------|
| Low   | 0 to 0.8V @ 1 $\mu$ A |
| High  | 2 to 5V @ 1 $\mu$ A   |

## 0.5 dB LSB GaAs MMIC 5-BIT DIGITAL ATTENUATOR, 0.1 - 30 GHz


### Absolute Maximum Ratings

|  |                |
|--|----------------|
| RF Input Power (0.1 to 30.0 GHz)   | +27 dBm        |
| Control Voltage (CLK, SERIN, LE, PUP, ASM1, ASM2, S/A)                     | Vdd + 0.5V     |
| Vdd, Vdd1  | +7 Vdc         |
| Vss  | -7 Vdc         |
| Channel Temperature  | 150 °C         |
| Continuous P <sub>diss</sub> (T = 85 °C)<br>(derate 6.8 mW/°C above 85 °C) | 0.453 W        |
| Thermal Resistance   | 143.5 °C/W     |
| Storage Temperature  | -65 to +150 °C |
| Operating Temperature  | -40 to +85 °C  |
| ESD Sensitivity (HBM)  | Class 1A       |



ELECTROSTATIC SENSITIVE DEVICE  
OBSERVE HANDLING PRECAUTIONS

### Outline Drawing



### Package Information







| Part Number  | Package Body Material                              | Lead Finish   | MSL Rating          | Package Marking <sup>[2]</sup> |
|--------------|--|---------------|---------------------|--------------------------------|
| HMC1019ALP4E | RoHS-compliant Low Stress Injection Molded Plastic | 100% matte Sn | MSL3 <sup>[1]</sup> | 1019A<br>XXXX                  |

[1] Max peak reflow temperature of 260 °C

[2] 4-Digit lot number XXXX


# 0.5 dB LSB GaAs MMIC 5-BIT DIGITAL ATTENUATOR, 0.1 - 30 GHz

## Pin Descriptions

| Pad Number                 | Function                          | Description  | Interface Schematic   |
|----------------------------|-----------------------------------|--|---|
| 1<br>2                     | SERIN<br>LE                       | See truth table, control voltage table and timing diagram.   |    |
| 3                          | Vss                               | Negative Bias -5V  |    |
| 4, 15                      | GND                               | These pins and package bottom must be connected to RF/DC ground.   |    |
| 6-13, 16                   | N/C                               | The pins are not connected internally; however, all data shown herein was measured with these pins connected to RF/DC ground externally. |   |
| 5, 14                      | RF1, RF2                          | These pins are DC coupled and matched to 50 Ohm. Blocking capacitors are required if RF line potential is not equal to 0V.               |   |
| 17                         | Vdd1                              | Positive Bias +5V  |  |
| 18                         | SEROUT                            | Serial input data delayed by 6 clock cycles.   |  |
| 19<br>21<br>22<br>23<br>24 | PUP<br>ASM1<br>ASM2<br>S/A<br>CLK | See truth table, control voltage table and timing diagram.   |  |
| 20                         | Vdd                               | Serial Controller Bias +5V   |   |

**0.5 dB LSB GaAs MMIC 5-BIT DIGITAL  
ATTENUATOR, 0.1 - 30 GHz**


**Application Circuit**





**0.5 dB LSB GaAs MMIC 5-BIT DIGITAL  
ATTENUATOR, 0.1 - 30 GHz**

**Evaluation PCB**



**List of Materials for Evaluation PCB EV1HMC1019ALP4 [1]**

| Item       | Description                     |
|------------|---------------------------------|
| J1, J2     | 2.9 mm PC Mount RF Connector    |
| J3, J4, J6 | DC Connector                    |
| J5         | 2mm DC Header                   |
| C1-C3      | 100 pF Capacitor, 0402 Pkg.     |
| C4-C6      | 1000 pF Capacitor, 0402 Pkg.    |
| U1         | HMC1019ALP4E Digital Attenuator |
| PCB [2]    | 600-00196-00-2 Evaluation Board |

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Rogers 4350

The circuit board used in the application should use RF circuit design techniques. Signal lines should have 50 Ohm impedance while the package ground leads should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Analog Devices upon request.

**0.5 dB LSB GaAs MMIC 5-BIT DIGITAL  
ATTENUATOR, 0.1 - 30 GHz****Notes:**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Analog Devices Inc.:](#)

[HMC1019ALP4E](#) [HMC1019ALP4ETR](#) [EV1HMC1019ALP4](#)