


ADAM-6521 Series

**Industrial Ethernet
Switches with 4 x
10/100Base-TX Ports
& 1 x 100Base-FX
Fiber Optic Port**



Features

- Provides 4 x 10/100 Mbps Ethernet ports with RJ-45 connector
- Provides 1 x 100 Mbps multi/single-mode fiber port with SC/ST connector
- Supports full/half duplex flow control
- Supports Integrated Loop-up engine
- Supports MDI/MDI-X auto crossover
- Provides broadcast storm protection
- Supports +10 ~ 30 V_{DC} voltage power input
- Supports 4,000 V_{DC} Ethernet ESD protection
- Provides flexible mounting: DIN-rail, Wall, Stack
- Supports operating temperatures from -10 ~ 65° C

Introduction

ADAM-6521 and ADAM-6521S are industrial-grade Ethernet switch with a fiber optic port that makes it possible to expand industrial networks fast and cost-effectively. ADAM-6521 and ADAM-6521S of 1 fiber port and 4-RJ-45 ports. With fiber optics, you can prevent noise interfering with your system and implement transmission distances up to 15 km.

ADAM-6521 and ADAM-6521S are especially suited for industrial environments with Ethernet networking needs such as: semi-conductor factories, inventory control environments, assembly line and production and more.

ADAM-6521 and ADAM-6521S support a wide voltage range of +10 ~ 30 V_{DC} over the terminal block, and 3,000 V_{DC} surge (EFT) protection to protect it from being damaged by over-voltage. A wide operating temperature range from -10 to 65° C (14 ~ 149° F), makes it functional in harsh operating environments. They also have six inclusive LED indicators which make troubleshooting the ADAM-6521 and ADAM-6521S easier. Each port has a pair of LEDs that indicate link status and transmission speed. This function conveniently informs users of any collisions, the link status, power failure and data receipts for immediate on-site diagnostics.

Specifications

Communications

- **Standard** IEEE 802.3, 802.3u, 802.3x
- **LAN** 10/100Base-T, 100Base-FX
- **Transmission Distance** Ethernet : Up to 100 m
Multi-mode Fiber : Up to 2 km
(ADAM-6521, ADAM-6521/ST)
Single-mode Fiber : Up to 15 km (ADAM-6521S)
- **Transmission Speed** Up to 100 Mbps

Interface

- **Connectors** 4 x RJ-45, 1 x SC type fiber connector (ADAM-6521, ADAM-6521S) or 1 x ST type fiber connector (ADAM-6521/ST)
2-pin removable screw terminal (power)
- **LED Indicators** Power, Link (100Base-FX), 100/10M (Ethernet)

Power

- **Power Consumption** ADAM-6521, ADAM-6521/ST: Max. 3 W
ADAM-6521S: Max. 4 W
- **Power Input** 1 x Unregulated 10 ~ 30 V_{DC}

Mechanism

- **Dimensions (W x H x D)** 70 x 112 x 27 mm
- **Enclosure** IP30, ABS+PC with solid mounting kits
- **Mounting** DIN 35 rail, Wall, Stack

Protection

- **ESD (Ethernet)** 4,000 V_{DC}
- **Surge (EFT for power)** 3,000 V_{DC}

Environment

- **Operating Temperature** -10 ~ 65° C (14 ~ 149° F)
stack : -10 ~ 60° C (14 ~ 140° F)
- **Storage Temperature** -20 ~ 80° C (-4 ~ 176° F)
- **Operating Humidity** 20 ~ 95% (non-condensing)
- **Storage Humidity** 0 ~ 95% (non-condensing)
- **MTBF** 1,150,000 hrs

Certifications

- **Safety** UL 60950-1, CAN/CSA-C22.2 No.60950
- **EMC** U.S.A.: FCC Part 15 CISPR 22
EU: EN55011, EN61000-6-4
EN55022 Class A,
EN61000-3-2/3,
EN55024,
IEC61000-4-2/3/4/5/6/8/11
EN61000-6-2

Ordering Information

- **ADAM-6521** Industrial Ethernet Switch with 4 x 10/100Base-TX Ports & 1 Multi-mode SC Type Fiber Optic Port
- **ADAM-6521/ST** Industrial Ethernet Switch with 4 x 10/100Base-TX Ports & 1 Multi-mode ST Type Fiber Optic Port
- **ADAM-6521S** Industrial Ethernet Switch with 4 x 10/100Base-TX Ports & 1 Single-mode SC Type Fiber Optic Port

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ADAM-6521/ST-AE](#)