


AIMB-782

LGA1155 3rd Generation Intel® Core™ i7/i5/i3/Pentium ATX with DVI/VGA, DDR3, SATA III



Features

- 3rd generation Intel® Core™ processor-based platform
- Supports Intel® Core™ i7/i5/i3/Pentium processor with Q77 chipset
- Four DIMM sockets support up to 32 GB DDR3 1066/1333/1600
- Supports dual display VGA/DVI-D and dual GbE LAN
- Supports SATA RAID 0, 1, 5, 10, AMT8.0, USB 3.0
- Supports Advantech LPC modules of TPM


Quiet

Specifications

CE FCC

Processor System	CPU	Core i7 3770	Core i7 2600	Core i5 3550S	Core i5 2400	Core i3 3220	Core i3 2120	Pentium G2120	Pentium G850	Celeron G540
	Speed	3.4 GHz	3.4 GHz	3.0 GHz	3.1 GHz	3.3 GHz	3.3 GHz	3.1 GHz	2.9 GHz	2.5 GHz
	L3 Cache	8 MB	8 MB	6 MB	6 MB	3 MB	3 MB	3 MB	3 MB	2 MB
	Socket	LGA1155								
	Chipset	Q77								
	BIOS	AMI 64 Mbit SPI								
Expansion Slot	PCI	32-bit/33 MHz, 4 slots								
	PCIe x 1 (Gen2)	500 MB/s per direction, 1 slot								
	PCIe x 4 (Gen2)	2.0 GB/s per direction, 1 slot								
	PCIe x16 (Gen3)	16 GB/s per direction, 1 slot								
Memory	Technology	Dual Channel DDR3 1066/1333/1600 (1600 only supported by Core i7/i5/i3 3xxx series processors)								
	Max. Capacity	32 GB								
	Socket	4 x 240-pin DIMM								
Graphics	Controller	Intel HD Graphics 2000/2500/3000/4000 (Depends on processor)								
	VRAM	1 GB maximum shared memory with 2 GB and above system memory installed								
Ethernet	Interface	10/100/1000 Mbps								
	Controller	GbE LAN1: Intel 82579LM, GbE LAN2: Intel 82583V								
	Connector	RJ-45 x 2								
SATA	Max Data Transfer Rate	600 MB/s								
	Channel	2								
	Max Data Transfer Rate	300 MB/s								
	Channel	4								
Rear I/O	VGA	1								
	DVI	1								
	Ethernet	2								
	USB	4 (Two USB 3.0)								
	Audio	2 (Mic-in, Line-out)								
	Serial	2 (RS-232)								
	PS/2	2 (1 x keyboard and 1 x mouse)								
Internal Connectors	USB	10 (Two USB 3.0)								
	Serial	4 (3 x RS-232, 1 x RS-232/422/485 with auto-flow control)								
	SATA	6 (SATA II x4 and SATA III x2)								
	Parallel	1								
	IrDA	1								
	GPIO	8-bit								
Watchdog Timer	Output	System reset								
	Interval	Programmable 1 ~ 255 sec								
Power Requirement	Power On	Intel Core i5 3550 3.0 GHz; DDR3 8G x 4								
		3.3 V	5 V		12 V		5 Vsb			
		0.77 A	2.23 A		3.56 A		0.46 A			
Environment		Operating					Non-Operating			
	Temperature	0 ~ 60° C (32 ~ 140° F), depends on CPU speed and cooler solution					-40 ~ 85° C (-40 ~ 185° F)			
Physical Characteristics	Dimensions	304.8 x 244 mm (12" x 9.6")								

Block Diagram



Ordering Information

Part Number	Chipset	Memory	Display	USB 3.0	USB 2.0	COM	GbE LAN	AMT	SATA III	SW RAID
AIMB-782QG2-00A1E	Q77	Non-ECC DDR3	VGA + DVI	4	10	6	2	Yes	2	Yes

Packing List

Part Number	Description	Quantity
1700003194	SATA HDD cable	x 2
1700022749-11	SATA power cable	x 1
1960050472T000	I/O port bracket	x 1
2002078210	Startup manual	x 1
2062078200	Driver CD	x 1

I/O View



AIMB-782QG2-00A1E

Optional Accessories

Part Number	Description
1700002204	Dual port USB 2.0 cable (27 cm) with bracket
1700028292-01	Dual port USB 3.0 Cable with bracket
1960047669N001	LGA1155/1156 CPU cooler for 4U and wallmount chassis
1960047831N001	LGA1155/1156 CPU cooler for 2U and wallmount chassis
1960049408N001	LGA1155/1156 CPU cooler for 1U and wallmount chassis
1700008809	Printer port cable kit (25 cm)
1700020294-01	Printer port cable kit (42 cm)
1701092300	COM port cable kit
1960055954T000	I/O port bracket for 1U chassis

Note 1: Purchasing AIMB-782's proprietary CPU cooler from Advantech is a must. Other brands' CPU coolers are NOT compatible with AIMB-782.

Note 2: 1960049408N001 is design to be used with Advantech 1U chassis and supports up to 73W processor, user needs to conduct thermal test before using this cooler with other brand chassis.

Riser Card

Part Number	Description
AIMB-R430P-03A2E	2U riser card with 3 PCI expansion
AIMB-R43PF-21A1E	2U riser card with 1 PCIe x16 & 2 PCI expansion

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[AIMB-782QG2-00A1E](#)