


AIMB-706

**LGA1151 8th/9th Generation Intel®
Core™ i7/i5/i3 & Pentium®/Celeron®
ATX with DVI/VGA, DDR4, SATA 3.0,
USB 3.1 & 6 COMs**



Features

- Intel® 8th/9th generation Core™ i7/i5/i3 & Pentium®/Celeron® processor with H310 chipset
- Dual channel (Non-ECC) DDR4 2400/2666 up to 64 GB
- Support VGA and DVI display
- SATA 3.0, USB 3.1, dual GbEs
- 5 RS-232 and 1 RS-232/422/485 serial ports
- 1 PCIe x16 (Gen 3) and 1 PCIe x4 (Gen 2), and 5 PCI expansion slots

Note 1: dTPM 2.0 module is required to enable Intel vPro and TPM technologies.

Note 2: Intel® Platform Trust Technology (Intel® PTT) ready for Windows 11.




Specifications



Processor System	CPU	i7-9700E	i7-9700TE	i7-8700	i7-8700T	i5-9500E	i5-9500TE	i5-8500	i5-8500T	i3-9100E	i3-9100TE	i3-8100	i3-8100T	G5400	G5400T	G4900	G4900T								
	Speed	2.6GHz	1.8 GHz	3.2 GHz	2.4 GHz	3.0 GHz	2.2 GHz	3.0 GHz	2.1 GHz	3.1 GHz	2.2 GHz	3.6 GHz	3.1 GHz	3.7 GHz	3.1 GHz	3.1 GHz	2.9 GHz								
	L3 Cache	12 MB	12 MB	12 MB	12 MB	9 MB	9 MB	9 MB	9 MB	6 MB	6 MB	6 MB	6 MB	4 MB	4 MB	2 MB	2 MB								
	Cores	8	8	6	6	6	6	6	6	4	4	4	4	2	2	2	2								
	TDP	65 W	35 W	65 W	35 W	65 W	35 W	65 W	35 W	65 W	35 W	65 W	35 W	58 W	35 W	54 W	35 W								
	Socket	LGA1151																							
	Chipset	Intel H310																							
	BIOS	AMI 128Mbit SPI Flash																							
Expansion Slot	PCI	5 (32-bit/33 MHz)																							
	PCIe x4 (Gen 2)	1																							
	PCIe x16 (Gen 3)	1																							
Memory	Technology	Dual Channel Non-ECC UDIMM DDR4 2400/2666																							
	Max Capacity	64 GB																							
	Sockets	2 (288-pin DIMM)																							
Graphics	Controller	Chipset integrated Intel HD Graphics																							
	VRAM	Shared system memory is subject to OS																							
Ethernet	Interface	10/100/1000 Mbps																							
	Controller	GbE LAN1: Intel I219-V, GbE LAN2 for G2 version: Intel I210-AT																							
	Connector	2 (RJ-45)																							
SATA	Max Data Transfer Rate	600 MB/s																							
	Channel	4																							
Rear I/O	VGA	1 (Resolution up to 1920 x 1200 @ 60 Hz)																							
	DVI	1 for G2 version (Resolution up to 1920 x 1200 @ 60 Hz)																							
	Ethernet	2 for G2 version; 1 for VG version																							
	USB	4 (2 x USB 3.1 Gen 1, 2 x USB 2.0)																							
	Audio	2 (Line-out, Mic-in)																							
	Serial	2 (RS-232)																							
	PS/2	2 (1 x keyboard and 1 x mouse)																							
Internal Connectors	USB	5 (2 x USB 3.1 Gen 1 via header, 2 x USB 2.0 via header, 1 x USB 2.0 Type-A connector)																							
	Serial	4 for G2 version (3 x RS-232, box-header; 1 x RS-232/422/485 with auto-flow control, box-header)																							
	SATA	4																							
	LPC	1 (Optional dTPM 2.0 module available)																							
	GPIO	8-bit																							
Watchdog Timer	Output	System reset																							
	Interval	Programmable 1 - 255 sec																							
Power Requirement	Test Environment	Intel Core i7-8700 3.2GHz; DDR4 2400 16 GB x 2																							
	Voltage	3.3V				5V				12V				5Vsb				-5V				-12V			
	Current	2.74A				3.5A				5.92A				0.05A				0.01A				0.08A			
Environment	Operating	Non-Operating																							
	Temperature	0 ~ 60 °C (32 ~ 140 °F), depends on CPU speed and system thermal solution																-40 ~ 85 °C (-40 ~ 185 °F)							
	Humidity	40 °C @ 95% RH Non-condensing																60 °C @ 95% RH Non-condensing							
Physical Characteristics	Dimensions (L x H)	304.8 x 244 mm (12" x 9.6")																							

Block Diagram



Ordering Information

Part Number	Chipset	Memory	Display	USB 3.1 Gen 1	USB 2.0	COM	GbE LAN	AMT	SATA	SW RAID	Intelligent System Module Support
AIMB-706G2-00A3	H310	Non-ECC	VGA + DVI	4	5	6	2	No	4	No	No
AIMB-706VG-00A2	H310	Non-ECC	VGA	4	5	2	1	No	4	No	No

Packing List

Part Number	Description	Quantity
1700003194	SATA HDD cable	x2
1700022749-11/ 1700022749-12/ 1700022749-13	SATA power cable	x1
1960050472T000	I/O port bracket	x1
2001070612	Startup manual	x1

Note: Driver CD is not provided. Please visit Advantech support website for driver download.

I/O View



AIMB-706G2-00A3



AIMB-706VG-00A2

Optional Accessories

Part Number	Description
1701090401	Single COM port cable(40 cm)
1701092300	Dual COM port cable(28.5 cm)
1700028292-01	2-port USB 3.0 cable w/ BKT(30 cm)
1700002204	2-port USB 2.0 cable w/ BKT(27 cm)
1960047669N001	CPU cooler for 4U and wallmount chassis
1960053207N001	CPU cooler for 2U chassis
1960049408N001	CPU heatsink for 1U chassis (for CPU TDP=35W only)
1960055954T000	IO bracket for 1U chassis
PCA-COM232-00A1E	4-port RS-232 LPC module
PCA-TPM-00B1E	dTPM 2.0 LPC module to enable TPM and vPro technologies

Note: Purchasing AIMB-706's proprietary CPU cooler from Advantech is a must. Other brands' CPU coolers are NOT compatible with AIMB-706.

Riser Card

Part Number	Description
AIMB-RP10P-01A1E	1U riser card providing 1 PCI slot
AIMB-RF10F-01A1E	1U riser card providing 1 PCIe x 16 slot
AIMB-RP30P-03A1E	2U riser card providing 3 PCI slots
AIMB-RP3PF-21A1E	2U riser card providing 1 PCIe x 16 and 2 PCI slots

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[AIMB-706G2-00A3](#)