


ASMB-781

LGA 1155 Intel® Xeon® E3/ 2nd Generation Core™ ATX Server Board with 1 PCIe x16 or 2 PCIe x8, Quad LANs



Features

- Supports LGA 1155 Intel® Xeon® E3 and 2nd Generation Core™ i3 / Pentium processors
- DDR3 1066/1333 MHz ECC UDIMM up to 32GB
- One Gen 2.0 PCIe x16 or two PCIe x8 slots
- Quad LANs with teaming function
- Rackmount optimized placement for thermal green design
- Supports IPMI, Embedded software APIs and utilities


Quiet

Specifications

CE FCC

Form Factor	ATX form factor	
Processor System	Socket	Intel LGA 1155
	CPU type	Intel Xeon E3-1200/ 2nd Generation Core i3 and Pentium series
Core Logic	Chipset	Intel C206 chipset
Memory	Total slot	4 (Dual Channel)
	Max. capacity	32 GB
	Memory type	DDR3 ECC/Non-ECC 1600/1333 MHz UDIMM (240-pin)
	Memory size	1 GB, 2 GB, 4 GB, 8 GB
Expansion Slots	Total PCI/PCI-X/PCIe slots	7
	Slot location 1	PCI
	Slot location 2	PCI
	Slot location 3	PCIe x4 (Gen2 x4 link)
	Slot location 4	PCI x16 slot (Gen2 x8 or x16 link)
	Slot location 5	PCI
	Slot location 6	PCI x16 slot (Gen2 x8 or x16 link)
	Slot location 7	PCI x1 slot (Gen2 x1 link)
Graphics	Controller	AST2300/1300
	VRAM	DDR3 512 Mbit (64 MB)
Storage	SATA controller	Intel C206: 4 SATA2 3 Gb/s ports, 2 SATA3 6Gb/s Intel Matrix Storage (for Windows only) (Supports software RAID 0, 1, 10 & 5)
	SAS controller	-
Networking	Interface	10/100/1000 Mbps
	Controller	GbE LAN1: Intel 82579LM; GbE LAN2: Intel 82574L; GbE LAN3/4: Intel 82580DB (Optional)
	Connector	RJ-45 x 4 for G4 version
Onboard I/O Connectors	Parallel connector	1
	PSU connector	24-pin SSI power connector + 8-pin SSI 12V power connector
	USB connector	3 (supports 6 USB port), 2* Type-A
	Fan header	5 (4-pin)
	SMBus	1
	Chassis intruder	1
	Front LAN LED	2
	Serial port header	1 (RS-232)
	Audio Connector	1 (Realtek ALC 892 optional)
Rear I/O Connectors	External serial port	1 (RS-232), COM1 don't support wake on modem
	External USB port	4
	VGA port	1
	RJ-45	2 for G2 version, 4 for G4 version
	PS/2 KB/mouse	2
Watchdog Timer	Output	System reset
	Interval	Programmable 1 ~ 255 sec
Power Requirement	Power On	3.3 V 5 V 12 V 12V_8P 5 Vsb -V12
		2.74 A 1.12 A 0.08 A 4.86 A 1.81 A 0.01 A
Environment		Operating Non-operating
	Temperature	0 ~ 60° C (32 ~ 140° F) Depends on CPU speed and cooler solution -40 ~ 85° C (-40 ~ 185° F)
	Humidity	0% ~ 90% 5% ~ 95% (Non-condensing)
Physical Characteristics	Dimensions	304.8 x 244 mm (12" x 9.6")

Block Diagram



Ordering Information

Part Number	Chipset	Memory	LAN	IPMI	Graphic
ASMB-781G2-00A1E	C206	DDR3 ECC UNB/Non-ECC UNB	2	-	AST1300
ASMB-781G4-00A1E	C206	DDR3 ECC UNB/Non-ECC UNB	4	Yes	AST2300

Packing List

Part Number	Description	Quantity
2066078100	Driver CD	x 1
2006078110	Startup manual	x 1
1700003194	SATA data cables	x 2
1700022749-11	SATA power cables	x 2
1960052312T000	I/O shield	x 1

Optional Accessories

Part Number	Description
1700002204	Dual port USB cable (27 cm) with bracket
1700008461	Four port USB cable (30.5 cm) with bracket
1960052651N021	LGA 1151/1150/1155 CPU cooler for 2U/4U and rackmount chassis (TDP up to 95W)
1960049408N001	LGA 1151/1150/1155 1U CPU Cooler (TDP up to 95W)
19Z0000406T000	1U I/O shield
1700008809	Printer port cable kit (25 cm)
1700020294-01	Printer port cable kit (42 cm)
1701090401	COM port cable with bracket (40 cm)
PCA-AUDIO-HDA1E	HD Audio-card
968EMLSAP2	SUSIAccess Pro 3.0
PCA-TPM-00A1E	TPM Module with Infineon TPM 1.2 solution

I/O View



ASMB-781G4-00A1E



ASMB-781G2-00A1E

Note 1: Please order 1 piece of each 1960049408N001 and 19Z0000406T000 for configuring ASMB-781 with 1U chassis.

Note 2: Purchasing ASMB-781's proprietary CPU cooler from Advantech is a must. Other brands' CPU coolers are NOT compatible with ASMB-781.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[ASMB781G200A1E-ES](#)