

# EKI-9508G-H

# EKI-9508G-L

**EN 50155 8-Port M12 Unmanaged Ethernet Switch 72/96/110 V<sub>DC</sub>**

**EN 50155 8-Port M12 Unmanaged Ethernet Switch 24/48 V<sub>DC</sub>**



CE FCC

## Features

- Complies with EN50155
- 8 port M12 X-coded 10/100/1000Mbps ports
- Power input
  - EKI-9508G-H: 72/96/110 V<sub>DC</sub>
  - EKI-9508G-L: 24/48 V<sub>DC</sub>
- Operating Voltage
  - EKI-9508G-H: 50.4~137.5 V<sub>DC</sub>
  - EKI-9508G-L: 16.8~60 V<sub>DC</sub>
- M12 connector with IP40 protection
- Operating temperature of -40 ~ 70°C

## Introduction

EKI-9500 series switch is designed for railway application, with rugged and high EMC performance. EKI-9500 series is the suitable networking solution for rolling stock and wayside applications. EKI-9500 series provide M12 connectors for Ethernet/ console/ relay/ power-input connections to ensure tight & robust connectivity, to guarantee reliable operation against environmental disturbances, such as vibration and shock on train. EKI-9508G-H & EKI-9508G-L is a Ethernet switch, it provides 8 x Gigabit Ethernet M12 X-code interface. EKI-9508G-H/ L features a "slim" design, can be easy deployed with its slender size and let network deployment more simple in crowded carriage/ cabinet.

## Specifications

### Interface

- I/O Port 8 x 10/100/1000 BASE-T M12 X-Coded
- Power Connector M12 A-Coded

### Physical

- Enclosure Metal Shell
- Protection Class IP 40
- Installation Wall Mount
- Dimensions (W x D x H) 122.5 x 179.4 x 71.8 mm
- Weight 1.3 kg

### LED Display

- System LEDs PWR1, PWR2, SYS

### Environment

- Operating Temperature -40 ~ 70 °C
- Storage Temperature -40 ~ 85 °C
- Ambient Relative Humidity 10 ~ 95% (non-condensing)

### Power

- Power Consumption ~ 5 Watts (System)
- Power Input
  - EKI-9508G-H: 72/96/110 V<sub>DC</sub>
  - EKI-9508G-L: 24/48 V<sub>DC</sub>
- Operating Voltage
  - EKI-9508G-H: 50.4~137.5 V<sub>DC</sub>
  - EKI-9508G-L: 16.8~60 V<sub>DC</sub>Dual inputs Supports Overload Current Protection  
Supports Reverse Polarity Protection

### Certification


- EMI FCC Part 15 Subpart B Class A  
CE EN55032 (CISPR)  
EN55024 Class A
- EMS EN61000-4-2 (ESD) EN61000-4-3 (RS);  
EN61000-4-4 (EFT); EN61000-4-5 (Surge);  
EN61000-4-6 (CS)
- Shock IEC 61373
- Freefall IEC 60068-2-32
- Vibration IEC 61373
- Rail Traffic EN 50155; EN50121-3-2

### L2 Features

- L2 MAC Address 8K
- Jumbo Frame 9 KB

## Dimensions


Unit: mm [inch]



## Ordering Information

- **EKI-9508G-H-AE** Layer 2 Switch, 8 x M12 Gigabit Ethernet, 72/96/110 V<sub>DC</sub> dual power input
- **EKI-9508G-L-AE** Layer 2 Switch, 8 x M12 Gigabit Ethernet, 24/48 V<sub>DC</sub> dual power input

## Accessories

PN		Description
OPT1-M12-CRP-8MX		Phoenix Contact M12 X-code 8 pin Male crimp type connector
OPT1-M12-CRP-4FA		Phoenix Contact M12 A-code 4 pin Female crimp type connector
OPT1-M12C-8MX-150R		M12 X-code 8 pin Male to RJ45, cable length: 1.5m
OPT1-M12C-4FA-100		M12 A-code 4 pin Female to 1m cable
1990023703S000		M12 waterproof CAP (1pc.)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[EKI-9508G-L-AE](#)