

Johanson Company: Johanson Technology inc. Product Release Date: 31 July, 2020

Deprecated P/N: 3400BL15A0100E

Datasheet Date: 08-09-2024

Description: RF Baluns, 805, 1800-5000MHz, 3W,
1, Ni/Sn (RoHS), 1.8 - 5.0GHz Wideband Ceramic
Balun, 1:2 Impedance Ratio, EIA 0805, 7" Reel
Embossed Tape

Life Cycle Stage: Active - Production

Schedule B: 8534

ECCN: EAR99

RoHS Compliance: Yes, RoHS 10/10

REACH: 1

Country of Origin: TW

Product Family: Integrated Passive Components

Product Subfamily: RF Baluns

Marking: Special

Web Page Link:

<https://www.johansontechnology.com/baluns>

Thickness (Max): 0.041

Thickness (Min): 0.033

End Band (Min):

End Band (Max):

Lead Time Typical (Weeks)*:

*This can vary significantly so it is important
to obtain a quotation with lead time for
production planning purposes. 20

Length (Min): 0.075

Length (Max): 0.083

Width (Min): 0.045

Width (Max): 0.053

Packaging: 7" Reel Embossed Tape

Packaging Qty: 4000

Operating Temp Range: -40°C to +85°C

Storage Temp Range (Packaged): -40°C to +85°C

Storage Temp Range (Non Operating): +5°C to
+35°C with RH 45% to 75%

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[3400BL15A0100E](#) [3400BL15A0100001E](#)