

**B&B ELECTRONICS**

10/100/1000 Mbps Managed Multi-port Optical Demarcation Device

Giga-AccessEtherLinX-II DC Version



PRODUCT FEATURES

- 802.1Q VLAN-tags on per-port basis, based on DiffServ or PRI values
- SNMP Manageable
- QoS - 802.1p-based packet prioritization
- Per-port bi-directional Bandwidth control
- VLAN-tagging and Q-in-Q (double-tagging) segregates customer traffic
- Up and running in less than five minutes

The Giga-AccessEtherLinX-II enables service providers to offer differentiated "Transparent LAN" services to multi-tenant building and business customers without the need for costly remote routers. Residing at the customer premises, the Giga-AccessEtherLinX-II provides a VLAN-based, Layer 2 entry point to the last mile fiber network to support trunking, differentiating and separating customer traffic. Featuring SNMP management with per-port 802.1Q VLAN, 802.1p QoS, traffic prioritization, bandwidth control and multicast pruning/snooping (using IGMP v1, v2), the Giga-AccessEtherLinX-II is perfect for a wide range of Fiber-to-the-Home, Fiber-to-the-Curb and Fiber-to-the-Business (FTTx) services, and is an ideal solution for delivering Ethernet-based services to customers quickly and cost effectively. Designed with a small footprint, the Giga-AccessEtherLinX-II facilitates easy installation inside the premises. It features four 10/100/1000 twisted pair Ethernet downlink ports (for connecting users/LANs), with either a 1000Base-FX fiber or SFP uplink port, and is powered from an internal AC or DC power supply.

The Giga-AccessEtherLinX-II accepts traffic containing VLAN tags on the Uplink port and directs that traffic to the twisted pair downlink ports based on the VLAN ID. In addition to assigning 802.1Q VLAN-tags on a per-port basis, users can also "Qualify" the different VLAN TAGS to assign based on the DiffServ or PRI value of the incoming frame. Traffic priority for each port is supported with a hi/low prioritization queues. The Giga-AccessEtherLinX-II includes per port bi-directional bandwidth control, and supports IGMP multicast pruning which ensures only the necessary amount of IP multicast packets are bridged.

ORDERING INFORMATION

MODEL NUMBER	FIBER	FIBER PORTS	RANGE	ETHERNET PORTS	ETHERNET CONNECTOR
Giga-AccessEtherLinX-II DC					
852-32302	SFP	1	Various	4	RJ45
852-32303	SX-MM850-SC	1	550 m	4	RJ45
852-32304	LX-SM1310-SC	1	15 km	4	RJ45
852-32305	LX-SM1310/PLUS-SC	1	40 km	4	RJ45
852-32306	LX-SM1550/PLUS-SC	1	80 km	4	RJ45
852-32307	LX-SM1550/XLONG-SC	1	100 km	4	RJ45
SINGLE STRAND FIBER *					
852-32310	SSLX-SM1310-SC	1	15 km	4	RJ45
852-32311	SSLX-SM1550-SC	1	15 km	4	RJ45
852-32312	SSBX-SM1310-SC	1	10 km	4	RJ45
852-32313	SSBX-SM1490-SC	1	10 km	4	RJ45
852-32314	SSLX-SM1310/PLUS-SC	1	40 km	4	RJ45
852-32315	SSLX-SM1550/PLUS-SC	1	40 km	4	RJ45
852-32316	SSBX-SM1310/PLUS-SC	1	30 km	4	RJ45
852-32317	SSBX-SM1490/PLUS-SC	1	30 km	4	RJ45
852-32318	SSLX-SM1490/LONG-SC	1	70 km	4	RJ45
852-32319	SSLX-SM1550/LONG-SC	1	70 km	4	RJ45

* These products have single-strand fiber technology. Deploy in pairs or connect another compatible B&B IMC LLC single-strand fiber product.

Giga-AccessEtherLinX-II DC also available in CWDM Fiber.
Call for details.

ACCESSORIES

895-39226 - Rackmount Bracket

895-39949 - Rackmount Shelf



iView: Windows 2000/XP/Vista/Win7

10/100/1000 Mbps Managed Multi-port Optical Demarcation Device

Giga-AccessEtherLinX-II DC Version



SPECIFICATIONS

GENERAL

- Monitors (remote) status without a physical presence or separate "IP" connection through UMA
- Maintains security; all management traffic can remain isolated from the data traffic
- Read/write IEEE 802.1Q VLAN-tags
- Q-in-Q (double-tagging) to further segregate customer VLAN traffic
- Can assign different TAGS based on DiffServ or PRI values of incoming frames.
- QoS: IEEE 802.1p-based or DSCP packet prioritization (2 queues [high/low] with 8 levels of priority)
- VLAN Tag-based on DSCP or priority of incoming frame ("traffic grooming")
- Layer 2 packet switching, store and forward operation
- Forwarding rate: 14,881 pps for 10 Mbps; 148,810 pps for 100 Mbps; 1,488,100 pps for 1000 Mbps
- Includes per-port bi-directional bandwidth control
- AutoCross for MDI/MDIX
- Features Auto Negotiation and Selective Advertising
- MTU: Supports packets up to 9600 bytes
- Supports Half- and Full-Duplex operation
- Supports IEEE 802.3x Flow Control

MANAGEMENT

- Includes GUI-based iView² software, featuring iConfig utility for rapid IP configuration
- SNMP V1 and V2c compatible

- Includes DHCP client for IP address assignment

- Features TFTP client for remote upgrades

- Supports Telnet - Includes DB-9 connector for serial configuration

- Includes per port loopback test modes



- Includes diagnostic LEDs

ETHERNET PROTOCOLS SUPPORTED

- 802.3 10Base-T twisted pair
- 802.3u 100Base-TX twisted pair
- 802.3ab 1000Base-T twisted pair
- 802.3z 1000Base-LX or SX fiber

MECHANICAL DIAGRAM

(dimensions in inches)



MECHANICAL

- Dimensions: 1.64" H x 5.64" W x 8.95" D (4.2 cm x 14.3 cm x 22.7 cm)
- Enclosure: Metal
- Shipping Weight: 1.6 lbs. (0.6 kg)

POWER RATING



- 100-240V AC, 50/60Hz, 0.5/0.25A

ENVIRONMENTAL

- Operating Temperature: +32° to 122° F (0° to +50° C)
- Storage Temperature: -13° to +158° F (-25° to +70° C)
- Operating Humidity: 5 to 95% Non-condensing

REGULATORY APPROVALS

- FCC Class B
- UL/cUL, CE, CB



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[852-32316](#) [852-32304](#) [852-32303](#) [852-32315](#) [852-32311](#) [852-32317](#) [852-32305](#) [852-32319](#) [852-32302](#) [852-32307](#) [852-32310](#) [852-32314](#) [852-32313](#) [852-32312](#) [852-32306](#) [852-32318](#)