

"High Frequency Ceramic Solutions"

Preliminary

1.6 GHz Antenna

P/N 1600AT45A0040

Detail Specification: 11/18/08

Page 1 of 3


General Specifications

Part Number	1600AT45A0040
Frequency Range	1580 - 1620 Mhz
Peak Gain	0.0 dBi typ. (XZ-Total)
Average Gain	-1.0 dBi typ. (XZ-Total)
Return Loss	9.5 dB min.

Input Power	2W max.
Impedance	50 Ω
Reel Quantity	1,000
Operating Temperature	-40 to +85°C
Storage Temperature	+5 to +35°C, Humidity: 45-75%RH, 12 mos. Max

P/N Suffix	Packaging	Bulk	Suffix = S	Eg. 1600AT45A0040S
	Style	T & R	Suffix = E	Eg. 1600AT45A0040E
	Termination	100% Tin	Suffix = None	Eg. 1600AT45A0040(E or S)
	Style	Tin / Lead	Please consult Factory	


Terminal Configuration	
No.	Function
1	Feeding Point
2	NC



The diagram shows a rectangular component with two terminals. Terminal 1 is on the right side, and Terminal 2 is on the left side. A brown square is located in the center of the component.

Mechanical Dimensions

	In	mm
L	0.374 $\pm$ 0.008	9.50 $\pm$ 0.20
W	0.079 $\pm$ 0.008	2.00 $\pm$ 0.20
T	0.047 +.004/-.008	1.20 +0.1/-0.2
a	0.020 $\pm$ 0.012	0.50 $\pm$ 0.30




The diagram shows two views of the component. The top view is a rectangle with dimensions L (length) and W (width). A brown square is in the center. The bottom view is a side view showing the thickness T and the distance a from the edge to the center of the brown square.

Mounting Considerations

Mount these devices with brown mark facing up. Units: mm

* Line width should be designed to provide 50 Ω impedance, depending on PCB material and thickness.



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2003 Johanson Technology, Inc. All Rights Reserved

"High Frequency Ceramic Solutions"

Preliminary

1.6 GHz Antenna


P/N 1600AT45A0040

Detail Specification: 11/18/08

Page 2 of 3


Typical Electrical Characteristics (T=25°C)

Test Board



Return Loss

a) Without Matching Circuits



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2003 Johanson Technology, Inc. All Rights Reserved

"High Frequency Ceramic Solutions"

Preliminary


1.6 GHz Antenna

Detail Specification: 11/18/08

P/N 1600AT45A0040

Page 3 of 3

Typical Radiation Patterns



Johanson Technology, Inc. reserves the right to make design changes without notice.

All sales are subject to Johanson Technology, Inc. terms and conditions.



www.johansontechnology.com

4001 Calle Tecate • Camarillo, CA 93012 • TEL 805.389.1166 FAX 805.389.1821

2003 Johanson Technology, Inc. All Rights Reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Johanson:](#)

[1600AT45A0040E](#) [1600AT45A0040001E](#)