### **B&B ELECTRONICS** Protocol-Independent, Fiber Mode Conversion via SFP Modules

**IE-ModeConverter** 



Mode converters allow network operators to incorporate multiple fiber types within a network. The IE-ModeConverter provides the ability to accomplish this by working with existing equipment and thus, eliminating replacement costs. With the flexibility to convert fiber between single-mode, multi-mode, single-strand and various wavelengths, one can easily extend network range to reach more remote locations. Additionally, since the IE-ModeConverter is an Industrial Equipment device (IE), the unit operates in environments that demand extended operating temperatures.

The IE-ModeConverter uses SFP modules to provide greater fiber flexibility in the network environment. The hot-swappable nature of the SFPs and the numerous fiber modes and types available allow for easy configuration and future upgrading as network demands evolve.

The SFP modules must be MSA compliant and support the same speed range. The IE-ModeConverter operates as a mode converter only and not as a rate or media converter.

### **PRODUCT FEATURES**

- Interchangeable SFP modules allow for multiple fiber mode/type conversion options (single-mode, multi-mode, long haul, short haul, etc.)
- Extended operating temperatures
- Multiple mounting options (Desktop, DIN Rail, IE-PowerTray/18-AC [for high-density installations])
- Compact size conserves space
- AC or DC powering options
- Supports a full range of fiber SFP Modules in various transmission speeds, from 10 Mbps up to 2.4 Gbps\*
- Wallmount Bracket

#### **ORDERING INFORMATION**

MODEL NUMBER	DESCRIPTION	FIBER PORTS	DISTANCE	
IE-ModeConverter SFP/SFP with AC Adapter **				
855-19619	SFP	2	Various	
IE-ModeConverter SFP/SFP without AC Adapter **				
854-19619	SFP	2	Various	

\* Certified at 1.25 Gbps, 2.4 Gbps is achievable

\*\* SFP fibers sold separately

#### ACCESSORIES

- 806-39105 DIN Rail Clip
- 806-39638 Double-USB Power Cable, 36"/.9m
- 806-39650 12"/.3m Barrel-Connector Power Cable
- 850-13086 IE-PowerTray/18-AC (-20°C to +70°C), 18-slot AC powered chassis
- 895-39229 Wall Mount Bracket

## Protocol-Independent, Fiber Mode Conversion via SFP Modules

IE-ModeConverter





### SPECIFICATIONS

TECHNICAL Two SFP ports Protocol-independent operation Converts between dissimilar fiber modes and wavelengths Includes diagnostic LEDs Hot-swappable architecture Small Form Factor 7 VDC to 50 VDC terminal block powering option Supports an external 5 VDC power module (not extended temperature) Extended temperature range from -10° to +50° C Compatible with IMC Networks SFPs and all standard MSA compliant SFP transceivers Supports DIN Rail mounting DC terminal block has dual inputs and supports cascading power Standard Compliance SFP-MSA SFP standard (September 14, 2000) SFF-8472 DDMI standard (Revision 1.0)

### **MECHANICAL DIAGRAM**


(dimensions in inches)





MECHANICAL				
Dimensions	0.83"H x 1.80"W x 3.35"D			
Dimensions	(2.11 x 4.57 x 8.51 cm)			
Shipping Weight	0.25 lbs (0.11 kg)			
AC WALL ADAPTER				
100 to240 ±10% VAC input, 5 VE	C output, 2A max.			
DC INPUT VOLTAGE				
+7 to +50 VDC @ 2.5 Watts (cha	assis grounded to negative terminal)			
POWER				
Maximum 3.3 Watts of combined	l power to both SFPs			
ENVIRONMENTAL				
Operating Temperature:	-13°F to +185°F (-25°C to +85°C)			
operating temperature.	DC configuration			
	-4°F to +158°F (-20°C to +70°C)			
	DIN Railmount power supply			
	+14°F to +122°F (-10°C to +50°C)			
	with AC wall adapter			
Storage Temperature:	-49°F to +185°F (-45°C to +85°C)			
Operating Humidity	5% to 95% (non-condensing), 0 – 10,000 ft. altitude			
REGULATORY APPROVALS				
FCC Class A				

UL/cUL, CSA, CE



**B&B** ELECTRONICS

orders@bb-elec.com support@bb-elec.com International Office: 707 Dayton Road PO Box 1040 Ottawa, IL 61350 USA 815-433-5100 Fax 433-5104 European Office: Westlink Commercial Park Oranmore Co. Galway Ireland +353 91 792444 Fax +353 91 792445

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

B+B SmartWorx: 855-19619