



PRODUCT BRIEF

Intel® Dual Band Wireless-AC 8265 Desktop Kit
4th Generation Intel 802.11ac, Dual Band, 2x2 Wi-Fi + Bluetooth* 4.2



Intel® Dual Band Wireless-AC 8265 Desktop Kit

Ultra Wi-Fi. Ultra Features. Ultra Connected Experience.



The Intel® Dual Band Wireless-AC 8265 Desktop Kit offers a comprehensive solution to enable Wi-Fi connectivity for your system. Give your desktop a boost with Bluetooth* 4.2 and 2x2 11ac Wi-Fi delivering up to 867Mbps¹ including wave 2 features such as downlink MU-MIMO, providing up to a 3x increase in user speeds in dense deployments and supporting fast downloads compared to legacy 11ac devices.² This kit includes two antennas, two RF cables with connectors, two mounting brackets (full and half size), and it is easy and simple to install. When combined with Intel® Core™ processors and exceptional Intel wireless innovations, the Intel® Dual Band Wireless-AC 8265 Desktop Kit dramatically reshapes your wireless experience.

4TH GENERATION INTEL® 802.11AC WIRELESS

Faster Speed
Better Coverage
Larger Capacity
802.11ac, Dual Band, 80MHz, 2x2, MU-MIMO

Delivers up to 3x faster Wi-Fi speeds (up to 867Mbps) than 802.11n, with up to 3x more bandwidth per stream for more users and devices³. Downlink MU-MIMO allows an Access Point to simultaneously transmit data to multiple clients and can improve overall downlink network capacity by up to 3x². Intel® Wireless-AC enables smoother streaming of higher resolution videos, fewer dropped connections, less congestion, and faster speed farther away from the router.

Bluetooth* 4.2

Dual Mode Bluetooth* 4.2 enables BR/EDR low-energy devices to act as a hub and peripheral at the same time. Connects to the newest low-energy Bluetooth* products as well as your familiar devices, such as headsets, keyboards, mice, and more.

Microsoft Windows 10* Ready

Full support for latest Microsoft Windows 10* OS.

M.2 2230
Form Factor

M.2 2230 module allows for a lower-cost wireless deployment over PCIe-based solutions. This solution requires a motherboard with an M.2 Key E connector for wireless.

EXPERIENCE THE INTEL® DIFFERENCE

Worldwide Regulatory Support
Intel® Dynamic Regulatory Solution

Enables worldwide regulatory compliance on a single Intel® Wireless-AC adapter SKU. The Intel® Dual Band Wireless-AC 8265 Desktop Kit detects its location and automatically optimizes the Wi-Fi settings to local regulatory requirements, simplifying global enterprise procurement. Future regulatory changes are easily managed during the product lifecycle.

BUSINESS-CLASS WIRELESS

Intel® PROSet/Wireless Software⁴

Includes advanced IT tools to improve security, reduce complexity, and save IT time and money. Streamlines client deployments and allows remote management of wireless settings and profiles by IT managers.

INTEL® DUAL BAND WIRELESS-AC 8265 TECHNICAL SPECIFICATIONS

General

Retail Single Box Dimensions (H x W x D)	145 mm x 205 mm x 26 mm
Retail Single Box Weight	143.5g
Overpack 5u Dimensions (H x W x D)	160 mm x 230 mm x 150 mm
Overpack 5u Weight	727.5g
WsP Module Dimensions (H x W x D)	22 mm x 30 mm x 2.4 mm
WsP Module Weight	2.6g
RF Cable	Coaxial cable OD 1.13 mm FEP Black Jacket
Connectors	SMA, male, brass, gold plated, insulated; MHF IV plug, gold plated
Antenna	Frequency 2.4-2.5GHz/5.15-5.85GHz, SMA plug
Antenna Diversity	Supported
Radio ON/OFF Control	Supported
Motherboard Connector Interface	M.2: key E or A for wireless
Operating Temperature (Adapter Shield)	0°C to +80°C
Humidity Non-Operating	50% to 90% RH non-condensing (at temperatures of 25°C to 35°C)
Operating Systems	Microsoft Windows 7*, Microsoft Windows 8.1*, Microsoft Windows 10*, Linux* (limited feature support)
Wi-Fi Alliance	Wi-Fi CERTIFIED* a/b/g/n/ac, WMM*, WMM-PS*, WPA*, WPA2*, WPS2*, Protected Management Frames, Wi-Fi Direct* for peer-to-peer device connections, Wi-Fi Miracast* as Source
IEEE WLAN Standard	IEEE 802.11a/b/g/n/ac, 802.11d, 802.11e, 802.11h, 802.11i, 802.11w; 802.11r, 802.11k, 802.11v pending OS support; Fine Timing Measurement based on 802.11REVmc
Roaming ⁵	Supports seamless roaming between access points
Bluetooth*	Dual Mode Bluetooth* 4.2, BLE

Security⁶

Authentication	WPA* and WPA2*, 802.1X (EAP-TLS, TTLS, PEAP, LEAP, EAP-FAST), EAP-SIM, EAP-AKA, EAP-AKA'
Authentication Protocols	PAP, CHAP, TLS, GTC, MS-CHAP*, MS-CHAPv2
Encryption	64-bit and 128-bit WEP, 128-bit AES-CCMP
Wi-Fi Direct* Encryption and Authentication	WPA2-PSK, AES-CCMP

Compliance

Regulatory	For a list of country approvals, please contact your local Intel representatives.
U.S. Government	FIPS ⁷ , FISMA
Product Safety	UL, C-UL, CB (IEC 60950-1)

PRODUCT NAME	MODEL NUMBER	VERSION
Intel® Dual Band Wireless-AC 8265 Desktop Kit	8265NGWMG.DTX1	802.11ac, 2x2, Bluetooth* 4.2



For more information on Intel® Wireless products, visit intel.com/wireless

¹ Based on the theoretical maximum bandwidth enabled by 2x2 802.11ac implementations. Actual wireless throughput and/or range will vary depending on your specific operating system, hardware, and software configurations. Check with your device manufacturer for details.

² 802.11ac downlink MU-MIMO technology allows concurrently serving multiple devices simultaneously, in turn increasing network capacity by up to 3x while improving per-user throughput.

³ Compared to 802.11n 40MHz channels, 802.11ac 80MHz provides 3x more bandwidth per stream (Max data rate for 2x2 802.11n 40MHz channel is 300Mbps, 150Mbps per stream; Max data rate for 2x2 802.11ac 80MHz channel is 867Mbps, 433Mbps per stream).

⁴ Intel® PROSet/Wireless Software may not be supported by your device manufacturer. Check with your device manufacturer for details on availability.

⁵ Roaming is supported only within each respective band and mode of access points.

⁶ Some security solutions may not be supported by your device operating system and/or by your device manufacturer. Check with your device manufacturer for details on availability.

⁷ Microsoft Windows 7*, Microsoft Windows 8.1* and Microsoft Windows 10*.

Software and workloads used in performance tests may have been optimized for performance only on Intel® microprocessors. Performance tests, such as SYSmark* and MobileMark*, are measured using specific computer systems, components, software, operations, and functions. Any change to any of those factors may cause the results to vary. You should consult other information and performance tests to assist you in fully evaluating your contemplated purchases, including the performance of that product when combined with other products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Intel's Terms and Conditions of Sale for such products, Intel assumes no liability whatsoever, and Intel disclaims any express or implied warranty, relating to sale and/or use of Intel products including without limitation, liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright or other intellectual property right. Intel products are not intended for use in medical, lifesaving, or life-sustaining applications. Intel may make changes to specifications and product descriptions at any time, without notice. For the most current product information, please visit: <http://www.intel.com/wireless>

Intel, Intel Core, and the Intel logo are trademarks or registered trademarks of Intel Corporation or its subsidiaries in the United States and other countries.

* Other names and brands may be claimed as the property of others. For more information, visit: <http://www.intel.com/content/www/us/en/legal/trademarks.html>

Copyright © 2017 Intel Corporation. All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Intel:](#)

[8265.NGWMG.DTX1](#)