

# swissbit®

Product Fact Sheet

## Industrial CFexpress Card

**G-20 Series**  
CFexpress v2.0, Type B, 3D TLC

Industrial Temperature Grade

Date: November 18, 2021  
Revision: 1.00



## Product Summary

- **Capacities:** 15 GBytes, 30 GBytes, 60 GBytes, 120 GBytes, 240 GBytes, 480 GBytes
- **Form Factor:** CFexpress® Type B card (38.5mm x 29.6mm x 3.8mm)
- **Compliance<sup>1</sup>:** CFexpress v2.00
- **Interface:** PCIe Gen3 x 2 Lanes
- **Command Sets:** Supports NVMe 1.3
- **Performance:**
  - Read Performance: Sequential Read up to 1,615 MBytes/s, Random Read 4K up to 115,000 IOPS
  - Write Performance: Sequential Write up to 827 MBytes/s, Random Write 4K up to 131,000 IOPS
- **Host Memory Buffer (HMB):** Support for increased random performance
- **Operating Temperature Range<sup>2</sup>:**
  - Industrial: -40 °C to 85 °C
- **Storage Temperature Range:** -40°C to 85°C
- **Operating Voltage:** 3.3V supply voltage
- **Low Power Consumption**
- **Power:**
  - Power States PSo, PS1, PS2, PS3 and PS4
  - Thermal Throttling supported
- **Data Retention:** 10 Years @ Life Begin; 1 Year @ Life End
- **High-Performance Processor with Integrated, Parallel Flash Interface Engines:**
  - 3D NAND Flash
  - LDPC Code ECC (up to 120bit corrections per 1KByte page)
- **High Reliability**
  - Designed for Industrial and Automotive market
  - Ideal for applications like automation, embedded computing, gaming, IIoT and NetCom
  - Optimized for long life cycle that requires superior data retention as well as power fail safety
  - Mean Time Between Failure: >2,000,000 hours
  - Data Reliability: < 1 non-recoverable error per 10<sup>16</sup> bits read
  - Number of insertion/removal cycles: up to 12,000

<sup>1</sup> The verification of host system and storage device compatibility is in customer's responsibility. Swissbit can provide guidance and support on request.

<sup>2</sup> Adequate airflow is required to ensure the drive temperature, as reported in the S.M.A.R.T. data, does not exceed the specified maximum operating temperature.

# Product Fact Sheet

## G-20 Series



### Product Features

- Dynamic and Static Wear Leveling
- Subpage Mode Flash Translation Layer (FTL)
- Data Care Management
  - Active: Adaptive Read Refresh
  - Passive: Background Media Scan
- Lifetime Enhancements
  - Dynamic Bad Block Remapping
  - Write Amplification Reduction
- Power Fail Data Loss Protection
- Data set management support (TRIM)
- Active State Power Management (ASPM) Support
- In-Field Firmware Update<sup>3</sup>
- Enterprise-Grade Self-Monitoring, Analysis, and Reporting Technology (S.M.A.R.T.)
- Gold-Plated Connector (IPC-6012B Class 2 Compliant)
- End-to-End (E2E) Data Protection
- AES256 Encryption (on request)
- Life Cycle Management, Controlled "Locked" BOM
- RoHS / REACH compliant
- Swissbit Life Time Monitoring (SBLTM) Tool and SDK for SBLTM (on request)



### Order Information for G-20

Density	Part Number	Temp. Range	Flash Technology
15GB	SFCE015GW1EC1T0-I-5E-111-STD	-40°C to 85°C	3D NAND Flash TLC-mode
30GB	SFCE030GW1EC1T0-I-5E-111-STD		
60GB	SFCE060GW1EC2T0-I-5E-111-STD		
120GB	SFCE120GW1EC4T0-I-5E-111-STD		
240GB	SFCE240GW1EC4T0-I-6F-111-STD		
480GB	SFCE480GW1EC4WD-I-6F-111-STD		

### Why Swissbit?

Swissbit is focused on the design, development, manufacture, and support of leading edge memory and storage solutions for the worldwide OEM/ODM marketplace. As a global supplier, Swissbit recognizes and addresses the higher level of application requirements of today's industrial, Netcom, and automotive customers by providing best-in-class products and services, with uncompromised attention to driving overall value and quality.

<sup>3</sup> The support of In-Field FW update capabilities on host systems is recommended.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Swissbit:

[SFCE015GW1EB1TO-I-5E-111-STD](#) [SFCE030GW1EB1TO-I-5E-111-STD](#) [SFCE060GW1EB2TO-I-5E-111-STD](#)  
[SFCE120GW1EB4TO-I-5E-111-STD](#) [SFCE240GW1EB4TO-I-6F-111-STD](#)