

ULI-224D ULI-224T ULI-224TCL

BB-4WSD9R
BB-4WSD9TB
BB-4WSD90TB

Inline, Commercial-grade RS-232 to RS-485 Serial Converters – with port power options



Features

- Convert RS-232 to RS-485 signals
- Extend RS-232 data signals up to 1.2 km
- Data rate: 115.2 kbps
- 2000V two-way optical isolation (ULI-224TCL)
- Quick, inline installation
- DIP switch selectable RS-422 or RS-485
- RS-232 port-power or 12 Vdc external power (sold separately)
- Isolated model requires 12 Vdc external power (sold separately)

Introduction

Advantech ULI series converters convert RS-232 to RS-422/RS-485 using either port-power or an external power supply. Data is converted in both directions, RS-232 TD is converted to balanced RS-422 or RS-485 TD. Received RS-422/485 signals are converted to RS-232. Automatic Send Data Control eliminates the need for programming hardware handshaking signals to control RS-422 or RS-485 operation. Model ULI-224TCL provides 2000 V optical isolation and requires an external power source.

Specifications

Serial Technology

- Data Rate 115.2 kbps, max.
- RS-232 Connector All models: DB9 female (DCE)
- RS-232 Signals RD, TD, GND
- RS-422/485 Connector

| | |
|------------|----------------|
| ULI-224D | DB9 female |
| ULI-224T | Terminal block |
| ULI-224TCL | Terminal block |

- RS-422/485 Signals TDA(-), TDB(+), RDA(-), RDB(+), GND
- RS-422/485 Operation DIP switch selectable RS-422 or RS-485
RS-485 2-wire or 4-wire, RS-422 4-wire
4.7k Ohms
- Biasing Resistors None
- Termination None
- Isolation ULI-224TCL: 2 kV, 2-way optical
- LEDs ULI-224TCL: TD, RD

Power

- Port Power RS-232 handshake lines
Pins 7 (RTS) and 8 (CTS) tied together.
Pins 6 (DSR), 1 (DCD) and 4 (DTR) tied together.

| Model: | Connector: | Port Power: | 12Vdc External Power (PSU#): |
|------------|------------------|-----------------|--------------------------------|
| ULI-224D | 2.5mm plug, tip+ | RS232 handshake | BB-SMI6B-12V-P230C1 (optional) |
| ULI-224T | 2.5mm plug, tip+ | RS232 handshake | BB-SMI6B-12V-P230C1 (optional) |
| ULI-224TCL | Terminal block | – | BB-SMI6B-12-V-ST (required) |

Mechanical

- Enclosure Plastic
- Installation Inline
- Dimensions

| | |
|------------|--------------------|
| ULI-224D | 7.8 x 4.3 x 2.0 cm |
| ULI-224T | 9.0 x 4.3 x 2.3 cm |
| ULI-224TCL | 9.8 x 4.3 x 2.3 cm |

Weight

| | |
|------------|-----------------------------------|
| ULI-224D | 0.049 kg (net, without packaging) |
| ULI-224T | 0.05 kg (net, without packaging) |
| ULI-224TCL | 0.05 kg (net, without packaging) |

Meantime Between Failures (MTBF)

- Calculation Method MIL217F Parts Count Reliability Prediction

| | |
|------------|--------------|
| ULI-224D | 880179 hours |
| ULI-224T | 345242 hours |
| ULI-224TCL | 179604 hours |

Environmental

- Operating Temperature 0 to +70 °C
- Storage Temperature -40 to +85 °C
- Operating Humidity 95%, non-condensing

Regulatory / Approvals / Certifications

- FCC, CE 2014/30/EU - Electromagnetic Compatibility
2011/65/EU amended by (EU) 2015/863 Reduction of Hazardous Substances (RoHS)
- CE Directives 2012/19/EU - Waste Electrical and Electronic Equipment
EN 55032 Class B - Electromagnetic Compatibility of Multimedia Equipment - Emission Requirements
EN 55024 - Information Technology Equipment - Immunity Characteristics - Limits and Methods of Measurement
EN 61000-6-3 + A1 - Generic Emission Standard for Residential, Commercial and Light-industrial Environments (Class B)
EN 61000-6-1 - Generic Immunity Standard for Residential, Commercial and Light-industrial Environments
- CE Standards (EMC)
- Other Standards

Ordering Information

| Model | Part Number to Order | Description |
|------------|----------------------|---|
| ULI-224D | BB-4WSD9R | RS-232 to RS-422/485 Converter – DB9F/DB9F |
| ULI-224T | BB-4WSD9TB | RS-232 to RS-422/485 Converter – DB9F/TB |
| ULI-224TCL | BB-4WSD90TB | RS-232 to RS-422/485 Converter – DB9F/TB, 2kV Isolation |

Accessories – Sold Separately

- BB-SMI6B-12V-P230C1 PSU, 12Vdc, 6W, 2.5mm plug, int'l AC input, int'l AC blades
(Optional for ULI-224D, ULI-224T)
- BB-SMI6B-12-V-ST PSU, 12Vdc, 0.5A, 8W, stripped/tinned
(Required for ULI-224TCL)

ULI-224TB BB-485BAT3

Battery Powered RS-232 to RS-422/485 Serial Converter



Features

- Change RS-232 TD and RD to RS-485 signals
- Extend RS-232 data signals up to 1.2 km
- Data rates up to 115.2 kbps
- 3 powering options: battery (2) AAA, RS-232 handshake lines, or external power supply (not included, sold separately)
- Quick, easy inline installation
- Automatic Send Data Control – no software drivers necessary

Introduction

With three power options, Model ULI-224TB (BB-485BAT3) is ideal for field service applications. Use battery power with a low-power RS-232 port (laptop), when handshake lines are unavailable, or when a PSU is not possible. The unit draws available power from the RS-232 port getting additional current from the batteries. If you have a full-power port and handshake lines, turn Off the battery switch to use port-powering, saving the batteries for emergencies. (Battery On/Off switch conserves battery life; it does not turn on/off all power.)

Specifications

Serial Technology

- **Data Rate** 115.2 kbps, max.
- **RS-232 Connector** DB9 female (DCE)
- **RS-232 Signals** RD, TD, GND, DCD, DTR, DSR, RTS, CTS
- **RS-232 Port Power** Pins 7 (RTS) and 8 (CTS) tied together.
Pins 6 (DSR), 1 (CD) and 4 (DTR) tied together.
Terminal Block
- **RS-422/485 Connector** TDA (-), TDB (+), RDA (-), RDB (+), GND
- **RS-422/485 Signals** DIP switch selectable RS-422 or RS-485
- **RS-422/485 Operation** RS-485 2-wire or 4-wire, RS-422 4-wire
- **Biasing Resistors** 4.7k Ohms
- **Termination** None

Power

- **Source #1: Battery** (2) AAA batteries (not included)
- **Source #1: Battery Life** 7 hours fully loaded with no port power available.
100 to 250 hours, typical.
- **Source #2: RS-232** Port-powered from RS-232 handshake lines
(requires 7-12 Vdc on at least one handshake line)
- **Source #3: External** 12 Vdc external PSU (not included, sold separately)
- **Source #3: Connector** Terminal block
- **Input Voltage** 12 Vdc @ 100 mA

Mechanical

- **Dimensions** 9.0 x 6.5 x 2.8 cm (3.6 x 2.6 x 1.1 in)
- **Enclosure** Plastic, ABS
- **Installation** Inline
- **Weight** 0.104 kg (net, without packaging)

Meantime Between Failures (MTBF)

- **MTBF** 241370 hours
- **Calculation Method** MIL217F Parts Count Reliability Prediction

Environmental

- **Operating Temperature** 0 to +70 °C
- **Storage Temperature** -40 to +85 °C
- **Operating Humidity** 95%, non-condensing

Regulatory / Approvals / Certifications

- **FCC Part 15, CISPR**
- **CE Directives** 2011/65/EU amended by (EU) 2015/863 Reduction of Hazardous Substances Directive (RoHS)
2011/65/EU amended by (EU) 2015/863 Reduction of Hazardous Substances (RoHS)
2012/19/EU - Waste Electrical & Electronic Equipment
EN 55022 + AC Class A Emissions
EN 61000-6-1 Generic Standards for Residential, Commercial and Light-Industrial Environments
- **Standards**

Ordering Information

| Model Number | Part Number to Order | Description |
|--------------|----------------------|--|
| ULI-224TB | BB-485BAT3 | RS-232 to RS-422/485 Converter – DB9F/TB, (2) AAA batteries or port powered or external source |

Accessories – Sold Separately

- **BB-SMI6B-12-V-ST** PSU, 12 Vdc, 500 mA, stripped/tinned

ULI-224TC BB-485LDRC9 ULI-224TCI BB-485DRCI ULI-224TE BB-485DRCI-PH

Industrial-grade RS-232 to RS-485 Serial Converters



Features

- Converts RS-232 signals to RS-422/RS-485 signals
- Data rate: up to 115.2 kbps
- Extends data up to 1.2 km
- Optical isolation protection
- Wide operating temperature range
- Modbus compatible
- Automatic Send Data Control - no software drivers required
- External power source required (not included, sold separately)
- DIN rail and panel mount options
- UL Class 1 / Division 2 and cULus Recognized options



Introduction

ULI-224 series industrial adapters convert RS-232 to RS-422/485. Optical isolation and surge suppression protect connected equipment from ground loops and surges - ideal for factory/warehouse automation, in-cabinet, security and other applications. Models ULI-224TCI and ULI-224TE provide premium 3-way isolation on input, output and power lines. Model ULI-224TCI is UL C1/D2 certified for rugged industrial use. Model ULI-224TE meets IEC-61850-3 and IEEE-1613 for electrical substations.

Specifications

Serial Technology

- **Data Rate** 115.2 kbps, max.
- **LED Indicators** TD, RD, Power
- **Modes** RS-422 4-wire, RS-485 2-wire & 4-wire
- **RS-232** Signals: TD, RD, GND

| Model: | RS-232 Connector: | RS-422/485 Connector: | Termination, Ohms: | Industrial Bus: | Biasing: |
|------------|-------------------|-----------------------|--------------------|--|-------------------------------------|
| ULI-224TC | DB9 female or TB | TB | 120Ω | Modbus ASCII/RTU | — |
| ULI-224TCI | DB9 female | TB | 120Ω | Modbus ASCII/RTU, Allen-Bradley® DH-485 compatible | — |
| ULI-224TE | DB9 female | TB | 120Ω | Modbus ASCII/RTU | 1.2KΩ XMT/RCV, built-in, switchable |

Isolation

- **Rating** 2000 V
- **Method** Optical
- **Lines Protected** ULI-224TC: Data lines
ULI-224TCI, ULI-224TE: Data lines, power

Surge Suppression

- **Method** TVS
- **Lines Protected** Data lines
- **Response Time** <1 pico-second
- **Peak Power Dissipation** ULI-224TC: 500 W, 7.5 bi-directional avalanche breakdown device
ULI-224TCI, ULI-224TE: 600 W

Environmental

- **Operating Temperature** ULI-224TC, ULI-224TCI: -40 to +80 °C
ULI-224TE: -40 to +85 °C
- **Storage Temperature** -40 to +85 °C (-40 to +185 °F)
- **Operating Humidity** 95%, non-condensing

Power

- **Source** External power required (sold separately)

| Model: | Connector: | Input Voltage: | Consumption: |
|------------|----------------|----------------|--------------|
| ULI-224TC | Terminal block | 10-30 Vdc | 0.5 W |
| ULI-224TCI | Terminal block | 10-48 Vdc | 0.96 W |
| ULI-224TE | Terminal block | 10-48 Vdc | 0.5 W |

Mechanical

| Model: | Enclosure: | Mounting: | Dimensions, mm: | Weight (net, without packaging): |
|------------|---------------|--------------------|-----------------|----------------------------------|
| ULI-224TC | IP20, plastic | DIN rail | 25 x 79 x 95 | 0.249 kg |
| ULI-224TCI | IP30, plastic | DIN rail | 114 x 33 x 124 | 0.204 kg |
| ULI-224TE | IP30, metal | Panel (DIN option) | 132 x 93 x 31 | 0.209 kg |

Mean Time Between Failures (MTBF)

- **Calculation Method** MIL217F Parts Count Reliability Prediction

| | |
|------------|--------------|
| ULI-224TC | 257448 hours |
| ULI-224TCI | 254617 hours |
| ULI-224TE | 163611 hours |


Regulatory/Approvals/Certifications

- **CE Directives (all)** 2014/30/EU – Electromagnetic Compatibility (EMC)
2011/65/EU amended by (EU) 2015/863 Reduction of Hazardous Substances (RoHS)
2012/19/EU – Waste Electrical and Electronic Equipment

| Model: | Regulatory: | CE Standards (EMC): | IEC Standards: |
|------------|--|--|---|
| ULI-224TC | FCC, UL Recognized Comp. #E222870, KCC | EN 55032 Class B – Electromagnetic Compatibility of Multimedia Equipment – Emission Requirement EN 55024 – Information Technology Equipment - Immunity Characteristics – Limits and Methods of Measurement | — |
| ULI-224TCI | FCC, UL C1/D2 #E245458, UL 508 #E222870 | EN 55011+AC – Information Technology Equipment – Class A RF Emissions EN 61000-6-2 – Generic Immunity Standard for (Heavy) Industrial Environments | EN 61000-6-1 – Generic Immunity Standards for Residential, Commercial and Light-Industrial Environments |
| ULI-224TE | FCC, UL C1/D2 #E245458, IEEE-1613, IEC-61850 | | — |


Dimensions - ULI-224TC

Unit = mm




Dimensions - ULI-224TCI

Unit = mm



Dimensions - ULI-224TE

Unit = mm



Ordering Information

| Model Number | Part Number to Order | Description |
|--------------|----------------------|--|
| ULI-224TC | BB-485LDR9 | RS-232 to RS-422/485 Converter – 2-way Isolation, RS-232 DB9/TB to RS-422/485 TB |
| ULI-224TCI | BB-485DRCI | RS-232 to RS-422/485 Converter – 3-way Isolation, DB9/TB, UL C1/D2, UL508, AB® DH-485 |
| ULI-224TE | BB-485DRCI-PH | RS-232 to RS-422/485 Converter – 3-way Isolation, DB9/TB, UL C1/D2, IEEE1613, IEC61850 |

ULI-224TH ULI-224THC

BB-SCP211-DFTB3

BB-SCP311-DFTB3

Compact, Panel Mount RS-232 to RS-485 Serial Converters



Features

- Convert RS-232 data signals to RS-422/485 signals
- 2kV optical isolation (Model# ULI-224THC)
- ESD protection: 8 kV contact, 15 kV air
- Data rate: up to 460.8 kbps (bit-wise enable)
- -40 to +80 °C wide operating temperature (model# ULI-224THC)
- Rugged metal panel mount case (DIN rail adapters sold separately)
- 10-30 Vdc external power source (not included, sold separately)
- UL Listed

Introduction

ULI- series RS-232 to RS-422/485 converters meet heavy industrial EMC standards. Bit-wise enabled circuitry automatically detects character time-outs – no need to set DIP switches for baud rate. Basic model ULI-224TH is designed for less demanding temperatures or when isolation is not required, such as applications where the data line does not exit the control cabinet. Model ULI-224THC is more robust and suitable for protecting expensive control equipment.

Specifications

Serial Technology

- Data Rate 460.8 kbps, max.
- RS-232 Connector DB9 female (DCE)
- RS-232 Signals TD, RD, GND
- RS-422/485 Connector Terminal block, removable
- Modes RS-422 4-wire, RS-485 2-wire & 4-wire
- LED Indicators TD, RD (Green LED, also indicates Power)
- Industrial Bus Modbus ASCII/RTU
- Biasing 1k Ω , switchable
- Termination, Ohms 120 Ω , switchable

Isolation

- Rating 2000 V (model# ULI-224THC)
- Method Optical
- Lines Protected Data lines

Surge Suppression

- DC Ports +/- 0.5 kV +/- 1 kV
- Signal Ports +/- 1 kV

Environmental

- Operating Temperature ULI-224TH: 0 to +70 °C
ULI-224THC: -40 to +80 °C
- Storage Temperature -40 to +85 °C
- Operating Humidity 95%, non-condensing

Power

- Source External PSU required (not included, sold separately)
- Connector Terminal block, removable
- Input Voltage 10-30 Vdc
- Consumption 1.0 Watt, max.

Mechanical

- Enclosure IP30, metal
- Mounting Panel (2 panel mount brackets included)
- Dimensions 99.1 x 22.9 x 73.7 mm
- Weight 0.15 kg (net, without packaging)

Meantime Between Failures (MTBF)

- MTBF ULI-224TH: 313926 hours
ULI-224THC: 217576 hours
- Calculation Method MIL217F Parts Count Reliability Prediction

Regulatory/Approvals/Certifications

- Emissions FCC Class B, CISPR Class B (File# EN55022)
- Regulatory UL Listed, UL File# E22870
- CE Directives 2014/30/EU - Electromagnetic Compatibility (EMC)
2011/65/EU amended by (EU) 2015/863 Reduction of Hazardous Substances (RoHS)
2012/19/EU - Waste Electrical and Electronic Equipment
EN 55032 Class B – Electromagnetic Compatibility of Multimedia Equipment - Emission Requirements
EN 55024 - Information Technology Equipment – Immunity Characteristics – Limits and Methods of Measurement
EN 61000-6-2 – Generic Immunity Standard for (Heavy) Industrial Environments
- CE Standards (EMC)
- ULI-224THC (only)

Ordering Information


| Model Number | Part Number to Order | Description |
|--------------|----------------------|---|
| ULI-224TH | BB-SCP211-DFTB3 | RS-232 to RS-422/485 Converter, DB9F/TB, Non-isolated, Standard Temp. |
| ULI-224THC | BB-SCP311T-DFTB3 | RS-232 to RS-422/485 Converter, DB9F/TB, 2kV Isolation, Wide Temp. |

Accessories – Sold Separately

- BB-SMI6-12-V-ST PSU, 12 Vdc, 500 mA, 6 W, stripped/tinned, international AC input & blades
- BB-DRAD35 DIN rail mounting clips, 35mm

Dimensions

Unit = mm / in



ULI-224 Series Selection Guide

RS-232 to RS-422/485 Converters



Common Features

- Convert RS-232 to RS-422/485 signals
- Data rates: up to 115.2 kbps or 480.8 kbps
- Industrial designs and specifications
- Automatic Send Data Control
- Isolation and surge suppression options
- Industrial protocol support options
- Wide operating temperature
- External, port or battery powering
- DIN rail, panel mount or in-line installation

Serial Converters Comparison Table

| Model Number | ULI-224TC | ULI-224TCI | ULI-224TE | ULI-224TH | ULI-224THC | ULI-224D | ULI-224T | ULI-224TCL | ULI-224TB |
|--|--|---|---|---|--|--|----------------|----------------------|---|
| Part Number to Order | BB-485LDC9 | BB-485DRCI | BB-485DRCI-PH | BB-SCP211-DFTB3 | BB-SCP311T-DFTB3 | BB-4WSD9R | BB-4WSD9TB | BB-4WSD90TB | BB-485BAT3 |
| Description | Industrial-grade RS-232 to RS-422/485 Converters | | | Compact, Panel Mount RS-232 to RS-422/485 Converters | | In-line, Commercial-grade RS-232 to RS-422/485 Converters | | | Battery-Powered RS-232 to 422/485 Converter |
| Key Features | Dual RS-232 connectors (terminal block & DB9) | 3-way isolation, A-B® DH-485, UL C1/D2, Oil & Gas | 3-way isolation, UL C1/D2, IEEE1613, IEC-61850, Power Utilities | Small Form Factor, Panel Mount | | Inline Installation | | | 3 power options |
| Industrial Rating | Light | | | Heavy | | Light | | | |
| RS-232 Connector | Terminal block (DB9 option) | DB9 female | | | | | | | |
| RS-422/485 Connector | Terminal block | | | | | DB9 female | Terminal block | | |
| Data Rate, maximum | 115.2 kbps | | | 460.8 kbps | | 115.2 kbps | | | |
| Modes (RS-422 4-wire RS-485 2 & 4 wire) | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| LEDs | TD, RD, PWR | | | TD, RD | | - | - | TD, RD | - |
| Isolation | 2 kV (input, output) | 2 kV (input, output, power) | | - | 2 kV (input, output) | - | - | 2 kV (input, output) | - |
| Surge Suppression | 500 W | 600 W | | ± 0.5 k Vdc ports, ±1 kV signal ports | | - | - | - | - |
| Modbus | ✓ | Allen-Bradley® DH-485 | ✓ | ✓ | ✓ | - | - | ✓ | - |
| Automatic Send Data Control | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ | ✓ |
| Operating Temperature | -40 to +80 °C | -40 to +85 °C | | -0 to +70 °C | -40 to +80 °C | 0 to +70 °C | | | |
| External Power | 10 to 30 Vdc | 10 to 48 Vdc | | 10 to 30 Vdc | | 12 Vdc | | 10 to 48 Vdc | 12 to 16 Vdc |
| Power Connector | Terminal block | | | | | 2.5 mm plug, tip positive | | Terminal block | |
| Port Power | - | - | - | - | - | RS-232 handshake | | - | RS-232 handshake |
| Battery Power | - | - | - | - | - | - | - | - | (2) AAA |
| Enclosure | IP20, plastic | IP30, plastic | IP30, metal | IP30, metal | | Plastic | | | |
| Mounting Installation | DIN rail | | Panel (DIN option) | | | Inline | | | |
| Dimensions, mm | 25 x 79 x 95 | 114 x 33 x 124 | 132 x 93 x 33 | 99 x 23 x 74 | 99 x 23 x 74 | 78 x 43 x 20 | 90 x 43 x 23 | 98 x 43 x 23 | 90 x 65 x 28 |
| MTBF (MIL217F), hours | 257448 | 254617 | 163611 | 313926 | 217576 | 880179 | 345242 | 179604 | 241370 |
| Regulatory/Approvals/ Certifications | FCC, CE | | | | | | | | |
| | KCC, cULus Recognized #E222870, EN55021, EN55024 | UL 508 #E222870, UL C1/D2 #E245458*, EN55032/B, EN55024, EN61000-6-1 | UL C1/D2 #E245458*, IEC61850-3†, IEEE-1613‡, EN55011+AC, EN61000-6-2 | UL, EN55032/B, EN55024 | UL, EN55032/B, EN55024, EN61000-6-2 | EN55032/B, EN55024, EN61000-6-3+A1, EN61000-6-1 | | | EN55022+AC, EN61000-6-1 |



*UL C1/D2
#E245458



†IEC61850-3



‡IEEE-1613

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[BB-4WSD9R](#)