

# ULI-238TS BB-CANOP

## CAN (Control Area Network) Optical Isolator



### Features

- Boost signals and increase node capacity of CAN networks
- Works with various CAN protocols and frame lengths
- 2,000 Vdc optical isolation protection from surges and spikes
- Data rate: up to 250 kbps (bit-wise enable)
- DIN rail mount enclosure – ideal for industrial cabinets
- 10-30 Vdc external power required (not included, sold separately)

### Introduction

Model ULI-238TS increases the node capacity of CAN (Control Area Network) systems while protecting from component destroying surges and transients. 2,000 Vdc optical isolation separates and protects critical segments of the system from the rest of the CAN network. Protocol independent, it works with different CAN protocols and frame lengths. Bit-wise enable function automatically adjusts for different baud rates. See quick start guide for bit-wise enable and termination details.

### Specifications

#### Serial Technology

- Baud Rate 250 kbps, maximum
- CAN Connectors Terminal blocks
- Turnaround <2 $\mu$  seconds
- LEDs TD, RD (may be difficult to see at high baud rates)

#### Isolation

- Voltage 2k Vdc
- Time 2kV RMS/1 minute

#### Power

- Input 150 mA @ 12 V, fully loaded
- Source External PSU, 10-30 Vdc, required (sold separately)

#### Environmental

- Operating Temperature 0 to +70 °C
- Storage Temperature -40 to +85 °C
- Operating Humidity 95%, non-condensing

#### Mechanical

- Enclosure Plastic
- Dimensions 93 x 86 x 36 mm
- Mounting In-line
- Weight 80 gm

#### Meantime Between Failures (MTBF)

- Calculation Method MIL217F Parts Count Reliability Prediction
- MTBF 269297 hours

#### Regulatory/Approvals/Certifications

- Approvals FCC, CE
- CE Directives 2014/30/EU – Electromagnetic Compatibility Directive  
2011-65/EU – amended by (EU) 2015/863  
Reduction of Hazardous Substances Directive  
2012/19/EU – Waste Electrical and Electronic Equipment  
EN 55032 – Class A Electromagnetic Compatibility of Multimedia Equipment – Emission Requirements  
EN 55024 – Information Technology Equipment – Immunity Characteristics – Limits and Methods of Measurement  
EN 61000-6-1 – Generic Immunity Standard for Residential, Commercial and Light-industrial Environments
- CE Standards

### Application - ULI-238TS



### Ordering Information

Model	Part Number to Order	Description
ULI-238TS	BB-CANOP	2 kV CAN Isolator

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[CANOP](#) [BB-CANOP](#)