


SBC86831

Socket M Intel® Core™2 Duo Mini ITX SBC with Intel® 945GME+ICH7M/-DH Chipset, VGA/LVDS, PCI Express x16 and Firewire



System


CPU	Socket M for Intel® Core™2 Duo/ Core™ Duo/ Core™ Solo/ Celeron® M processors with FSB 533/667 MHz; Intel® Celeron® M processor ULV 423 onboard
System Memory	2 x 240-pin DIMM supports DDR2-533/667 max. up to 4 GB
Chipset	Intel® 945GME + ICH7M/ICH7M-DH
BIOS	Phoenix-Award 4Mbit with RPL/PXE LAN Boot ROM, SmartView and customer CMOS backup
SSD	1 x CompactFlash™ type-II (optional)
Watchdog Timer	255 levels, 1~255 sec.
Expansion Interface	1 x PCIe x16 graphics port supports for SDVO or PCIe x1 devices 1 x PCI for 32-bit PCI supports 2 bus masters 1 x PCI Express Mini Card (optional)
Battery	Lithium 3V/220 mAh
Power Requirements	Intel® Core™2 Duo T7600 2.33 GHz, 2 GB DDR2 Max. RMS: +5V_SBY @ 0.025A, +3.3V @ 0.105A, +5V @ 1.93A, +12V @ 1.583A, -12V @ NA
Size	170 x 170 mm
Board Thickness	1.6 mm
Temperature	0° ~ +60°C (32°F ~ 140°F), operation
Relative Humidity	10% ~ 95% relative humidity, non-condensing

I/O

MIO	1 x IDE; PATA-100 1 x FDD/LPT(default); with SPP/EPP/ECP supported 1 x PS/2 keyboard; 1 x PS/2 mouse 3 x RS-232 (COM 2/3/4); with +5V/+12V powered 1 x RS-232/422/485 (COM 1); with +5V/+12V powered
SATA	2 x SATA-150; with RAID 0/1 (optional with ICH7M-DH)
Hardware Monitoring	Detect CPU/system temperature, voltage and fan speed
Ethernet	2 ports as 10/100/1000Mbps support Wake-on-LAN, RPL/PXE Boot ROM with Realtek RTL8111B
Audio	AC'97 Codec audio as MIC-in/Line-out with Realtek ALC655
USB	8 x USB 2.0
Firewire	2 x IEEE 1394a
TPM	Infineon SLB9635 for trusted platform (optional)
SMBus	System Management Bus for advanced monitoring/control interface
Digital I/O	8 channels (3-IN & 5-OUT)

Features

- Socket M for Intel® Core™2 Duo/ Core™ Duo/ Core™ Solo processor with FSB 533/667 MHz
- With high performance integrated graphics controller and discrete solution through PCIe x16 interface
- RAID 0/1 (optional with ICH7M-DH)
- 4 COM ports for transaction terminal applications
- 8 USB 2.0 ports and 2 IEEE 1394a ports
- Display: VGA/LVDS



▲ Side view

Display

Chipset	Intel® GMA 950 graphics core
Memory Size	Intel® DVM T 3.0 compliant
Display Interface	1 x VGA 1 x LVDS; 18/24-bit single/dual channel

Packing List

Standard	Quick installation guide, user's manual/utility CD, cable, CPU cooler
-----------------	---

Cable		
Part Number	Description	Qty
593826A0000E	SATA signal cable 500 mm	1
59382601000E	Ultra DMA66 IDE cable 40-pin 455 mm	1
59384500200E	COM x 2 w/ bracket, P=2.0, L=250 mm	1
59386831000E	USB cable x 2 w/ bracket, P=2.54 mm L=180 mm	1

Ordering Information

Standard	SBC86831VGGAF (P/N: E386831100)	Socket M Mini ITX SBC with VGA/LVDS LCD, 2 10/100/1000Mbps Ethernet, AC'97 audio, 4 COM ports and firewire
-----------------	------------------------------------	--

SBC Services and Solutions

Systems on Modules

Embedded SBCs >EPIC

Embedded SBCs >3.5" Capa

Embedded SBCs >Nano-ITX

Embedded SBCs >Pico-ITX

Embedded SBCs >PC/104

Industrial Motherboards

Slot CPU Cards

Accessories

Appendix

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[SBC86831VGGAF](#)