


# GOT5100T-834

10.4" XGA/SVGA TFT Fanless Touch Panel Computer with Intel® Celeron® Processor J1900



1. Power switch
2. Terminal block for DC power input or
3. Screw conn. w/ AC power adapter
4. USB 3.0 x 2
5. COM 1 (RS-232/422/485)
6. COM 2 (RS-232/422/485)
7. Ethernet x 2
8. USB 2.0 x 2
9. Audio (Line-out)



▲ Side view



▲ Desktop stand



Fanless



Low Power



DDR3L



AiRD



IP65

## Features

- 10.4" XGA/SVGA TFT LCD display with LED backlight
- Fanless design with Intel® Celeron® processor J1900 and internal antenna
- 2 GbE LAN, 4 USB and 2 COM
- Plastic and IP65-rated front bezel
- Supports RFID (optional)
- Supports panel mount/wall mount/VESA arm

## Introduction

The GOT5100T-834 is a 10.4" Intel® Celeron®-based fanless touch panel computer. In response to market demand, this panel computer is a cost effective solution. It adopts a modern, super sleek and fanless design and is equipped with a 10.4" TFT LCD as well as Intel® Celeron® processor J1900 4 cores (Bay Trail). For wireless network connection, the GOT5100T-834 offers 2 PCI Express Mini Card slots. By just plugging in the mini card WLAN card, customers can have instant access to wireless LAN/GPRS/GSM/4G environments. Besides, it provides two types of power input. One is DC power input (9 to 36 VDC) with terminal block connector, and another is AC power adapter with screw type connector.

### Super Slim & Ultra Lightweight Design

The GOT5100T-834 is a super slim touch panel computer for space-limited environment with its thickness of 45.8 mm and weight of 1.8 kg only, which make it installed everywhere.

### Built-in Internal WLAN Antenna

The GOT5100T-834 provides 2 PCIe Mini Card slots and a built-in WLAN antenna for wireless network connections. By simply plugging in the wireless LAN card, customers can use the GOT5100T-834 in a wireless LAN/GPRS/GSM/4G environments.

### Aluminum Back Chassis with Excellent Thermal Solution

With Axiomtek's patent for plastic plus aluminum mechanism design, the GOT5100T-834 can dissipate the heat easily and keep the system operation stable.



## Specifications

Front Bezel	IP65, NEMA 4 rugged protection, plastic front bezel	
LCD Panel	Display Type	10.4" XGA/SVGA TFT LCD with LED backlight
	Brightness (cd/m <sup>2</sup> )	350 nits (XGA) 400 nits (SVGA)
	Resolution	1024 x 768 (XGA) 800 x 600 (SVGA)
	Viewing Angel (H/V)	140°/120°
Main System	CPU	Intel® Celeron® processor J1900 4 cores
	System Memory	1 x 204-pin DDR3L-1333 MHz SO-DIMM, up to 8GB
	BIOS	AMI UEFI BIOS
	Storage	1 x 2.5" 7/9.5 mm SATA HDD 1 x CFast™ or mSATA
	Watchdog Timer	255 levels, 0 to 255 sec.
I/O Connector	Onboard Graphics	Integrated in Intel® GFX
		2 x RS-232/422-485 (default RS-232, COM 1/2) 2 x 10/100/1000 Mbps Ethernet (Intel® i210IT) 2 x USB 2.0 2 x USB 3.0 1 x Audio (Line-out)
TPM	N/A	
Expansion Interface	1 x full-size PCI Express Mini Card slot with mSATA	
	1 x full-size PCI Express Mini Card slot with SIM	
Touchscreen	Resistive type	
Power Supply	1. DC version: 9 to 36 VDC with over-current protection fuse	
	2. AC version: 100 to 240 V AC-DC, 60W power adapter	
Power Consumption	32 W	
Dimensions (W x D x H)	292.5 x 45.8 x 235.8 mm (11.52" x 1.80" x 9.28")	
Packing Dimensions (W x D x H)	415 x 100 x 315 mm (16.34" x 3.94" x 12.4")	
Weight (net/gross)	1.8 kg (3.96 lb)/3 kg (6.61 lb)	
Environment	Operating temperature: 0°C to +50°C (+32°F to +122°F) (with W.T. DRAM/HDD in airflow condition)	
	0°C to +45°C (+32°F to +113°F) (with W.T. DRAM/HDD)	
	Relative humidity: 20% to 90% @ +40°C; non-condensing	
	Operation vibration: 2G, 5 to 500Hz, random for CFast™	
Certificate	CE	

## Ordering Information

### Standard

GOT5100T-834-J (P/N:E225100116)	10.4" SVGA fanless touch panel computer with Intel® Celeron® processor J1900, 5-wire resistive touch screen, AC-DC 60W power adapter (screw type connector) and EMI class B
GOT5100T-834-DC (P/N:E225100118)	10.4" SVGA fanless touch panel computer with Intel® Celeron® processor J1900, 5-wire resistive touch screen and 9 to36 VDC power input (terminal block connector)

### Optional

Wi-Fi + Bluetooth kit	
Speaker kit	
E226171106	Stand kit
E29R334100	RFID kit

\* Specification and certifications are based on options and may vary.

---

## Packing List

1 x GOT5100T-834  
1 x Adapter (GOT5100T-834-J)  
1 x Panel mount kit  
1 x Wall mount kit  
1 x Phoenix connector (GOT5100T-834 DC)

---

## Optional EOS Installation

WES7  
WE8S  
Windows® 10 IoT Enterprise

---

## Optional OS Installation


Windows® 7  
Windows® 8.1  
Windows® 10

---



▲ AC power adapter  
(for GOT5100T-834-J)

## Dimensions



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[GOT5100T-834-J](#) [GOT5100T-834](#) [GOT5100T-834-J-XGA](#) [GOT5100T-834-XGA](#) [GOT5100T-834-J-US](#) [GOT5100T-834-J-XGA-US](#) [GOT5100T-834-XGA-DC](#) [GOT5100T-834-DC](#) [GOT5100T-834 DC](#) [GOT5100T-834 J-US](#) [GOT5100T-834 N-DC](#) [GOT5100T-834 N-J-XGA-US](#) [GOT5100T-834 N-XGA-DC](#) [GOT5100T-834 XGA-DC](#)