



GOT3217WL-845-PCT NEW


21.5" FHD TFT Multi-touch Panel Computer with Intel® Pentium® Processor N3710
(0°C to +45°C)

Features

- 21.5" FHD 10-point multi-touch projected capacitive wide screen
- Fanless design with Intel® Pentium® processor N3710
- 2.5" SATA HDD & mSATA
- 3G, WLAN module & antennas (optional)
- 2 Gigabit LANs, 2 USB 3.0, 2 USB 2.0 & 2 COM ports
- IP65 aluminum front bezel
- Supports panel mount and optional VESA arm/desktop stand/wall mount
- Adjust RS-232/422/485 setting via BIOS



▲ Rear view



- | | | |
|--------------------------------------|------------------------------|---------------------------|
| 1. Terminal block for DC power input | 6. COM 2 (RS-232) | 11. Power Switch (ATX) |
| 2. Screw conn. w/ AC power adapter | 7. HDMI output | 12. Speaker |
| 3. USB 2.0 x 2 | 8. USB 3.0 x 2 | 13. Backlight switch |
| 4. Audio (Line-out) | 9. Ethernet x 2 | 14. Brightness adjust +/- |
| 5. COM 1 (RS-232/422/485) | 10. AT/ATX selectable switch | |



Introduction

The GOT3217WL-845-PCT adopts an 21.5-inch FHD LCD and supports Intel® Braswell processor. The Lite rugged industrial panel PC supports low power Intel® Pentium® processor N3710. It also provides two PCI Express Mini card slots for 3G, wireless network connectivity. This 21.5" multi-touch panel computer is suitable for transportation, heavy-duty industry, smart factory automation, and oil pipe monitoring systems.

21.5-inch FHD LCD with Projected Capacitive Multi-touch

The 21.5" FHD touch panel PC supports 250 nits brightness, able to display contents in HD resolution. With projected capacitive 10-point multi-touch screen, users can operate the device more directly and friendly. The hardness of touch glass surface is up to 7h for anti-scratch purpose.

WLAN Antenna Supported (optional)

The IP65-rated industrial panel PC, GOT3217WL-845-PCT, provides two PCI Express Mini card slots and WLAN antennas for 3G and wireless network connectivity.


Specifications

Front Bezel	IP65 front bezel	
LCD Panel	Display Type	21.5" FHD TFT LCD
	Brightness (cd/m ²)	250 nits
	Resolution	1920 x 1080
Main System	CPU	Intel® Pentium® processor N3710 4C @1.6 GHz (Braswell)
	Chipset	SoC Integrated
	System Memory	1 x 204-pin DDR3L-1333/1600 SO-DIMM, up to 8GB
	BIOS	AMI UEFI BIOS
	Storage	1 x 2.5" SATA HDD 1 x mSATA
	Watchdog Timer	255 levels, 0 ~ 255 sec.
	Onboard Graphics	Integrated Intel® HD Graphics

Specifications

I/O Connector	1 x RS-232 (COM 2) 1 x RS-232/422/485 (COM 1) 1 x Switch for power on/off (ATX) 1 x Audio (Line-out) 2 x USB 3.0 2 x USB 2.0 2 x 10/100/1000 Mbps Ethernet (Intel® i217LM & i210AT)
Expansion Interface	1 x Full-size PCI Express Mini Card with mSATA 1 x Full-size PCI Express Mini Card with SIM slot
Touchscreen	10-point projected capacitive multi-touch
Power Supply	1. DC version: 24 VDC 2. AC version: 12 VDC 60W adapter
Power Consumption	48 W
Dimensions	547.6 mm (21.56") (W) x 58.5 mm (2.30") (D) x 339.0 mm (13.35") (H)
Packing Dimensions	720 mm (28.34") (W) x 210 mm (8.27") (D) x 550 mm (2.17") (H)
Weight (net/gross)	7.6 kg (16.8 lb)/10.5 kg (23.1 lb)
Environment	Operating temperature: 0°C ~ +45°C (+32°F ~ +113°F) Relative humidity: 20% ~ 90% @ 40°C; non-condensing Operation vibration: 1 G, 10 ~ 500 Hz, random for 2.5" SATA HDD
Certificate	CE

Dimensions



Ordering Information

GOT3217WL-845-PCT-J	21.5" FHD TFT fanless touch panel computer with Intel® Pentium® N3710 1.6 GHz quad core processor, 10-point projected capacitive multi-touch screen and AC-DC 12 VDC power adapter (screw type connector)
GOT3217WL-845-PCT-DC	21.5" FHD TFT fanless touch panel computer with Intel® Pentium® N3710 1.6 GHz quad core processor, 10-point projected capacitive multi-touch screen and 24 VDC terminal block connector

Optional EOS Installation

Windows® 10 IoT Enterprise (64-bit)

Optional OS Installation

Windows® 10 (64-bit)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[GOT3217WL-845-PCT-DC](#) [GOT3217WL-845-PCT-J-US](#)