


IPC964-512-FL

4-slot Fanless Industrial System with LGA1151 Socket 7th/6th Gen Intel® Core™ i7/i5/i3 or Celeron® Processor, Intel® Q170, Front-access I/O, and PCIe & PCI Slots



1. 2 x Antenna opening

2. Remote switch

3. Mic-in & Line-out

4. 2 x LAN

5. VGA

6. Reset switch

7. Power on/off button with LED

8. Terminal block

9. HDD & power LED

10. 4 x USB 3.0

11. HDMI
12. AT/ATX quick switch

13. Extension system I/O module

(1) AX93511

(2) AX93512

(3) AX93516

(4) AX93519

(5) Blank I/O cover

14. Expansion interface

(1) AX96410

(2) AX96411

Features

- LGA1151 socket 7th/6th gen Intel® Core™ i7/i5/i3 or Celeron® processor, up to 65W (Kaby Lake/Skylake)*
- Intel® Q170 chipset
- Supports 4 expansion slots
- Power input: 24 VCD (uMin=19V/uMax=30V)
- Compact & front I/O design
- -10°C to +60°C operating temperature range
- Supports 2 swappable 2.5" HDD & RAID 0,1
- Supports ECM BIOS setting
- Supports WLAN module & antenna (optional)
- Supports TPM 2.0



▲ Rear view

Specifications

Standard Color	Silver
Construction	Aluminum extrusion heavy-duty cold-rolled steel
Processor	CPU Level7th/6th gen Intel® Core™ i7/i5/i3 & Celeron® processor up to 65W (Kaby Lake/Skylake)*
System	ChipsetIntel® Q170
System Memory	2 x DDR4-2133/2400 un-buffered SO-DIMM, up to 32GB
System I/O	1 x Power on/off button with LED (ATX) 1 x Remote switch 1 x Reset switch 1 x 3-pin terminal block 1 x AT/ATX selectable switch 2 x 10/100/1000 Mbps Ethernet (Intel® I210-AT) 4 x USB 3.0 1 x HDMI 1 x VGA 1 x Audio (Mic-in/Line-out)
TPM	TPM 2.0

Specifications

Expansion Interface	AX96410: 1 PCIe x16 + 3 PCIe x4 AX96411: 1 PCIe x16 + 1 PCIe x4 + 2 PCI (support by project) 1 x Full-size PCI Express Mini Card slot with SIM slot (USB & PCIe interface)
Storage	2 x 2.5" swappable HDD (15 mm height)
System Indicators	1 x Power LED 1 x HDD LED
Power Input	Type: ATX/AT Input: 24 VDC (uMin=19V/uMax=30V)
Operating Temperature	-10°C to +60°C (+14°F to +140°F) with 6th gen Intel® Core™ up to 35W and W.T. HDD/SSD* -10°C to +50°C (+14°F to +122°F) with 6th/7th gen Intel® Core™ up to 65W and W.T. HDD/SSD*
Storage Temperature	-20°C to +80°C (-4°F to +176°F)
Humidity	10% to 90%, non-condensing
Dimensions	188.1 mm (7.39") (W) x 192 mm (7.54") (H) x 230 mm (9.04") (D)
Weight (net/gross)	4.8 Kg (10.56 lb) / 5.9 Kg (12.98 lb)
Certifications	CE, FCC

* Please refer to the user manual for the list of CPU support and the operating temperature of the system.

Ordering Information

System

IPC964-512-DC-FL (P/N: E26G964100)	4-slot fanless industrial system with 7th/6th gen Intel® Core™ i7/i5/i3 processor, Intel® Q170, and front-access I/O
---------------------------------------	--

Extension System I/O Module & Expansion Interface

AX93511 (P/N: E29R127122)	4 x RS-232/422/485 module (default RS-232)
AX93512 (P/N: E29R127123)	2 x RS-232/422/485 with isolated 1.5kVDC & 8-in/8-out with isolated 1.5kVDC DIO module (support by project)
AX93516 (P/N: E29R127124)	4 x RS-232/422/485 with isolated 2kVDC module (support by project)
AX93519 (P/N: E29R127125)	1 x 10/100/1000 Mbps (Intel® or I210-AT) Ethernet, 2 x RS-232/422/485 & 2 x USB 3.0 module
726G9620610E	Blank I/O cover
AX96410 (P/N: 83964101000E)	1 x PCIe x16 + 3 PCIe x4
AX96411 (P/N: 83964111010E)	1 x PCIe x16 + 1 PCIe x4 + 2 PCI (support by project)

Optional Accessory

2.5" SATA HDD/SSD	
DDR4-2133/2400 un-buffered SO-DIMM, up to 32GB	
E29R127128	IPC964-512-FL fan module kit
E29R127129	Wall mount bracket kit
509000001500	Adaptor 24V/120W, wire only
50906A24000E	Adapter 24V/230W, wire only

Power Protection


DC Version

OVP (over voltage protection)
OCP (over current protection)
Reverse protection

Packing List

1 x IPC964-512-FL unit
1 x Screw pack
4 x Foot pad
1 x CPU grease
1 x Terminal block
1 x Remote power switch cable
1 x Holder bracket

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Axiomtek:](#)

[IPC964-512-DC-FL](#)