

WISE-4220

Industrial Wi-Fi 2.4GHz Wireless I/O Module

NEW



Features

- 2.4GHz Wi-Fi reducing the wiring cost during big data acquisition
- Easily extend the existing network by adding APs, and share existing Ethernet software
- Configured by mobile devices directly without installing any software or Apps
- Zero data loss using the log function with RTC time stamp
- Data can be automatically pushed to Dropbox or computer
- Supports RESTful web API in JSON format for IoT integration

Introduction

The WISE-4220 series is an Ethernet-based wireless IoT device, integrated with IoT data acquisition, processing, and publishing functions. As well as various I/O and sensor types, the WISE-4220 series provides data pre-scaling, data logic, and data logger functions. These data can be accessed via mobile devices and be published to the cloud with security at anytime and anywhere.

Features

IEEE 802.11 b/g/n 2.4GHz Wi-Fi with AP Mode

The Wi-Fi interface is easily integrated with wired or wireless Ethernet devices, users only need to add a wireless router or AP to extend existing Ethernet network to wireless. The limited AP mode enables the WISE-4220 to be accessed via other Wi-Fi devices directly as an AP.



HTML5 Web Configuration Interface

All the configuration interfaces are applied in web service, and the web pages are based on HTML5, so users can configure the WISE-4220 without the limitation of OS/devices. You can use your mobile phone or tablet to directly configure the WISE-4220.



Data Storage

The WISE-4220 can log up to 10,000 samples of data with a time stamp. The I/O data can be logged periodically, and also when the I/O status changes. Once the memory is full, users can choose to overwrite the old data to ring log or just stop the log function.



Cloud Storage

Data logger can push the data to file-based cloud services like Dropbox using pre-configured criteria. With RESTful API, the data can also be pushed to a private cloud server in the format of JSON. Users can setup their private cloud server using the provided RESTful API and their own platform.



Specifications

General

- **WLAN Standard** IEEE 802.11b/g/n
- **Frequency Band** 2.4GHz ISM Band
- **Transmit Power** 802.11b: 12.0 dBm \pm 1dBm
802.11g: 15.5 dBm \pm 1dBm
802.11n: 15.5 dBm \pm 1dBm
- **Antenna** Connector: Reverse SMA
Gain (Peak): 2.45 dBi
150m with line of sight
- **Outdoor Range** Plug-in screw terminal block (power)
- **Connectors** System (1.6 second) and
- **Watchdog Timer** Communication (programmable)
- **Certification** CE, FCC, IC, NCC, SRRC, RCM, VCCI, TELEC (CC3200 listed antenna)

▪ Dimensions (W x H x D)	70 x 102 x 38 mm
▪ Enclosure	PC
▪ Mounting	DIN 35 rail, wall, stack, and pole
▪ Power Input	10 ~ 50 V _{DC}
▪ Power Consumption	1.2 W @ 24 V _{DC}
▪ Power Reversal Protection	
▪ Supports User Defined Modbus Address	
▪ Supports Data Log Function	Up to 10000 samples with RTC time stamp
▪ Supported Protocols	Modbus/TCP, TCP/IP, UDP, DHCP, and HTTP
▪ Supports RESTful Web API in JSON format	
▪ Supports Web Server in HTML5 with JavaScript & CSS3	
▪ Supports System Configuration Backup and User Access Control	

Environment

▪ Operating Temperature	-25 ~ 70°C (-13~158°F)
▪ Storage Temperature	-40 ~ 85°C (-40~185°F)
▪ Operating Humidity	20 ~ 95% RH (non-condensing)
▪ Storage Humidity	0 ~ 95% RH (non-condensing)

WISE-4220-S231 (Built-in Temperature and Humidity Sensor)

Temperature Sensor

▪ Operating Range	-25°C ~ 70°C (-13°F ~ 157.9°F)
▪ Resolution	0.1 (°C/°F/K)
▪ Accuracy	±2.0°C (±35.6°F) (vertical installation)

Humidity Sensor

▪ Operating Range	10 ~ 90% RH
▪ Resolution	0.1% RH
▪ Accuracy	±4% RH @ 0%-50% RH ±10% RH @ 50%-60% RH ±13% RH @ 60%-90% RH

WISE-S214 (4AI/4DI)

Analog Input

▪ Channels	4
▪ Resolution	16bits Bipolar; 15bits Unipolar
▪ Sampling Rate	10Hz (Total) with 50/60Hz Rejection
▪ Accuracy	±0.1% for Voltage Input; ±0.2% for Current Input
▪ Input Range	0~150mV, 0~500mV, 0~1V, 0~5V, 0~10V, ±150mV, ±500mV, ±1V, ±5V, ±10V, 0~20mA, ±20mA, 4~20mA
▪ Input Impedance	>1MΩ (Voltage)
▪ Support Data	240 Ω (External resistor for current) Scaling and Averaging

Digital Input

▪ Channels	4 Dry Contact (Wet Contact by request for customization)
▪ Supports 200Hz Counter Input (32-bit + 1-bit overflow)	
▪ Supports keep/discard counter value on power-off	
▪ Support inverted digital input status	
▪ Support configuration by each channel	
▪ Support digital filter (min 0.1ms)	
▪ Support high-to-low and low-to-high latch	
▪ Supports 3kHz Frequency Input	

WISE-S250 (6DI, 2DO & 1RS-485)

Digital Input

▪ Channels	6 (Dry Contact)
▪ Supports 3kHz Frequency Input	
▪ Supports 200Hz Counter Input (32-bit + 1-bit overflow)	
▪ Supports keep/discard counter value on power-off	
▪ Support inverted digital input status	
▪ Support configuration by each channel	
▪ Support digital filter (min 0.1ms)	
▪ Support high-to-low and low-to-high latch	

Digital Output (Sink Type)

▪ Channel	2
▪ Output Current	100 mA
	At 0 → 1: 100 us
	At 1 → 0: 100 us
	(for Resistive Load)
▪ Supports Pules Output	5 kHz
▪ Max. Load Voltage	30V
▪ Support pulse high/low width and duty cycle adjustment	
▪ Support high to low and low to high delay time setup	

Serial Port

▪ Port Number	1
▪ Type	RS-485
▪ Data Bits	8
▪ Stop Bits	1, 2
▪ Parity	None, Odd, Even
▪ Baud Rate (bps)	1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200
▪ Protocol	Modbus/RTU (Total 64 addresses by 30 max. instructions)

WISE-S251 (6DI/1RS-485)

Digital Input

▪ Channels	6 Dry Contact (Wet Contact by request for customization)
▪ Supports 3kHz Frequency Input	
▪ Supports 200Hz Counter Input (32-bit + 1-bit overflow)	
▪ Supports keep/discard counter value on power-off	
▪ Support inverted digital input status	
▪ Support configuration by each channel	
▪ Support digital filter (min 0.1ms)	
▪ Support high-to-low and low-to-high latch	

Serial Port

▪ Port Number	1
▪ Type	RS-485
▪ Data Bits	8
▪ Stop Bits	1, 2
▪ Parity	None, Odd, Even
▪ Baud Rate (bps)	1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200
▪ Protocol	Modbus/RTU (Total 64 addresses by 30 max. instructions)

Ordering Information

Wi-Fi 2.4GHz Wireless I/O Module


▪ WISE-4220-A	Wi-Fi 2.4GHz Wireless I/O Module
▪ WISE-4220-S231-A	Wi-Fi 2.4GHz Wireless Module with Temperature and Humidity Sensor

WISE-S200 I/O Module

▪ WISE-S214-A	4AI/4DI
▪ WISE-S250-A	6DI, 2DO & 1RS-485
▪ WISE-S251-A	6DI & 1RS-485

Accessories

▪ 96PSD-A30W24-DS	DIN Rail Power Supply (1.25A Output Current)
▪ BB-RPS-V2-WR2-US	Power Supply, 12V/1A, US plug
▪ BB-RPS-V2-WR2-EU	Power Supply, 12V/1A, EU plug



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Advantech:](#)

[WISE-4220-A](#)