

2 Pt100 KN 3026

The KN Series Ceramic Wire Wound PRTDs are suitable for general applications requiring temperature stability. The dual sensor can be used in redundancy systems.

Applications: Industrial resistance thermometers, especially in chemical, power generation plants and analytical equipment.

Construction: Two separate platinum coils are embedded and sealed inside a high purity aluminum oxide ceramic body. Lead wires are shear force resistant and assure proper connection to extension leads and cables.



Models

Description	Tolerance IEC 60751	Order No.	Dimensions mm					Self Heating 0°C (K/mW)	Response time			
			L	D	d	l ₁	l ₂		Water current V=0.4m/s		Air stream V=3m/s	
2Pt100 KN 3026	W0.3	32.206.620	30 ⁺³ ₋₀	2.6±0.15	0.27±0.01	11.0±0.5	10.0±0.5	0.04	0.3	0.6	11.0	36.0
	W0.15	32.206.569										
	W0.1	32.206.647										

Technical Specification

Nominal resistance:	100 Ohm @ 0 °C	Measuring current:	1 mA
Temperature range:	W0.3 (Class B) = -196 to +660 °C W0.15 (Class A) = -196 to +600 °C (Heraeus exceeds IEC 60751: -100 to +450 °C) W0.1 (Class 1/3) = -100 to +350 °C	Tolerance class:	- According to IEC 60751:2008 - Other standards and narrower tolerances are available on request
Temperature coefficient:	Tc = 3850 ppm/K	Temperature stability:	Excellent long-term stability
Leads:	Palladium-gold alloy	Also available:	- Platinum-gold alloy - Different temperature coefficients (3916 ppm/K - old JIS) - Extension leads
Insulation resistance after assembly:	> 100 MOhm @ 25 °C		

The measuring point is located at 8 mm from the end of the sensor body.

Heraeus Sensor Technology USA

1901 Route 130
North Brunswick, NJ 08902
Phone 732-940-4400 Fax 732-940-4445
Email info.hst-us@heraeus.com
www.hst-us.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Heraeus:](#)

[32206620](#) [32206569](#) [32206647](#)