





Plug






Wire Terminated




Solder Cup

Socket



Wire Terminated



Solder Cup

DRAWING REVISIONS
(RELEASE DATE ON FILE)

REV	DOCUMENT	APP	APPROVAL DATE
1	CCS XXXXX	JW	ON FILE

NO. OF CONTACTS	A ± .010"	B MAX. (Plug) Min. (Socket)	C +.010" -.018"	D ±.005"	E ± .010"	F Max.
9 Plug	.778	.292	.398	.565	.208	.173
9 Socket	.778	.292	.398	.565	.208	.173
15 Plug	.928	.442	.548	.715	.208	.173
15 Socket	.928	.442	.548	.715	.208	.173
21 Plug	1.078	.592	.698	.865	.208	.173
21 Socket	1.078	.592	.698	.865	.208	.173
25 Plug	1.178	.692	.798	.965	.208	.173
25 Socket	1.178	.692	.798	.965	.208	.173
31 Plug	1.328	.842	.948	1.115	.208	.173
31 Socket	1.328	.842	.948	1.115	.208	.173
37 Plug	1.478	.992	1.098	1.265	.208	.173
37 Socket	1.478	.992	1.098	1.265	.208	.173
51 Plug	1.428	.942	1.048	1.215	.250	.220
51 Socket	1.428	.942	1.048	1.215	.250	.220

UNITS
ENGLISH INCHES

PRO/E

CATALOG DRAWING
DESIGN ENGINEER
J. WARRAICH

DATE
3/14/22

CONFIDENTIAL
THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH. ©COPYRIGHT 2009 CINCH

APPROVALS ON FILE

CINCH
1700 FINLEY RD
LOMBARD, IL 60148

MODELED BY:

TITLE
**DURA-CON ALL PLASTIC MICRO-D,
SOLDER CUP AND WIRE TERMINATED**

MATERIAL
CONTROL SPEC NUMBER

MATERIAL SPEC NUMBER
FINISH
PROJECT NUMBER

CAD FILE NUMBER
DCDAXXXX


DRAWING NUMBER
DCDAXXXX

CAGE IDENT NO.
71785

SIZE
B

SCALE
NONE

SHEET 1 OF 2



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cinch Connectivity Solutions:

[DCDA21SSB](#) [DCDA9SSB](#) [DCDA9PSB](#) [DCDA15P6E5-18.0B](#) [DCDA15P6E5-36.0B](#) [DCDA15PSB](#) [DCDA51S6E5-36.0B](#) [DCDA51SSB](#) [DCDA9P6E5-18.0B](#) [DCDA9P6E5-36.0B](#) [DCDA9S6E5-18.0B](#) [DCDA9S6E5-36.0B](#) [DCDA37S6E5-36.0B](#) [DCDA37SSB](#) [DCDA51P6E5-18.0B](#) [DCDA51P6E5-36.0B](#) [DCDA51PSB](#) [DCDA51S6E5-18.0B](#) [DCDA31S6E5-36.0B](#) [DCDA31SSB](#) [DCDA37P6E5-18.0B](#) [DCDA37P6E5-36.0B](#) [DCDA37PSB](#) [DCDA37S6E5-18.0B](#) [DCDA25S6E5-36.0B](#) [DCDA25SSB](#) [DCDA31P6E5-18.0B](#) [DCDA31P6E5-36.0B](#) [DCDA31PSB](#) [DCDA31S6E5-18.0B](#) [DCDA21S6E5-18.0B](#) [DCDA21S6E5-36.0B](#) [DCDA25P6E5-18.0B](#) [DCDA25P6E5-36.0B](#) [DCDA25PSB](#) [DCDA25S6E5-18.0B](#) [DCDA15S6E5-18.0B](#) [DCDA15S6E5-36.0B](#) [DCDA15SSB](#) [DCDA21P6E5-18.0B](#) [DCDA21P6E5-36.0B](#) [DCDA21PSB](#)