



Figure 1 illustrates the dimensions and marking of the 100-pin BGA package. The package is shown from two perspectives: a top view and a side view. The top view dimensions are 7.3MAX (width), 6.8MAX (height), and 3.2±0.2 (pin pitch). The side view dimensions are 1.8MAX (height), 4.2REF (width), and 1.3REF (height). The marking diagram shows the package with 'XXX' and 'XXXX-XX' markings, and a circular marking with 'S' and 'F' in circles. The dimensions 7.4, 3.7, and 3.45 are also indicated.

1. Lowest DCR/uH in this small package size.
2. Frequency range up to 5.0MHZ.
3. -55°C to +125°C operating temperature.
4. Handles high transient current spikes without saturation.
5. Composite construction providing extremely low buzz noise.

[illegible]

- (1). Inductance tolerance $\pm 20\%$ tested at 0.25V, 0ADC and 25°C
- (2). DCR measured at 25°C.
- (3). The DC current at which the inductance decreases by 20% from its initial value.
- (4). The DC current that results in a 40°C temperature rise from 25°C ambient
- (*) Part temperature (ambient + temp rise) should not exceed 125°C under worst case operating conditions. Circuit design, component placement, PCB trace size and thickness, airflow and other cooling provisions may affect the temperature of the part. Part temperature should be verified in the end application.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

<u>SCIHP0724-1R5M</u>	<u>SCIHP0724-3R3M</u>	<u>SCIHP0724-R68M</u>	<u>SCIHP0724-R47M</u>	<u>SCIHP0718-3R3M</u>	<u>SCIHP0724-R56M</u>
<u>SCIHP0718-2R2M</u>	<u>SCIHP0718-1R0M</u>	<u>SCIHP0718-1R5M</u>	<u>SCIHP0718-4R7M</u>	<u>SCIHP0724-2R2M</u>	<u>SCIHP0724-R82M</u>
<u>SCIHP0718-R33M</u>	<u>SCIHP0718-R82M</u>	<u>SCIHP0724-1R0M</u>	<u>SCIHP0718-R68M</u>		