

Recommended EMI/EMC Filter NAC-06-472



High voltage pulse noise type : NAP series
Low leakage current type : NAM series

* The EMI/EMC Filter is recommended to connect with several devices.

- ① Series name
- ② Single output
- ③ Output wattage
- ④ Universal input
- ⑤ Output voltage
- ⑥ Optional *7
- C : with Coating
- G : Low leakage current
- V : External potentiometer for output voltage adjustment
- U : Low input voltage stop (Complies with SEMI F-47)
- R : Remote on/off (Required external power source)
- F4 : Low speed fan
- T2 : Horizontal terminal block (non-screw-hold type)

See 5.1 in Instruction Manual.

SPECIFICATIONS

	MODEL		PLA300F-5	PLA300F-12	PLA300F-15	PLA300F-24	PLA300F-36	PLA300F-48
INPUT	VOLTAGE[V]		AC85 - 264 1 ϕ (Output derating is required at AC85V - 115V. See 1.1 and 3.2 in Instruction Manual) *3 (DC input and AC265 - 277V input *3)					
	CURRENT[A]	ACIN 100V	3.1typ (Io=90%)	3.4typ (Io=90%)				
		ACIN 115V	3.0typ (Io=100%)	3.3typ (Io=100%)				
		ACIN 230V	1.5typ (Io=100%)	1.7typ (Io=100%)				
	FREQUENCY[Hz]		50 / 60 (47 - 63) (DC input and 440Hz *3)					
	EFFICIENCY[%]	ACIN 100V	73typ (Io=90%)	78typ (Io=90%)	80typ (Io=90%)	84typ (Io=90%)	84typ (Io=90%)	84typ (Io=90%)
		ACIN 115V	74typ (Io=100%)	78typ (Io=100%)	80typ (Io=100%)	84typ (Io=100%)	84typ (Io=100%)	84typ (Io=100%)
		ACIN 230V	77typ (Io=100%)	81typ (Io=100%)	83typ (Io=100%)	87typ (Io=100%)	87typ (Io=100%)	87typ (Io=100%)
	POWER FACTOR	ACIN 100V	0.98typ (Io=90%)					
ACIN 115V		0.98typ (Io=100%)						
ACIN 230V		0.95typ (Io=100%)						
INRUSH CURRENT[A]	ACIN 100V	20typ (Io=90%) Ta=25℃ at cold start						
	ACIN 115V	20typ (Io=100%) Ta=25℃ at cold start						
	ACIN 230V	40typ (Io=100%) Ta=25℃ at cold start						
LEAKAGE CURRENT[ma]		0.75max (ACIN 115V / 240V, 60Hz, Io=100%, According to IEC60950-1 and DEN-AN)						
OUTPUT	VOLTAGE[V]		5	12	15	24	36	48
	CURRENT[A]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)					
		ACIN 115V-264V	50	25	20	12.5	8.4	6.3
	WATTAGE[W]	ACIN 85-115V	Output derating is required at ACIN 115V or less (refer to instruction manual 3.2)					
		ACIN 115V-264V	250	300	300	300	302.4	302.4
	LINE REGULATION[mV] *4		20max	48max	60max	96max	144max	192max
	LOAD REGULATION[mV] *4		40max	100max	120max	150max	150max	300max
	RIPPLE[mVp-p] *1	0 to +50℃	80max	120max	120max	120max	150max	150max
		-10 to 0℃	140max	160max	160max	160max	160max	400max
	RIPPLE NOISE[mVp-p] *1	0 to +50℃	120max	150max	150max	150max	200max	200max
		-10 to 0℃	160max	180max	180max	180max	240max	500max
	TEMPERATURE REGULATION[mV]	0 to +50℃	50max	120max	150max	240max	360max	480max
-10 to +50℃		75max	180max	180max	290max	440max	600max	
DRIFT[mV] *2		20max	48max	60max	96max	144max	192max	
START-UP TIME[ms]		300typ (ACIN 115V, Io=100%)						
HOLD-UP TIME[ms]		20typ (ACIN 115V, Io=100%)						
OUTPUT VOLTAGE ADJUSTMENT RANGE[V]		4.50 to 5.50	10.80 to 13.20	13.50 to 16.50	21.60 to 26.40	32.40 to 39.60	43.20 to 52.80	
OUTPUT VOLTAGE SETTING[V]		5.00 to 5.15	12.00 to 12.48	15.00 to 15.60	24.00 to 24.96	36.00 to 37.44	48.00 to 49.92	
PROTECTION CIRCUIT AND OTHERS	OVERCURRENT PROTECTION		Works over 105% of rating and recovers automatically					
	OVERVOLTAGE PROTECTION[V]		5.75 to 7.00	13.80 to 16.80	17.25 to 21.00	27.60 to 33.60	41.40 to 50.40	55.20 to 67.20
	OPERATING INDICATION		LED (Green)					
	REMOTE SENSING		Not provided					
REMOTE ON/OFF		Optional (Required external power source. Option -R)						
ISOLATION	INPUT-OUTPUT • RC *10		AC3,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	INPUT-FG		AC2,000V 1minute, Cutoff current = 10mA, DC500V 50MΩ min (At room temperature)					
	OUTPUT • RC-FG *10		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
	OUTPUT-RC *10		AC500V 1minute, Cutoff current = 100mA, DC500V 50MΩ min (At room temperature)					
ENVIRONMENT	OPERATING TEMP., HUMID.AND ALTITUDE *5		-20 to +70℃ (Output derating is required), 20 - 90%RH (Non condensing), 3,000m (10,000 feet) max					
	STORAGE TEMP., HUMID.AND ALTITUDE		-20 to +75℃, 20 - 90%RH (Non condensing), 9,000m (30,000 feet) max					
	VIBRATION		10 - 55Hz, 19.6m/s ² (2G), 3minutes period, 60minutes each along X, Y and Z axes					
	IMPACT		196.1m/s ² (20G), 11ms, once each X, Y and Z axes					
SAFETY AND NOISE REGULATIONS	AGENCY APPROVALS		UL60950-1, C-UL (CSA60950-1), EN60950-1, EN50178 Complies with DEN-AN					
	CONDUCTED NOISE		Complies with FCC-B, VCCI-B, CISPR22-B, EN55011-B, EN55022-B					
	HARMONIC ATTENUATOR *9		Complies with IEC61000-3-2 class A					

SPECIFICATIONS

OTHERS	CASE SIZE/WEIGHT	102×41×190mm [4.02×1.61×7.48 inches] (Excluding terminal block and screw) (W×H×D) / 1.0kg max	
	COOLING METHOD	*8	Forced cooling (internal fan)
WARRANTY	WARRANTY	*6	5 years (subject to the operating conditions)

*1 This is the result of measurement of the testing board with capacitors of 22 μ F and 0.1 μ F placed at 150 mm from the output terminals by a 20 MHz oscilloscope or a ripple-noise meter equivalent to Keisoku-Giken RM103.
See 1.6 of Instruction Manual for more details.

*2 Drift is the change in DC output for an eight hour period after a half-hour warm-up at 25°C.

*3 Output power derating is required. Consult us if the power supply needs to be used for DC input, 440Hz input or AC265-277V input.

*4 Consult us about dynamic load and input response.

*5 Output power derating is required. See 3.2 in Instruction Manual.

*6 See 3.3 in Instruction Manual for more details.

*7 Consult us about safety agency approvals for the models with optional functions.

*8 The fan speed slows down at no load.

*9 Consult us about other classes.

*10 The RC terminal is added to option -R models. The RC terminal is isolated from input, output, and FG.

* Do not use the power supply in overcurrent conditions or in unspecified input voltage ranges. Otherwise the internal components may be damaged.


* Parallel operation is not possible with this mode.

* Sound noise may be heard from the power supply when used for pulse load.

Features


- Cost-effective
- Longer life (see Instruction Manual)
- Low profile (meets 1U height = 41 mm or 1.61 inches)
- Wide operating temperature range (-20°C to +70°C see instruction manual)
- Screw hold type terminal block
- Slow fan speed at no load
- Many optional functions
- Complies with SEMI F-47 (-U option, see Instruction Manual for details)

Block diagram



External view

The external size of -V option, -R option, and -T2 option models is different from the standard model. See "5. Options and Others" in Instruction Manual for more details.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cosel:

[PLA300F-12-C](#) [PLA300F-12-G](#) [PLA300F-12-U](#) [PLA300F-12-V](#) [PLA300F-15-C](#) [PLA300F-15-G](#) [PLA300F-15-U](#)
[PLA300F-15-V](#) [PLA300F-24-C](#) [PLA300F-24-G](#) [PLA300F-24-U](#) [PLA300F-24-V](#) [PLA300F-36-C](#) [PLA300F-36-G](#)
[PLA300F-36-U](#) [PLA300F-36-V](#) [PLA300F-48-C](#) [PLA300F-48-G](#) [PLA300F-48-U](#) [PLA300F-48-V](#) [PLA300F-5-C](#)
[PLA300F-5-G](#) [PLA300F-5-U](#) [PLA300F-5-V](#)