


RED INDICATES ORIGINAL

DISK #	DWG SIZE	REVISIONS			1-0341		SH 1
		REV	EO	DESCRIPTION	DWN	APPROVED	
C5	C	T	9367	.830 DIA MAX WAS .810 DIA	DKC	B.M. <i>H</i>	7-23-91

DASH NO	FIG	CABLES ACCOMMODATED	ASSEMBLE PER
-1	1.3	RG-58	TAI-101
-U1		ESSEX 621-715	
-2		RG-59	
-U2			
-2A		BELDEN 8279	
-U2A			
-2B		W.E.CO. 730A	
-U2B			
-3		RG-223	
-U3			
-3A		RG-55	
-U3A			
-4		RG-122	
-U4		BELDEN 8218	
-5		RG-174	
-U5		RG-187	
-5A		RG-196	
-U5A			
-5B		HEWLETT-PACKARD 8120-1107	
-U5B			
-21		RG-303	
-U21			
-22		RG-180	
-U22			
-31		GRUMMAN 6C8758P1	
-U31		RG-187 DBL SHLD	
-34		BELDEN 8228	
-U34			
-36		275-3991 MICRODOT	
-U36		616-569 AMPEX	
-37		810 RAYCHEM	
-U37			
-41		RG-304	
-U41		9248 BELDEN	
-44		BRAND-REX B749	
-U44		60RE C06C032	
-53		69555 BELDEN	
-63		734A, AT&T	
-U63			
-086	2	RG-405	TAI-130
-U086			
-141		RG-402	
-U141			

FIG 1
- 1 SHOWN



INCH	MM
.005	0.13
.030	0.76
.096	2.44
.125	3.18
.187	4.75
.250	6.35
.281	7.14
.284	7.21
.312	7.92
.437	11.10
.630	16.00
.635	16.13
.750	19.05
.790	20.07
.830	21.08
1.000	25.40
1.406	35.71
1.846	46.89

FIG 2
- 086 SHOWN






FIG 3
- 1 SHOWN



- ⚠ IF BEND RELIEF SPRING REQUIRED (FIG 3)
ADD SUFFIX "BR" TO MODEL NO (NOT AVAILABLE WITH
CABLE GROUPS -63, -U63, -086, -U086, -141 & -U141)
5. FEMALE TYPE BNC COAXIAL INSULATED BULKHEAD JACKS,
BOTH 50 & 75 OHM VERSIONS
 4. MAX PANEL THK .187
 3. DASH NO DENOTES CABLE GROUP EXCEPT "U" PREFIX DENOTES 75 OHM VERSION
 2. FINISH: TFS-1A (NICKEL)
 1. ALL DIM ARE IN INCHES

RECOMMENDED
PANEL CUTOUT
SCALE: NONE



QTY	DESCRIPTION	PART NUMBER	ITEM
110-0002	TOL UNLESS SPECIFIED	BJ26/UBJ26 BJ26BR/UBJ26BR	
105-0717	.XX ±		
105-0623	.XXX ± .005		
305-0361	155-0393	DRAWING NO. 1-0341	REV T
108-1016	ENGR		
NEXT ASSY	APPR		
SCALE 2/1		DATE 10/13/89	SHEET 1 OF 2

TROMPETER
RF connectivity

MATERIAL
CODE IDENT
14949

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[UBJ26-5](#)