

Technical drawing of a rectangular floor slab. The overall dimensions are 25 (width) by 48 (length). The width is divided into a central section of 14 and two side sections of 7 x 2 = 14. The length is divided into a central section of 24 x 2 = 48 and two end sections of 2. The drawing shows a grid of reinforcement bars. The top reinforcement is labeled with '1' and the bottom reinforcement with '2'. The reinforcement bars are shown as circles with cross-hatching. The drawing is a top-down view of the slab.

Technical drawing of a rectangular plate. The overall width is 50 max. and the overall height is 22.95 ±0.2. The plate has a series of 20 vertical slots along its length. The distance between the centers of adjacent slots is 1 max. The plate is shown in a perspective view with a dashed line indicating the center of the slots.

1) $\varnothing 0,6 \pm 0,05$ Durchmesser des metallisierten Loches
 $\varnothing 0,6 \pm 0,05$ Diameter of finished plated-through hole
 $\varnothing 0,7 \pm 0,02$ Bohrungsdurchmesser des Loches
 $\varnothing 0,7 \pm 0,02$ Diameter of drilled hole

Metal plating of plated-through hole
see drawing 114406

Information:		Tolerances		 Scale 2:1		Angaben zu entsprechender Ident-Nr. siehe Fertigungsunterlagen For further information about I.D. number see manufacturing document	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation ERmet Federleiste E ERmet Female Type E			
		 www.ERNI.com		104087		1	
a		12.03.2001		M:00019595_SZA		ERM	
Index		Date					

Marking see drawing 401194

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[104087](#)