






M 2:1



Masse nur informativ
keine Prüfpläne erstellen.

Technical Data:

Insertion/withdrawal force per contact: $\leq 10\text{N} / \leq 1.6\text{N}$
 Mechanical operations: ≥ 500
 Contact resistance: $\leq 1\text{m}\Omega$

Operation Temperature: $-55^\circ\text{C} - +125^\circ\text{C}$

Solder temperature: according JEDEC 020C
 Suitable assembly process: leadfree wave / reflow soldering

RoHS compliance: yes (6/6)

Designed for use with: straight female DIN, female 2mm HM connector

Packaging: antistatic plastic bag
 Packaging unit: 100 pieces per bag
 Marking of packaging: label or direct printed on bag
 required date see ERNI labeling spec. 254792

Current	Cable cross area	AWG
10 A	1.5 mm ²	16
20 A	4 mm ²	12
30 A	6 mm ²	10
40 A	10 mm ²	8

Missing informations
and dimensions
see at DIN 41626

594176	1	40 A	2-4 $\mu\text{mNiP}+$ 0.1 $\mu\text{m Au}$	4.8	5.6	5.2
594174	1	20 A		2.9 $\sim$ 0.5	3.7	4.0
594172	1	10 A		1.8	2.5 $\pm$ 0.3	3.0
294761	1	40 A	2 - 3 $\mu\text{m Ni}$ min. 1.3 $\mu\text{m Au}$	4.8	5.6	5.2
053456	1	30 A		3.45 $\pm$ 0.1	4.5	4.7 $\pm$ 0.6
294760	1	20 A		2.9 $\sim$ 0.5	3.7	4.0
294759	1	10 A		1.8	2.5 $\pm$ 0.3	3.0
Part-No.	Class	Current	Plating	ϕA	ϕB	C

Information:		Tolerances	 All Dimensions in mm	Scale	5:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation High Current Female Contact <i>Hand Solder Termination</i>		
 www.ERNI.com		053316		I A3		
I	18.06.2015	Date		Class	STVSKO	

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 9001:2015 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[594174](#) [594172](#) [594176](#)