


- NOTES:
- 1.0 SPECIFICATIONS:
    - 1.1 FREQUENCY RANGE: DC to 500 MHz
    - 1.2 MAXIMUM INPUT POWER:
      - +25°C 2 WATTS
      - +125°C 0.5 WATTS
    - 1.3 OPERATING TEMPERATURE RANGE:
      - 55°C to +125°C
    - 1.4 MAXIMUM VSWR: 1.25:1
    - 1.5 IMPEDANCE: 50 OHMS

- 2.0 MARKING
  - 2.1 MARK UNIT AS SHOWN (REF.: INK-02639-27-55)

- 3.0 DIMENSIONS IN PARENTHESIS ARE IN MILLIMETERS.



REV.	DESCRIPTION	DATE
-	RELEASED	2/16/95
A	ECN 14586	7/6/95
A1	ADDED TITLEBLOCK	10/26/05

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE:  3 PLACE DECIMALS ±.005  2 PLACE DECIMALS ±.02  FRACTIONS ±1/64  PARALLELITY: T.I.R. _____  FLATNESS: T.I.R. _____  CONCENTRICITY: T.I.R. _____  ANGLES AND PERPENDICULARITY: ±1'	FSCM NO. <b>34078</b>		<i>MIDWEST MICROWAVE</i>	
	NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Midwest Microwave		TITLE  TERMINATION	
	DRAWN/DATE A.BEATTY 2/14/95		ENG./DATE A.OSGA 2/16/95	
CHECKED/DATE P.GOODMAN 2/16/95		APPROVED/DATE		
		DRAWING NUMBER  TRM-2050-MM-BNC-10		
		SCALE: 5=1	SHEET 1 of 1	

MODEL NUMBER	REV.
TRM-2050-MM-BNC-10	A1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[TRM-2050-MM-BNC-10](#)