







Layout



M 2:1



Masse nur informativ,
keine Prüfpläne erstellen.

Technical Data:

Insertion/withdrawal force per contact:	≤ 10N
Mechanical operations:	≥ 500
Contact resistance inner conductor:	≤ 10 mOhm
outer conductor:	≤ 3 mOhm
Insulation resistance inner/outer conductor:	≥ 200 MOhm
Operation Temperature:	-55°C - +125°C
Frequency range:	0-2 GHz
Return loss:	> 20dB (2GHz)
Solder temperature:	according JEDEC 020C
Suitable assembly process:	leadfree wave / reflow soldering
RoHS compliance:	yes (6/6)
Designed for use with:	female 2mm HM connector
Packaging:	antistatic plastic bag
Packaging unit:	100 pieces per bag
Marking of packaging:	label or direct printed on bag
	required date see ERNI labeling spec. 254792

Missing informations
and dimensions
see at DIN 41626

104875	1	1.5-2.5µm Cu, 2 - 3µmNiP+ 0.15µm Au
294874	1	2 - 3µm Ni min.1.3µm Au sel.
Part-No.	Class	Plating

Information:		Tolerances	 All Dimensions in mm	Scale	5:1	
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation Coaxial Male Contact 50 Ohm Right Angle Press-fit Termin.		
e		31.07.2013	 www.ERNI.com		294873	
Index		Date	Class		STVSKO	
					I A3	

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 9006 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[104875](#)