

PART NUMBER	ITEM ① BODY	ITEM ② CONTACT	ITEM ③ INSULATOR	ITEM ④ SCREW
142-0711-281	BRASS GOLD PL .00002 MIN OVER NICKEL PL .00005 MIN OVER COPPER	BERYLLIUM COPPER GOLD PL .00005 MIN OVER NICKEL PL .00005 MIN OVER COPPER	TEFLON	STAINLESS STEEL L=3/16"

REV	ECO	DATE
1	INITIAL RELEASE	24MAR2023

NOTES:

1. ELECTRICAL SPECIFICATIONS:

- 1.1 IMPEDANCE: 50 OHMS
- 1.2 FREQUENCY RANGE: 0-26.5 GHz
- 1.3 VSWR: 1.50 MAX
- 1.4 WORKING VOLTAGE: 170 VRMS MAX AT SEA LEVEL
- 1.5 DIELECTRIC WITHSTANDING VOLTAGE: 500 VRMS MIN AT SEA LEVEL
- 1.6 INSULATION RESISTANCE: 1000 MEGOHM MIN
- 1.7 CONTACT RESISTANCE:
 - 1.7.1 CENTER CONTACT - INTIAL 3.0 MILLIOHM MAX, AFTER ENVIRONMENTAL 4.0 MILLIOHM MAX
 - 1.7.2 OUTER CONDUCTOR - INITIAL 2.0 MILLIOHM MAX
- 1.8 CORONA LEVEL: 125 VOLTS MINIMUM AT 70,000 FEET
- 1.9 RF HIGH POTENTIAL WITHSTANDING VOLTAGE: 335 VRMS MIN AT 4 AND 7 MHZ


2. MECHANICAL SPECIFICATIONS:

- 2.1 ENGAGE/DISENGAGE TORQUE: 2 IN LBS MAX
- 2.2 MATING TORQUE: 7-10 IN LBS
- 2.3 DURABILITY: 500 CYCLES MIN

3. ENVIRONMENTAL:





(MEETS OR EXCEEDS THE APPLICABLE PARAGRAPH OF MIL-PRF-39012)

- 3.1 THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B EXCEPT 115°C HIGH TEMP.
- 3.2 OPERATING TEMPERATURE: -65 °C TO 165 °C
- 3.3 CORROSION: MIL-STD-202, METHOD 101, CONDITION B
- 3.4 SHOCK: MIL-STD-202, METHOD 213, CONDITION I
- 3.5 VIBRATION: MIL-STD-202, METHOD 204, CONDITION D
- 3.6 MOISTURE RESISTANCE: MIL-STD-202, METHOD 106




2X #0-80UNF SCREW

RECOMMENDED SCREW DIMENSIONS	
L	PCB THICKNESS
3/16"(4.76mm)	.030"(0.76mm) to .096"(2.44mm)



DETAIL A
SCALE 10:1



RECOMMENDED PCB LAYOUT
NOTE: THIS PATTERN IS FOR REFERENCE ONLY.
PATTERN MAY VARY DEPENDING ON ASSEMBLY
PROCESS, BOARD TYPE, OR SPECIFIC ELECTRICAL OR
MECHANICAL REQUIREMENTS.

 <small>This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is not traced or copied without permission and is returnable upon demand.</small> <small>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018.</small>	Model No: 142-0711-281/290	Title: JOHNSON	
	RoHS <input checked="" type="checkbox"/> (EU)/2015/863 COMPLIANT	Cage Code	
	UNLESS OTHERWISE SPECIFIED UNITS: INCH .X ± - .XX ± - .XXX ± .005 ANGLE ± 2°	3RD ANGLE PROJECTION Drawn by: TOMMY REN Date: 2023/03/24	Drawing No. 142-0711-281/290 Rev. 1
	Size B	DO NOT SCALE DRAWING	Workmanship Std/Sheet NONE 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[142-0711-281](#)