


RoHS COMPLIANT



For stripping and assembly instructions see Drawing Number: VAIF1301

Electrical Characteristics

Nominal Impedance:	Cable Dependent
Frequency Range:	DC to 2 GHz
VSWR:	1.35:1 maximum
Operating Voltage (rms):	250 V maximum at sea level

Mechanical Characteristics

Mating Cycles:	500 cycles minimum
Interface Dimensions:	Conform to MIL-C-39012

Environmental Characteristics

Temperature Range:	-55 °C to +85 °C
--------------------	------------------

	PART	DESCRIPTION		
1	Body	Brass, nickel plated		
CAD Issue		SN	2	30 Sep 02
First Issue		AT	1	15 Nov 99
DESCRIPTION OF REVISION		APPVD	ISS	DATE



Cinch Connectivity Solutions
7-13 Russell Way,
Widford Industrial Estate,
Chelmsford, Essex,
CM1 3AA, UK.
Tel: +44 (0) 1245 359515
Fax: +44 (0) 1245 358938

SCALE: Not To Scale

DIMENSIONS: mm

TOLERANCES:
± 0.2mm unless
otherwise stated

DRAWN BY:

S Nash

CHECKED BY:

APPROVED BY:

DATE:

30 Sep 02

TITLE:

F Twist-On Plug for RG58

PART NUMBER:

TOF58

PAGE: 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[TOF58](#)