




Leiterplattendicke 2 mm
Layoutempfehlung siehe 225321




PCB thickness 2 mm
For recommended dims see 225321



SCHNITT D-D
SECTION D-D

Leiterplattendicke 1,6 mm
Layoutempfehlung siehe 225321




PCB thickness 1,6 mm
For recommended dims see 225321



SCHNITT D-D
SECTION D-D


Leiterplattendicke 1 mm
Layoutempfehlung siehe 225321

PCB thickness 1 mm
For recommended dims see 225321




SCHNITT D-D
SECTION D-D


Abspulrichtung / Reel off direction



M 1:5
SCALE 1:5



SIEHE ANSICHT A
SEE DETAIL A







ANSICHT A
M 1:1
DETAIL A
SCALE 1:1




VPE: 250 Stück
PU: 250 pcs.

Anwendungsbeispiel / Application example




Gewinde-Löcher / Thread holes



Standard-Löcher / Standard holes



Montageloch für Verdrehschutz / Assembly hole for twist protection




Maßempfehlung für Gehäuseintegration siehe 225406
Recommended dimensions for integration in housing see 225406

Technische Daten siehe Document 225407
Technical data see document 225407


Hinweise:
Für den O-Ring ist eine Einführschrage vorzusehen! Zur Verringerung der Montagekräfte den O-Ring oder das Gehäuse ggf. befetten.
Je nach Lötverfahren oder Lötanlage kann es notwendig sein den O-Ring erst nach dem Löten zu montieren.
Note:
For the O-ring there has to be a smooth chamfer at the housing! For reduction of assembly force grease for O-ring or housing can be used if applicable.
Dependent on soldering process or solder machines there can be a need to attach the O-ring after soldering.

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 16016 is to be observed.


225263	2	no	no	4	1,2,3,4	T&R	
225264	2	yes	no	4	1,2,3,4	T&R	
Ident-Nr. Ident No.	Zeichnung Nr. Drawing No.	Schirm Shield	O-ring O-ring	Polzahl No. pins	Kontakt Nr. Contact No.	Verpackung Packaging	Bemerkung Remarks
Information		Tolerances			Scale	1:4	
All rights reserved. Only for information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		Subject to modification without prior notice. Drawing will not be updated.		Designation all Varianten / all versions M12 90° M D THR Rückmontage M12 90° M D THR rear mount			
						www.ERNI.com	
B		06.10.17			Class	M12	
Index		Date					

Ident-Nr. <i>Ident-No.</i>	O-ring <i>O-ring</i>	Schirm <i>Shield</i>	Verguß Potting
225263	no	no	recommended
225264	no	yes	not needed


Darstellung mit Schirm und O-Ring
Drawn with shield and O-ring




Gemessen über Schirmkontakte
Measured over shield contacts




SNITT E-E
SECTION E-E




SNITT B-B
SECTION B-B



Ansaugfläche
Pick & place area



SNITT F-F
SECTION F-F



Steckgesicht nach IEC 61076-2-101
Mating face acc. IEC 61076-2-101

Handschriftliche Änderungen auf
CAD Zeichnungen sind nicht zulässig!

Information		Tolerances		Scale	5:1
All rights reserved. Only for information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.		All Dimensions in mm		Designation	
		Subject to modification without prior notice. Drawing will not be updated.		4 polige Version / 4 pin version M12 90° M D THR Rückmontage M12 90° M D THR rear mount	
B	06.10.17	www.ERNI.com		225265	I (2 / 2) A2
Index	Date	Class		M12	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[225263](#) [225264](#)