






RECOMMENDED PCB LAYOUT (COMPONENT SIDE VIEW)
EMPFOHLENES LEITERPLATTEN-LAYOUT (BESTUECKUNGSSEITE)
TOL. ±0.05 [0.002] UNLESS NOTED



RECOMMENDED PANEL CUTOUT
EMPFOHLENER FRONTPLATTEN-AUSSCHNITT



Technical specifications

Materials & Finish

Insulation body	PBT
Contact material	Phosphor Bronze (C5210)
Contact finish, mating zone	30µin Au
Contact finish, termination zone	150-200µin Sn matte
Underplating	50-100µin Ni
Shell/shield material	C2680 (acc. JIS)
Shell/shield plating	30µin Ni

Assembly Process

Packaging	Tray
Solder temperature	240°C at 3-5s
Suitable assembly process	wave

Approvals

UL insulation body	V0
UL File No.	E145613
RoHS compliant	Yes

Mechanical properties

Insertion/withdrawal force	IEC 603-7	max. 20 N
Mechanical operations	IEC 512-5, 9a	min. 1.000
Effectiveness of connector coupling device	IEC 512-8, 15f	50 N

Electrical properties

Creepage / clearance distances		
a) Contact - contact	IEC 807-3	0,52 mm
b) Contact - shell	IEC 807-3	min 1,0 mm
Voltage proof (Dielectric Withstand Voltage)		
a) Contact - contact	IEC 512-2, 4a	min. 1.000 V AC/DC
b) Contact - shell/ testpane	IEC 512-2, 4a	min. 1.500 V AC/DC
Current carrying capacity	IEC 512-3, 5b	1.5 A @ 25°C
Contact resistance	IEC 512-2, 2a	max. 30 mOhm
Insulation resistance	IEC 512-2, 3a	min. 500 MOhm

Environmental properties

Operation temperature	-40 to +85°C
-----------------------	--------------

NOTE 1: C-UL APPROVED E145613 AND MEETS FCC REQUIREMENTS
NOTE 2: RoHS COMPLIANT

PART NO. IDENT. NR.	TRANSMISSION REQUIREMENT ÜBERTRAGUNGSANFORDERUNG		
203540	CATEGORY 3/4		
Information:	Tolerances x ±0.50 x.x ±0.38 x.xx ±0.25		Scale 2:1
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.	Subject to modification without prior notice. Drawing will not be updated.	Designation MOD JACK - MJV 8P8C, 1 x 4, VERTICAL	
www.ERNI.com		203539	(1/1) A3
Index	11.12.2013 Date	Class	MJ

Copyright by ERNI GmbH
Proprietary notice pursuant to ISO 9006 to be observed.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ERNI Electronics:](#)

[203540](#)